

# Miscellaneous Accessories



301

## Scotchcast™ 4413 Filled Cable Cleaning Kit



A specially formulated cleaning solvent for cleaning grease and Flex-Gel filling compound from filled core cable without damaging connectors, cable or individual conductors. One bag will clean both cable ends at splice point. Comes complete with the right amount of solvent sealed in the bag. No special tools are required. Virtually no personnel contact with the solvent or solvent vapors occurs during cleaning because of the unique packaging concept.

Kit contents:

- Heat-sealed cleaning bag with solvent
- Pair gloves
- Puncture-protection bags (2)

Four different sizes are available to meet a wide range of applications.



302

## Scotchcast 4414 Filled Cable Cleaning Kit



The Scotchcast 4414 Filled Cable Cleaning Kit provides all the necessary materials for cleaning the filling compound from filled copper and fiber optic cables in an easy-to-transport kit. This kit includes 15 pads saturated in cleaning solvent, five scraper pads and 10 towels.

The specially formulated cleaning solvents are contained in premeasured portions on saturated pads for fast, easy, convenient solvent application to cable core after sheath has been removed. The solvent and wet pads effectively remove cable filling compound from conductors and connectors with no damage to either.

Kit contents:

- Solvent Saturated Pads (15)
- Scraper Pads (5)
- Towels (10)

Additional materials required:

- Scotchcast 4435 Sheath Scuff
- Scotch 88T Vinyl Tape



303

## Scotchcast 4415 Service Wire Cleaning Kit



Everything needed to clean troublesome filled service wire is included in the 4415 Kit. Solvent saturated pads are individually bagged for convenience. No extra tools are needed, and an instruction sheet is included in each kit.

Kit contents:

- Towels (10)
- Solvent Saturated Pads (10)



304

## Scotchcast W-9 Channeling Wedge



The Scotchcast W-9 Channeling Wedge is used in separating bundles of conductors when plugging cable. Made of flexible plastic, tapered at one end and grooved, the W-9 wedge separates conductors to ensure maximum penetration of the compound when forming a plug.



**Product Referral  
Generator**

Scotchcast 4435 Sheath Scuff pg. 196


Scotch™ 88T Vinyl Tape pg. 184

## Scotchcast™ 4435 Sheath Scuff



This flexible 80 grit, non-conductive, aluminum oxide strip is used to clean and rough up cable sheath. The clean, scuffed sheath greatly enhances the bond between the compound and sheath. Since the strip is 25.4 mm (1") wide, it encourages the craftsperson to scuff around the sheath rather than along it, thus eliminating moisture paths along the sheath, and also makes it easy to get into tight places.

Size: 25.4 mm x 22.86 m (1" x 75') roll



305

## Scotchcast 4458, 4458-W Pair Saver



Protect cable pairs from the sharp edges of the shield and template, while permitting standard bond connector installations.

4458

Size: 21.6 mm x 5.4 m (0.85" x 18') rolls

4458-W

Size: 38 mm x 5.5 m (1.5" x 18') rolls



306

## Ordering Information for Miscellaneous Accessories

Product Number	Packaging kg (lbs.)/cs.	Minimum Order	UPC
4413 Filled Cable Cleaning Kit			
4413-S (for up to 200-pair cables)	8/cs., 5.18 (11.5)	8 kits	054007-17442
4413-L (for up to 600-pair cables)	4/cs., 4.95 (11)	4 kits [87204013]	054007-17443
4413-XL (for 600- to 900-pair)	2/cs., 5.40 (12)	2 kits	054007-17441
4413-SXL (for 900-pair and more)	2/cs., 9.54 (21.2)	2 kits	054007-68466
4414 Filled Cable Cleaning Kit	1/cs., 0.63 (1.4)	1 kit [524082]	054007-57218
4415 Service Wire Cleaning Kit	10/kit, 10 kits/cs., 3.3 (7.3)	10 kits [525932]	054007-57219
4435 Sheath Scuff	1/box, 10/cs., 5.9 (13)	10 rolls [577541]	054007-13947
4458, 4458-W Pair Saver			
4458- 21.6 mm x 5.4 m (.85" x 18') rolls	1/box, 10/cs., 1.9 (4.0)	10 rolls	054007-32560
4458-W- 38 mm x 5.5 m (1.5" x 18') rolls	1/box, 10/cs., 3.7 (7.9)	10 rolls [315776]	054007-33629
Scotchcast W-9 Channeling Wedge	100/box, 1000/cs., 1.8 (4)	1000 each [529348]	054007-30229