



WATER RESISTANT


**3M**

THINSULATE™  
Insulation

# 3M™ Thinsulate™ Water Resistant Insulation

3M™ Thinsulate™ Water Resistant Insulation opens up a whole new world of warmth and comfort. Made with hydrophobic fibers for advanced water resistance, it will keep users warm, comfortable and dry without unnecessary weight.

- Contains siliconized synthetic fibers that absorb less than 1% of their weight in water
- Soft and luxurious feel



“My jacket with Thinsulate helps keep me warm and moving when I'm out hiking through the Pacific Northwest. It doesn't weigh me down, and helps me enjoy the outdoors longer and more comfortably!”

-KATHERINE G. | OREGON

Consumer received free product.  
Actual consumer not shown in photo.



TECHNOLOGY				ORIGINAL		FOOTWEAR	
<div style="display: flex; justify-content: space-around;"> <span>☹️</span> <span>☺️</span> <span>🔥</span> <span>👤</span> <span>⚠️</span> <span>🔄</span> </div>						👤	
<div style="display: flex; justify-content: space-between;"> <span>Warmest (140g and above)</span> <span>Warmer (60g-140g)</span> <span>Warm (60g or less)</span> </div>							
<div style="display: flex; justify-content: space-between;"> <span>FX40 FX70 FX100</span> <span>XT-S40</span> </div>				U40		BQ400	
<div style="display: flex; justify-content: space-between;"> <span>XT-S80 XT-S80 XT-S100</span> <span>FR20</span> </div>				U70 U100		B2200 B2400 B2500 BQ600	
<div style="display: flex; justify-content: space-between;"> <span>XT-S150</span> <span>FR150 FR200</span> </div>				C200 C250 C300		B600	
<div style="display: flex; justify-content: space-between;"> <span></span> <span>J60 J80 J100</span> </div>				U150 U200			
<div style="display: flex; justify-content: space-between;"> <span></span> <span>R70 R100 R150</span> </div>				G1100 G1200 G1500			
<div style="display: flex; justify-content: space-between;"> <span></span> <span>J120 J150 J200 J250</span> </div>				KL150 KL200 KL250 TYPE O			
<div style="display: flex; justify-content: space-between;"> <span></span> <span>R200</span> </div>				M200			
<div style="display: flex; justify-content: space-between;"> <span></span> <span>FL700</span> </div>							
<div style="display: flex; justify-content: space-between;"> <span>Fill Power Warmth (650-800)</span> <span>Fill Power Warmth (500-650)</span> <span>Fill Power Warmth (350-500)</span> </div>							
<div style="display: flex; justify-content: space-between;"> <span>Warmest (140g-250g)</span> <span>Warmer (60g-140g)</span> <span>Warm (Up to 60g)</span> </div>							
<div style="display: flex; justify-content: space-between;"> <span>Warmest (600g-1000g)</span> <span>Warmer (300g-600g)</span> <span>Warm (Up to 300g)</span> </div>							



**Home Care Division**

3M Center, Building 223-4NE-13  
St. Paul, MN 55144-1000  
651-575-6694  
thisinsulate.com

**3M and Thinsulate are trademarks of 3M, used under license in Canada.**  
Please recycle. Printed in U.S.A.  
© 3M 2015. All rights reserved.  
70-0717-0896-3

**IMPORTANT NOTICE**

**WARRANTY, LIMITED REMEDY AND DISCLAIMER:** 3M warrants that 3M™ Thinsulate™ Insulation that is stored, maintained and used in accordance with 3M's written instructions will meet the applicable 3M product specifications. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If any Thinsulate insulation does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**LIMITATION OF LIABILITY:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract or strict liability.

**PRODUCT USE:** Because of the variety of factors that can affect the use and performance of Thinsulate insulation, user is solely responsible for evaluating the product and determining whether it is fit for a particular purpose and suitable for user's method of application. 3M may change the product, specification and availability of the product as improvements are made; therefore, user should contact 3M for latest information before specifying the product.

All Thinsulate insulation rolls are made within strict dimensional tolerance specifications. However, length and/or width dimensions may shift, shrink, or otherwise change up to a maximum of ±4% during handling or shipment. Please allow 24 hours after vacuum pack is removed.



**WATER RESISTANT**  
J60, J80, J100, J120,  
J150, J200, J250