

# 3M™ Solus 1000 Series Safety Spectacles

## Technical datasheet



### Product description

The 3M™ Solus 1000 is a Safety Spectacle with:

- ▶ Slim frame
- ▶ 3M™ Scotchgard™ Anti-Fog coating
- ▶ Optional adjustable headband to be used with foam insert

### Key features

- ▶ Optical class 1 lens for prolonged use
- ▶ Single piece ocular lens
- ▶ Semi-rimless ocular frame
- ▶ Frame colours in either blue/black or green/black
- ▶ 3M™ Scotchgard™ Anti-Fog coating providing protection against fogging and scratching, meeting K & N marking requirements of EN 166
- ▶ Offers protection against UV radiation
- ▶ 3M™ Scotchgard™ Anti-Fog coating provides scratch resistance and durability, even after multiple washes
- ▶ Can be autoclaved for use in cleanroom environments (based on internal testing)

### Product range

3M™ Solus 1101SGAF-EU, clear polycarbonate lens with Scotchgard™ coating and Blue/Black frame

3M™ Solus 1201SGAF-EU, clear polycarbonate lens with Scotchgard™ coating and Green/Black frame

3M™ Solus 1103SGAF-EU, amber polycarbonate lens with Scotchgard™ coating and Blue/Black frame

3M™ Solus 1203SGAF-EU, amber polycarbonate lens with Scotchgard™ coating and Green/Black frame

3M™ Solus 1102SGAF-EU, grey polycarbonate lens with Scotchgard™ coating and Blue/Black frame

3M™ Solus 1202SGAF-EU, grey polycarbonate lens with Scotchgard™ coating and Green/Black frame

3M™ Solus 1201SGAFKT-EU, clear polycarbonate lens with Scotchgard™ coating, Green/Black frame, with foam insert and headband

3M™ Solus 1000S-EU, headband

3M™ Solus 1000G-EU, foam insert

### Typical applications

These products may be suitable for use in a wide variety of applications including:

- ▶ Industrial manufacturing
- ▶ Metal working
- ▶ Construction
- ▶ Food industry
- ▶ Pharmaceutical
- ▶ General laboratory

### Intended use

These products are intended for protection against a variety of hazards including low energy impact (F) at extremes of temperature -5°C and +55°C (T) in accordance with EN 166:2001. These products also help protect against UV radiation in accordance with EN 170:2002 (clear and amber lenses), and sun glare in accordance with EN 172:1994 (grey).

The Solus 1000 lenses are also intended to give an enhanced level of protection against fogging and scratching from the 3M™ Scotchgard™ coating which meets K rating for anti-scratch (AS) and N rating for anti-fog (AF) as per EN 166:2001.

Sterilisation by autoclaving - limited internal testing has been carried out on samples subjected to 10x, 20x, 30x and 40x automatic cleaning and disinfection and sterilisation by autoclaving at 121°C. Testing was then carried out on the following properties:

- ▶ Mechanical performance (BT)
- ▶ Anti-Fog properties (K)
- ▶ Anti-scratch properties (N)
- ▶ Optical performance

Based on the internal testing the claims remain valid.

**NOTE:** Sterilisation by autoclaving was only tested on the safety spectacles (Solus 1101SGAF-EU and Solus 1201SGAF-EU). Testing was NOT carried out on the foam insert or headband.

A number of lens options are available for a variety of different applications:

- ▶ Clear - Good colour recognition and excellent UV protection
- ▶ Grey - Protection from sunglare
- ▶ Amber - Enhanced contrast in low light conditions
- ▶ 3M™ Scotchgard™ – for added protection against fogging and scratching (EN 166 Anti-Fog (N) and Anti-Scratch (K))

## Use limitation

- ▶ Never modify or alter this product
- ▶ Do not use this product against hazards other than those specified in this document
- ▶ These products are not suitable for grinding or welding
- ▶ These products are NOT designed to be worn over prescription spectacles

## Standards and approval

These products are type examined by ECS GmbH European Certification Service, Obere Bahnstrasse 74, 73431 Aalen, Germany, Notified Body number 1883.

These products are CE marked to the requirements of the Community Directive 89/686/EEC or European Regulation (EU) 2016/425.

The applicable legislation can be determined by reviewing the Certificate and Declaration of Conformity at [www.3M.com/Eye/certs](http://www.3M.com/Eye/certs).

## Materials listing

Component	Material
Lens	Polycarbonate
Frame (rigid)	Polycarbonate
Frame (soft)	TPE
Headband	Nylon fibre
Headband connector	Polycarbonate
Foam insert (frame)	Nylon
Foam insert	EVA foam

## Marking

The products have demonstrated compliance with the requirements of EN 166:2001 and associated standards and bear the following marks:

Product lens	Frame	Marking
S1101SGAF-EU	2C-1.2 3M 1 FT K N	EN 166 FT CE
S1201GAF-EU	2C-1.2 3M 1 FT K N	EN 166 FT CE
S1103SGAF-EU	2C-1.2 3M 1 FT K N	EN 166 FT CE
S1203SGAF-EU	2C-1.2 3M 1 FT K N	EN 166 FT CE
S1102SGAF-EU	2C-3 / 5-3.1 3M 1 FT K N	EN 166 FT CE
S1202SGAF-EU	2C-3 / 5-3.1 3M 1 FT K N	EN 166 FT CE

## Explanation of marking

Marking	Description
2C-1.2 (EN 170:2002)	UV protection with good colour recognition. This product conforms to the requirements of the standard, providing UV protection for the complete specified range (210nm – 365nm).
5-3.1 (EN 172:1994 (as amended))	Sun-glare protection conforming to the requirements of the standard, providing UV protection for the complete specified range (280nm – 350nm).
1	Optical class
F	Impact protection against high speed particle at low energy (45m/s)
T	Tested for impact protection at extreme temperature conditions -5°C and +55°C
K	Resistance to surface damage by fine particles
N	Resistance to fogging

## IMPORTANT NOTICE

The use of the 3M product described within this document assumes that the user has previous experience of this type of product and that it will be used by a competent professional. Before any use of this product it is recommended to complete some trials to validate the performance of the product within its expected application.

All information and specification details contained within this document are inherent to this specific 3M product and would not be applied to other products or environment. Any action or usage of this product made in violation of this document is at the risk of the user.

Compliance to the information and specification relative to the 3M product contained within this document does not exempt the user from compliance with additional guidelines (safety rules, procedures). Compliance to operational requirements especially in respect to the environment and usage of tools with this product must be observed. The 3M group (which cannot verify or control those elements) would not be held responsible for the consequences of any violation of these rules which remain external to its decision and control.

Warranty conditions for 3M products are determined with the sales contract documents and with the mandatory and applicable clause, excluding any other warranty or compensation.

For more information on 3M products and services please contact 3M.