



# Flexible Air Sealing Tape 8068E

## FAST-G / FAST-M

### Product Data Sheet

Date: June 2016  
Supersedes: November 2014

#### Product Description

3M™ Flexible Air Sealing Tape 8068E FAST-G / FAST-M are air, moisture and water impermeable tape with an aggressive, high-tack acrylic pressure sensitive adhesive and reinforcing grid. 3M™ FAST-G is a self-wound tape, while 3M™ FAST-M has a poly-coated kraft paper release liner

#### Intended Use

- Seaming air of interior water vapour membranes
- Taping gaps and penetrations to stop free air flow

#### Key Features

- Aggressive acrylic pressure sensitive adhesive bonds to concrete, concrete block, anodized aluminium, galvanized metal, exterior gypsum and plywood without the use of any adhesion promoters.
- Reinforcing grid helps strengthen backing and reduce stretch
- Resists UV exposure up to 12 months
- Can be installed at temperatures as low as -20 °C and as warm as 50 °C
- Measurement markings for ease in cutting to the desired length

#### Physical Properties

	<b>8068E FAST-M</b>
Tape Colour	Tan, semi-translucent
Thickness of Tape (Film & Adhesive) (ASTM D-3652)	0,250 mm
Thickness of Adhesive	0,130 mm
Liner	0,150 mm
Backing	Multilayer Elastomeric Film
Release Liner	Poly-coated kraft paper
Adhesive Type	Acrylic

	<b>8068E FAST-G (LL)</b>
Tape Colour	Tan, semi-translucent
Thickness of Tape (Film & Adhesive) (ASTM D-3652)	0,250 mm
Thickness of Adhesive	0,130 mm
Backing	Multilayer Elastomeric Film
Adhesive Type	Acrylic

**Building Materials  
Compatibility Testing  
by “ift Rosenheim”**

The following building materials have been tested on compatibility (up to 60 °C) with 3M™ Flexible Air Sealing 8068E FAST-G / FAST-M by the scientific service provider and international testing institute “ift Rosenheim” with the result of no optical or function-affecting impairments.

- Concrete C35
- Exterior plaster HASIT 650 cement mortar
- Interior plaster HASIT 150
- Building plaster with Weber light mortar LM21 without primer
- Building plaster with Weber light mortar LM21 with primer
- fibreC glass fibre concrete slab 2.0
- Wood (spruce) rough, grinded / varnished / painted
- OSB panels class 3 with rough surface
- PVC-U, white
- Anodised aluminium / Powder-coated aluminium
- Vapour barrier: Ampatex DB90
- Vapour barrier: Öko Natur vapour barrier (Isozell)
- Vapour barrier: Folog Starvap D2 (PO)
- Vapour barrier: Isover Vario KM (PA)
- Vapour barrier: Siga Majpell (PE)
- Vapour barrier: D-Tack Tacolau (Alu Coating surface)

**Performance Characteristics**

	<b>8068E FAST-M</b>	<b>8068E FAST-G (LL)</b>
<b>Adhesion to Stainless Steel</b> 90° peel @room temp, 24 hr dwell, jaw speed 300mm/min (ASTM D-3330)	55 N/100mm	55 N/100mm
<b>Adhesion to Polyethylene</b> 90° peel @room temp, 24 hr dwell, jaw speed 300mm/min (ASTM D-3330)	33 N/100mm	33 N/100mm
<b>Adhesion to Anodised Aluminium</b> 90° peel @room temp, 24 hr dwell, jaw speed 300mm/min (ASTM D-3330)	77 N/100mm	77 N/100mm
<b>Tensile Properties</b> Longitudinal Transverse (acc. to EN 12311- 100mm/min)	138 N/50 mm / 1393 % 62 N/50 mm / 825 %	95 N/50 mm / 1466 % 64 N/50 mm / 914 %
<b>Thermal Shock Resistance</b> -20 °C up to 60 °C Ift Richtlinie MO-01/1 (4.3)	fulfilled	fulfilled
<b>Dynamic Shear Strength to different substrates</b> (acc. to EN 12311-, 5mm/min)	24 – 41 kPA	23 – 43 kPA
<b>Light resistance and resistance to moisture penetration</b> Ift Richtlinie MO-01/1 (4.4)	fulfilled	fulfilled

<b>Water Penetration Around Nails</b> (ASTM 1970)	Pass	Pass
<b>Water Vapour Permeability</b> (S <sub>d</sub> value) (EN 12572:2001-06)	11.6 m	14.8 m
<b>Application Temperature Performance</b>	-20 °C up to 50 °C	-20 °C up to 50 °C

---

### Application Handling

To obtain the best adhesion, 8068E FAST-G / FAST-M can be installed when outdoor temperatures range from -20 °C up to 50 °C over clean surfaces that are free from dirt and debris and have not absorbed water.

Surfaces should be free of any damaged, unsupported areas, sharp protrusions or voids.

Surfaces must be clear of snow, ice or frost

Concrete must be cured a minimum of 7 days before application.

Block or brick walls should have mortar joints stuck flush.

---

### UV Durability

When exposed to natural sunlight in Florida and Arizona and when exposed to accelerated aging conditions, the performance of 3M™ Flexible Air Sealing Tape 8068E FAST-G / FAST-M remains stable over an extended period. Based on these tests and performance observed in actual installations, 3M is confident in claiming that the tape will remain fully functional up to 12 months of exposure to sunlight.

---

### Storage & Shelf Life

Store at 16 °C – 25 °C and 40-65 % relative humidity in its original box. The product can be stored up to 24 months after production.

**Note:** Product shall not be exposed to UV radiation during storage

---

### For Additional Information

To request additional product information or to arrange for sales assistance, please see below for contact details.

---

---

## Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

---

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

---

3M is a trademark the 3M Company.



### **3M Svenska AB Industri**

Bollstanäsvägen 3

191 89 Sollentuna

Tel: 08-92 21 00

Fax: 08-92 22 88

E-post:

[kundservice@mmm.co](mailto:kundservice@mmm.com)

[m](http://www.3m.se/tejp)

[www.3m.se/tejp](http://www.3m.se/tejp)

### **3M a/s Industri**

Hannemanns Allé 53

2300 København S

Tlf.: 43 48 01 00

Fax.: 43 20 15 65

E-mail:

[dkindustri@mmm.co](mailto:dkindustri@mmm.com)

[m](http://www.3mindustri.dk)

[www.3mindustri.dk](http://www.3mindustri.dk)

### **3M Norge AS Avd. Industri**

Hvamveien 6

2013 Skjetten

Tel: 0 63 84

Fax: 63 84 17 88

E-post:

[Kundeservice@mmm.co](mailto:Kundeservice@mmm.com)

[m](http://www.3m.no/tape)

[www.3m.no/tape](http://www.3m.no/tape)

### **Suomen 3M Oy Teollisuustuotteet**

PL 600

Keilaranta 6

02151 Espoo

Puh: 09-525 21

Fax: 09-525 2279

[www.3m.fi/teollisuus](http://www.3m.fi/teollisuus)