


3M Science.
Applied to Life.™

3M™ Wrap Film Series 1380

The Next Generation of Wrap Films



The Wrap Film
You've Been Asking for

- Conformability without cutting
- Warranted Lifting Resistance
- Impressive Film Appearance
- Optimized Initial Tack
- 25 'on-trend' colours

11 NEW colours

3M™ Wrap Film Series 1380 The Next Generation of Wrap Films

The main characteristic of this evolutionary product is its outstanding conformability which allows application on the most severe recessed areas of a vehicle without the need for any cuts.

Lifting resistance of 3M Wrap Film Series 1380 is backed by 3M™ MCS™ Warranty, providing peace of mind to wrappers for all vehicle applications.

3M Wrap Film Series 1380 comes with the 3M™ Controltac™ film patented technology which allows easy positioning and repositioning on the surface of vehicles during application.

It also integrates 3M™ Comply™ adhesive non visible air release system that provides an even and smooth surface appearance after application while helping prevent air bubbles.

Conformability without cutting

3D warranted conformability that eliminates the need for cutting and reduces risk of future cracking



Warranted Lifting Resistance

3M™ Wrap Film Series 1380 stays in place. This is warranted by 3M!



3M™ MCS™ Warranty



Commercial Solutions

Hermeslaan 7
1831 Diegem
Belgium

www.3M.eu/graphicsolutions

3M, Comply and Controltac are trademarks of 3M.
Please recycle. Printed in Germany
© 3M 2017. All rights reserved.

Impressive Film Appearance


3M Non-Visible Air Release Channels result in a very uniform final appearance on the vehicle.



Optimized Initial Tack

New adhesive system associated with 3M™ Controltac™ film technology and 3M™ Comply™ adhesive non visible air release channels provides very low initial tack, allowing easy repositioning.

This makes application easier and more efficient when an installer is working alone.



For more details please see our product information at www.3M.eu/graphicsolutions or contact your 3M distributor.