

3M™ Thinsulate™ Insulation (Type G/KL)


3M™ Thinsulate™ Insulation (Types G and KL) is a workhorse insulation—warm, durable, versatile, yet lightweight. These insulations help trap and hold body heat, while still allowing moisture to escape. The lofty profile enables versatile garment design, with extra warmth and durability.

- Holds up in harsh conditions
- Versatile cleaning options, including industrial wash (some weights)
- Thermally bonded fiber matrix for durability

“My gloves with Thinsulate are great for a car guy who might have to wrench in the cold, but needs to have some sense of touch. They are super useful in any garage or cold environment.”

-BILL S. | MINNESOTA

Consumer received free product.
Actual consumer not shown in photo.



TECHNOLOGY		ORIGINAL		FOOTWEAR	
Warm (60g or less)		Warm (Up to 60g)		Warm (Up to 300g)	
PX40 FX70 FX100	XT-S40	U40	M60	BQ400 B100 B200	
Warmer (60g-140g)		Warmer (60g-140g)		Warmer (300g-600g)	
XT-S80 XT-S80 XT-S100	FR120 J60 J80 J100	U70 U100	M80 M100 M150	BZ200 BZ400 BZ500 BQ600	B400
Warmest (140g and above)		Warmest (140g-250g)		Warmest (600g-1000g)	
XT-S150	FR150 FR200 J150 J200 J250	C200 C250 C300 U150 U200	M200 G100 G120 G150 G200		B600
Fill Power Warmth (650-800)		Fill Power Warmth (650-800)		Fill Power Warmth (650-800)	

TYPE G/KL
G60, G80, G100, G120, G150, G200,
KL100, KL150, KL200, KL250



IMPORTANT NOTICE

WARRANTY, LIMITED REMEDY AND DISCLAIMER: 3M warrants that 3M™ Thinsulate™ Insulation that is stored, maintained and used in accordance with 3M's written instructions will meet the applicable 3M product specifications. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If any Thinsulate insulation does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

LIMITATION OF LIABILITY: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract or strict liability.

PRODUCT USE: Because of the variety of factors that can affect the use and performance of Thinsulate insulation, user is solely responsible for evaluating the product and determining whether it is fit for a particular purpose and suitable for user's method of application. 3M may change the product, specification and availability of the product as improvements are made; therefore, user should contact 3M for latest information before specifying the product.

All Thinsulate insulation rolls are made within strict dimensional tolerance specifications. However, length and/or width dimensions may shift, shrink, or otherwise change up to a maximum of ±4% during handling or shipment. Please allow 24 hours after vacuum pack is removed.



Home Care Division

3M Center, Building 223-4NE-13
St. Paul, MN 55144-1000

651-575-6694
thinsulate.com

3M and Thinsulate are trademarks of 3M, used under license in Canada.

Please recycle. Printed in U.S.A.
© 3M 2015. All rights reserved.
70-0717-1081-1