




ODOR RESISTANT

**3M**  
THINSULATE™  
Insulation

## 3M™ Thinsulate™ Odor Resistant Insulation

3M™ Thinsulate™ Odor Resistant Insulation with X-STATIC® fibers is an advanced textile fiber that combines insulation and precious metal technology for warmth and odor resistance. With its natural antimicrobial properties, a layer of pure silver is used on the X-STATIC® fibers to inhibit the growth of odor-causing bacteria in the insulation. This mid-loft insulation helps keep outerwear, sportswear, and workwear cozy and fresh.

- Warmth with odor resistance that is safe and hypoallergenic



“My Thinsulate lined jacket traps my body heat in without making me sweat. Once I get moving on the jobsite, I'm warm all day.”

-MICK T. | CALIFORNIA

Consumer received free product.  
Actual consumer not shown in photo.



## TECHNOLOGY

		ORIGINAL		FOOTWEAR	
Warm (90g or less)	FX40 FX70 FX100				
	XT-S40	U40	M60	B0400	B100 B200
Warmer (90g - 140g)	XT-S80 XT-S80 XT-S100				
		U70 U100	M80 M100 M150	B2200 B2400 B2500 B0400	B400
Warmest (140g and above)	XT-S150				
		C200 C250 C300	M200		B600



### Home Care Division

3M Center, Building 223-4NE-13  
St. Paul, MN 55144-1000  
651-575-6694

thinsulate.com

**3M and Thinsulate are trademarks of 3M, used under license in Canada.**

X-STATIC® is a registered trademark of Noble Fiber Technologies, LLC.

Please recycle. Printed in U.S.A.  
© 3M 2015. All rights reserved.  
70-0777-0898-9

### IMPORTANT NOTICE

**WARRANTY, LIMITED REMEDY AND DISCLAIMER:** 3M warrants that 3M™ Thinsulate™ Insulation that is stored, maintained and used in accordance with 3M's written instructions will meet the applicable 3M product specifications. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If any Thinsulate Insulation does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**LIMITATION OF LIABILITY:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract or strict liability.

**PRODUCT USE:** Because of the variety of factors that can affect the use and performance of Thinsulate Insulation, user is solely responsible for evaluating the product and determining whether it is fit for a particular purpose and suitable for user's method of application. 3M may change the product, specification and availability of the product as improvements are made; therefore, user should contact 3M for latest information before specifying the product.

All Thinsulate Insulation rolls are made within strict dimensional tolerance specifications. However, length and/or width dimensions may shift, shrink, or otherwise change up to a maximum of ±4% during handling or shipment. Please allow 24 hours after vacuum pack is removed.



**ODOR RESISTANT**  
XT-S40, XT-S60, XT-S80,  
XT-S100, XT-S150