




Duct Tape for All-Around Maintenance

MRO
Essentials



The one tape to readily seal, mask, bundle, hold, patch, reinforce, repair, and more

3M™ Duct Tape 3900 is an all-around performer for maintenance jobs throughout a facility. Features include:

- Natural rubber adhesive grips on contact to many surfaces
- Waterproof polycoated cloth backing resists wear, abrasion, moisture and weathering for reliable performance in tough conditions
- Conforms to contours for a tight seal
- Tears easily straight across and down without curling

- Surface can be written on

Typical applications:

- Bundling
- Reinforcing
- Patching
- Sealing
- Splicing
- Holding
- Wrapping
- Capping pipe and conduit
- Masking
- Packaging
- Hanging poly drapes
- Moisture proofing
- Marking and labeling
- Color coding
- Taping insulation



3M™ Duct Tape 3900

Product/ Color	UPC # 051131-	Size	Tape Thickness	Adhesion to Steel oz./in. (N/100 mm)	Tensile Strength lbs./in. (N/100 mm)	Temperature Use °F (°C)	Backing	Adhesive Type	Packaging
ASTM Test Method:			D-3652	D-3330	D-3759				
3900/Silver	06976-3	48mm width x 54.8m long (2" x 60 yds.)	7.7 mil (0.19mm)	67 (73)	21 (368)	Up to 200°F (93°C)	Polyethylene coated cloth scrim	Natural rubber	24 per case
3900/Black	49833-6	48mm width x 54.8m long (2" x 60 yds.)	7.7 mil (0.19mm)	67 (73)	21 (368)	Up to 200°F (93°C)	Polyethylene coated cloth scrim	Natural rubber	24 per case
3900/Olive	49831-2	48mm width x 54.8m long (2" x 60 yds.)	7.7 mil (0.19mm)	67 (73)	21 (368)	Up to 200°F (93°C)	Polyethylene coated cloth scrim	Natural rubber	24 per case
3900/Red	49830-5	48mm width x 54.8m long (2" x 60 yds.)	7.7 mil (0.19mm)	67 (73)	21 (368)	Up to 200°F (93°C)	Polyethylene coated cloth scrim	Natural rubber	24 per case
3900/White	49829-9	48mm width x 54.8m long (2" x 60 yds.)	7.7 mil (0.19mm)	67 (73)	21 (368)	Up to 200°F (93°C)	Polyethylene coated cloth scrim	Natural rubber	24 per case
3900/Yellow	49828-2	48mm width x 54.8m long (2" x 60 yds.)	7.7 mil (0.19mm)	67 (73)	21 (368)	Up to 200°F (93°C)	Polyethylene coated cloth scrim	Natural rubber	24 per case
3900/Blue	49832-9	48mm width x 54.8m long (2" x 60 yds.)	7.7 mil (0.19mm)	67 (73)	21 (368)	Up to 200°F (93°C)	Polyethylene coated cloth scrim	Natural rubber	24 per case

NOTE: The technical information and data provided above is a general guide only and should be considered representative or typical only and should not be used for specification purposes.

MRO Essentials— You could browse through the thousands of products at 3M to find time and work saving solutions for MRO tasks and problems. Or you could make one call to **1-800-362-3550** or go to the one site that focuses specifically on your needs. From abrasives to adhesives, masking tape to ear plugs, electrical connectors to cleaning products, simply click...

www.3M.com/industrial

Product Use: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy: Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. **3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability: Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Industrial Business

Customer Response Center
900 Bush Avenue, Building 21-1W-10
St. Paul, MN 55144-1000



Minimum 10% Post-Consumable Fiber

3M is a trademark of 3M

Printed in U.S.A.
© 3M 2004 78-6901-2106-2