

3M™ Acrylic Plus Tape WT4112

Technical Data Sheet




3M Acrylic Plus Tape WT4112 is a 1.20 mm (0.047 in) thick, black acrylic foam tape, constructed with two different adhesives, and is typically used to attach weatherstrip and/or gasket seals for automotive and industrial applications.

3M WT4112 Tape offers the following key features:

- Heat-activated adhesive on the non-liner side forms an immediate, consistent and durable bond to most EPDM formulations and TPE materials
- Excellent adhesion to a wide variety of automotive paints, including the new scratch-and mar-resistant, low surface energy, and traditional paint systems
- Combination of high initial adhesion with a stress handling core for demanding applications
- Acrylic foam core uniquely designed for excellent conformability of the seal to the substrate, delivers excellent wet-out
- Black core provides improved bond-line aesthetics
- Ability to apply tape to seal components prior to high-temperature processing such as seal coating bakes.

Product Construction



Liner Options



See the technical update [“3M™ Acrylic Foam and Acrylic Plus Tapes: Product Constructions”](#) for liner and tabbing information.

Physical Properties

WT4112	
Thickness Range	1.20mm ± 0.10 mm (0.047 inch ± 0.004 in)
Density Range	550 kg/m ³ ± 65 kg/m ³ (34 lb/ft ³ ± 4 lb/ft ³)

Performance Properties

Typical performance of 3M™ Acrylic Plus Tape WT4112 is shown below. Peel values depend on the composition and cross-section of a particular weatherstrip. These values are for reference only.



Shelf Life

Two years from date of manufacture when stored at 4°C - 38°C (40°F - 100°F) and 0-95% relative humidity (RH). The optimum storage conditions are 22°C (72°F) and 50% relative humidity.

Regulatory Information

Please refer to the product label and Safety Data Sheet (SDS) for health and safety information before using. Observe proper handling precautions as outlined in the SDS, which is available on request or at www.3M.com/msds.

The product is published as a material entry and is available for access on www.mdssystem.com. For product IMDS I.D. number, email requests to 3M-IMDSrequest@mmm.com.

Contact Information

The information provided in this technical document is intended as a guide for this product. For more information or help in selecting a 3M product for an application, please contact your 3M technical service representative or call 1-800-328-1684.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. **Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. **Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Automotive and Aerospace Solutions Division

3M Center
St. Paul, MN 55144-1000
Phone 1-800-328-1684
Web www.3M.com/autosolutions

3M is a trademark of 3M Company
Please recycle. Printed in USA.
© 3M 2019. All rights reserved.