

3M Automotive Aftermarket  
3M™ Weld Thru II 50410



# Weld Thru II

coating for spot and  
MIG welding

- Easy and consistent sprayability
- Superior coverage
- Fast drying
- Easy to weld through
- Minimal weld spatter
- Excellent corrosion protection

**3M**

# Weld Thru II

## coating for spot and MIG welding

Weld Thru II is a zinc-rich weldable primer providing superior sprayability, corrosion protection and weldability. It is easy to apply and work with and ideal for any bodyshop undertaking welding work.

Weld Thru II is highly concentrated, allowing the required coverage to be achieved quickly and easily, without runs. Panels can be spot or MIG welded within 20 minutes of application.

Weld Thru II's advanced formula minimises weld spatter, reducing the risk of operator injury, or damage to items in the working environment, and protects against nozzle blockage, avoiding product wastage.

- Advanced anti-corrosion formula provides long-lasting protection of the repaired area
- Reduced spatter minimises the danger of operator injury or damage to items nearby when welding
- Excellent sprayability provides good coverage and reduces incidence of runs.



*“Quite impressed - I've used and abused it and it still sprays well”*

*“Better than others for MIG welding due to less spatter”*

Quotes taken from field test testimonials.

Product	Part Number	Size	Cans/Units
3M™ Weld Thru II	50410	377ml aerosol can	6

# 3M

Automotive Aftermarket  
3M United Kingdom PLC,  
Tel: 016 1237 6391  
Fax: 016 1237 5911  
aadenquiries.uk@mmm.com

Automotive Aftermarket  
3M Ireland  
Tel: (01) 280 3555  
Fax: (01) 280 3509

Please recycle. Printed in UK.  
© 3M 2007. All rights reserved.  
IG07WII-001



1. Sand - P60 - P120



2. Clean/Degrease



3. Shake for 1 min



4. 25-30cm



5. 2 thin layers



6. 10-20 mins

