



3M™ Headlight Lens Restoration System | 39008

Plastic lenses can yellow with age, reducing headlight brightness, and new lenses can be expensive. The 3M™ Headlight Lens Restoration System lets you shine and restore plastic lenses, including headlights, taillights, fog and directional lights. Now you can produce professional results with the 3M™ Headlight Lens Restoration System and a household drill (1200-1600 rpm).

DIRECTIONS FOR USE:

- Detailed instructions for use available as a separate document on 3Mcarcare.com

PRODUCT FEATURES

- | | | |
|----|---|--------------------------|
| A. | Easy to use with a household drill | <input type="checkbox"/> |
| B. | Sands away the outer layer to restore clarity to headlight lenses that have become yellowed, cloudy, or hazed over time | <input type="checkbox"/> |
| C. | Refines and reduces scratches | <input type="checkbox"/> |
| D. | Polishes lenses for clarity and shine | <input type="checkbox"/> |

BENEFITS TO USERS

- | | | |
|----|--|--------------------------|
| A. | By restoring clarity to the lens, the performance of the headlight is improved and the appearance of the vehicle is enhanced | <input type="checkbox"/> |
| B. | More cost effective than paying for a professional service | <input type="checkbox"/> |
| C. | Kit includes all items necessary to perform the task except for the drill, tape and clean cloth | <input type="checkbox"/> |



For more information on 3M Car Care products, visit www.3Mcarcare.com or call (877) MMM-CARS