

3M™ Electrically Conductive Double Coated Adhesive Transfer Tape (ECATT) 7772

Product Description

3M™ Electrically Conductive Double Coated Adhesive Transfer Tape (ECATT) 7772 is an isotropically electrical conductive tape. It consists of conductive acrylic pressure sensitive adhesive loaded with Aluminum foil carrier. The result is a double-sided tape providing both high adhesion and good electrical conductivity. The Aluminum foil in 3M ECATT 7772 provides both good electrical conductivity and improved handling characteristics.

3M ECATT 7772 conducts electricity through the thickness (Z-axis) and in the plane of the adhesive (X, Y planes), it is ideal for EMI shields and EMI gasket attachment to electronic and electrical devices. It may be used with many types of foil laminate shields to provide a customized shielding solution. This tape may also be used to attach conductive fabric/foam core EMI gaskets to electronic cabinetry.

Construction

Product	3M™ Electrically Conductive Adhesive Transfer Tape 7772
Adhesive Type	Conductive acrylic based pressure sensitive adhesive
Carrier Type	Aluminum foil
Tape Thickness	2.6 mil (66 µm)
Liner Color, Type, Print	White PCK with white 3M logo
Liner Caliper	5.5 mil (140 µm)



3M™ Electrically Conductive Double Coated Adhesive Transfer Tape (ECATT) 7772

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product	3M™ Electrically Conductive Adhesive Transfer Tape 7772
Adhesion - 180 degree peel strength to stainless steel (Modified ASTM D3330 180 degree, 2 mil PET as backing)	Oz/in (N/100 mm)
- 20 minutes @ RT	46 (50)
- 24 hours @ RT	51 (55)
- 72 hours @ RT	57 (62)
Operating Temperature Ranges*:	
Long Term (days, weeks)	158°F (70°C)
Short Term (minutes, hours)	250°F (121°C)
*3M™ Electrically Conductive Adhesive Transfer Tape 7772 is not recommended for uncertain high or low temperature excursions where the electrical performance might be compromised, even if holding power is not affected. The user is responsible for the temperature performance qualification of 3M ECATT 7772 in their design.	
Electrical Conductivity	
Electrical resistance through adhesive*	< 0.15Ω/inch ²
*3M internal test method: Based upon general resistance measurements made with crossed pieces of foil/tape/foil construction using a 1.0 in. x 1.0 in. square piece of 3M ECATT 7772.	
Shelf Life of Tape in Roll Form	24 months from date of manufacture when stored in original cartons at 70°C (21°C) and 50% relative humidity.

3M™ Electrically Conductive Double Coated Adhesive Transfer Tape (ECATT) 7772

Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improves bond strength as well as electrical conductivity. Pressure must be applied to the bond line after assembly to wet the substrates with 3M™ Electrically Conductive Adhesive Transfer Tape 7772 to get good adhesion and electrical connection. Mechanical pressure (roller, metal bar) or finger pressure at 15 psi (0.10 Mpa) or greater is suggested. Heat may be applied simultaneously to improve wetting and final bond strength as well as electrical conductivity.

To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.*

***Note:** Carefully read and follow the manufacturer's precautions and directions for use when working with solvents.

Ideal tape application temperature range is 61°F to 100°F (16°C to 38°C). Tape application below 50°F (10°C) is not recommended because the adhesive will be too firm to wet the substrates, resulting in low adhesion and poor electrical conductivity. Once properly applied, low temperature holding power is generally satisfactory.

General Information

3M™ Electrically Conductive Adhesive Transfer Tape 7772 provides good adhesion to metal surfaces and provides low electrical resistance that is stable over time. The pressure sensitive nature and Aluminum foil carrier of 3M ECATT 7772 makes this product convenient to use and shows good handling properties.

Application Ideas

3M™ Electrically Conductive Adhesive Transfer Tape 7772 is ideal for attaching foil laminate EMI shields and EMI gaskets to electronic and electrical devices. These shields typically consist of either copper or aluminum foils and the gaskets typically consist of conductive fabric over a foam core. 3M ECATT 7772 may be applied in strips or die cut to specific shapes and sizes to meet the design.

3M™ Electrically Conductive Double Coated Adhesive Transfer Tape (ECATT) 7772

Certification/Recognition

MSDS: 3M has not prepared a MSDS for this product which is not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements.

RoHS: This product complies with the requirements of EU Directive 2002/95/EC and 2005/618/EC.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-251-8634. Address correspondence to: 3M Electronics Markets Materials Division, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55144-1000. Our fax number is 651-778-4244 or 1-877-369-2923. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Markets Materials Division 3M Electronics

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle. Printed in U.S.A.
© 3M 2009. All rights reserved.
60-5002-0376-9

