



# Scotch-Weld™

## Low Odor Acrylic Adhesives

DP810 • DP810 Black • DP810NS

Technical Data

October 2018

**Product Description** 3M™ Scotch-Weld™ Low Odor Acrylic Adhesives are two-part, 1:1 mix ratio, toughened structural adhesives with less odor than most acrylic adhesives. These adhesives have excellent shear and peel strength along with good impact resistance and durability. They can quickly bond to most metals, ceramics, rubbers, plastics and wood with minimal surface preparation.

- Features**
- Tough, durable bonds
  - Minimal surface prep
  - 20 minute time to handling strength
  - Bonds stainless steel
  - Low odor acrylic adhesive
  - 10 minute work life
  - 1:1 mix ratio
  - Excellent shear and peel strength

**Typical Uncured Physical Properties** **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

Property		3M™ Scotch-Weld™ Low Odor Acrylic Adhesive		
		DP810	DP810 Black	DP810NS
<b>Color</b>	<b>Base (B) Accelerator (A)</b>	Green White	Black White	Blue/Green White
<b>Lbs./gal.</b>	<b>Base (B) Accelerator (A)</b>	8.7 - 9.1 8.7 - 9.1	8.7 - 9.1 8.7 - 9.1	8.7 - 9.1 8.7 - 9.1
<b>Viscosity (cps)<sup>(1)</sup></b>	<b>Base (B) Accelerator (A)</b>	18,000 - 22,000 18,000 - 22,000	18,000 - 22,000 17,000 - 21,000	90,000 - 95,000 95,000 - 100,000
<b>Base Resin</b>	<b>Base (B) Accelerator (A)</b>	Acrylic Acrylic	Acrylic Acrylic	Acrylic Acrylic
<b>Mix Ratio</b>	<b>(Volume) (Weight)</b>	1:1 1:1	1:1 1:1	1:1 1:1
<b>Time to Handling Strength (50 psi)</b>		20 minutes	20 minutes	20 minutes
<b>Full Cure @ 73°F (23°C)</b>		8 - 24 hours	8 - 24 hours	8 - 24 hours
<b>Work Life @ 73°F (23°C)</b>		10 minutes	10 minutes	10 minutes

For footnotes, see Test Methods and Footnotes on Page 4.

# 3M™ Scotch-Weld™

## Low Odor Acrylic Adhesives

DP810 • DP810 Black • DP810NS

### Typical Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### Overlap Shear Strength (psi)<sup>(2)</sup>, tested @ 73°F (23°C)

Substrate	3M™ Scotch-Weld™ Low Odor Acrylic Adhesive		
	DP810	DP810 Black	DP810NS
Etched Aluminum	4200 CF	4200 CF	4200 CF
Abraded Aluminum	3900 CF	3750 CF	3700 CF
Bare Aluminum	3800 CF	3850 CF	4100 CF
CRS	3100 CF	3600 CF	3100 CF
Oily CRS	3450 CF	3450 CF	3500 CF
Stainless Steel	3400 CF	3500 CF	3400 CF
Green FRP	3800 CF	3000 CF	1900 CF
Acrylic	1100 SF	550 MM	700 SF
PVC	1000 SF	1000 SF	800 SF
Polycarbonate	850 MM	500 MM	500 MM
ABS	600 MM	700 MM	900 MM

#### Overlap Shear Strength (psi), tested @ temperature

Temperature	3M Scotch-Weld Low Odor Acrylic Adhesive		
	DP810	DP810 Black	DP810NS
-20°F (-29°C)	1750 MM	2000 MM	1000 AF
75°F (24°C)	3650 CF	3550 CF	3700 CF
120°F (49°C)	2000 CF	2000 CF	2350 CF
180°F (82°C)	550 CF	500 CF	1000 CF

#### T-Peel Strength (piw)<sup>(3)</sup>, tested @ 73°F (23°C)

Substrate	3M Scotch-Weld Low Odor Acrylic Adhesive		
	DP810	DP810 Black	DP810NS
Etched Aluminum	30	20	23

SF = Substrate Failure/Break  
 CF = Cohesive Failure  
 AF = Adhesive Failure  
 MM = Mixed (Mode of AF and CF)

# 3M™ Scotch-Weld™

## Low Odor Acrylic Adhesives

DP810 • DP810 Black • DP810NS

### Environmental Resistance<sup>(4)</sup>

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Overlap Shear Strength (psi), tested @ 73°F (23°C)

Condition	Time	3M™ Scotch-Weld™ Low Odor Acrylic Adhesive		
		DP810	DP810 Black	DP810NS
Control	14 Days	3900 CF	3750 CF	3700 CF
160°F (71°C)/100% RH	14 Days	1500 MM	1500 MM	1250 AF
160°F (71°C)/Soak	14 Days	1750 MM	1650 MM	1600 AF
20% Bleach	14 Days	3450 CF	3250 CF	3750 CF
IPA	14 Days	3150 CF	3050 CF	3200 CF
50% Antifreeze	14 Days	3850 CF	3900 CF	4000 CF
Gasoline	14 Days	2550 CF	2550 CF	3000 CF
Diesel Fuel	14 Days	4000 CF	3950 CF	4050 CF
Toluene	14 Days	2650 CF	2600 CF	3400 CF
MEK	14 Days	50 CF	75 CF	1000 CF
Acetone	14 Days	75 CF	50 CF	900 CF

CF = Cohesive Failure

MM = Mixed (Mode of AF and CF)

AF = Adhesive Failure

### Typical Rate of Strength Build-Up

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Overlap Shear Strength (psi), tested @ 73°F (23°C) at various times after bonding.

Condition	3M™ Scotch-Weld™ Low Odor Acrylic Adhesive		
	DP810	DP810 Black	DP810NS
10 minutes	50	30	500
20 minutes	1500	1150	1750
1 hour	2250	2200	2850
2 hours	2750	2700	3350
4 hours	2950	2900	3700
8 hours	3350	3200	3850
24 hours	3600	3550	4000

# 3M™ Scotch-Weld™

## Low Odor Acrylic Adhesives

DP810 • DP810 Black • DP810NS

---

### Test Methods and Footnotes

- 1) Viscosity obtained by Brookfield, DV-II, #7 Spindle, 20 rpm at 75°F(24°C).
- 2) Overlap Shear Test Method: overlap shear test for adhesion determined in accordance to ASTM D1002-72, sample dimensions were 1" x 4" x 1/8", with a 1/2 square inch area of overlap, bonded to themselves unless otherwise noted, allowed to cure for at least 6 hours at 75°F (24°C) before testing. Data were collected using a Sintech 5GL Mechanical Tester with a 2000# or 5000# load cell. Test rate was 0.1"/minute. Strength determined at 75°F (24°C) unless otherwise noted.
- 3) Peel tests (ASTM D1876-61T) on FPL etched, 0.032" gauge aluminum, with a .017" bondline thickness. Jaw separation rate 20"/min. All bonds were allowed to cure for at least 6 hours at 75°F (24°C) before testing.
- 4) Environmental tests were conducted by immersing bonded coupons prepared in accordance to description in footnote 2.

# 3M™ Scotch-Weld™

## Low Odor Acrylic Adhesives

DP810 • DP810 Black • DP810NS

---

### Handling/Curing Information

#### **Directions for use:**

Apply adhesive to clean, dry substrates, which are free of paint, oxide films, oils, dust, mold release agents and all other surface contaminants. See the Surface Preparation section for specific substrate preparation method.

#### **50 ml cartridge:**

Place Duo-Pak cartridge in 3M™ EPX Applicator. Remove cap. Dispense and discard a small amount of adhesive to assure even ratio and free flow. Clear orifice if necessary. Attach mixing nozzle. Apply adhesive to clean surfaces, join parts, secure until adhesive sets.

#### **200/400 ml cartridge**

While holding Duo-Pak cartridge in an upright position, remove and discard the insert from the cartridge by unscrewing plastic nut and removing metal washer. Place cartridge in a 1:1 200/400 ml EPX applicator. Dispense and discard a small amount of adhesive to ensure even ratio and free flow. Attach mixing and nozzle and secure with plastic retaining nut. Apply adhesive to clean surfaces, join parts, secure until adhesive sets.

#### **Clean-up:**

Excess adhesive can be removed with solvent such as MEK.\* Edge tack on a finished part or bond line can be removed with isopropyl alcohol.\*

**\*Note:** When using solvents, extinguish all ignition sources and follow the manufacturer's precautions and directions for use.

#### **Heat Cure:**

Full cure can be attained by raising the bondline temperature to 120°F (49°C) for 30 minutes or to 150°F (66°C) for 10 minutes.

# 3M™ Scotch-Weld™

## Low Odor Acrylic Adhesives

DP810 • DP810 Black • DP810NS

---

### Surface Preparation

3M™ Scotch-Weld™ Low Odor Acrylic Adhesives can bond oily metal, plastic and other substrates with very little surface preparation. However, for the most consistent results and environmental resistance, all substrates should be clean, dry and free of paint, oxide films, dust, mold release agents and all other surface contaminants. The amount of surface preparation directly depends on the bond strength and environmental resistance desired by the user.

The following cleaning methods are suggested for common surfaces.

### Steel and Aluminum

- 1) Wipe free of dust with oil-free solvent such as acetone or isopropyl alcohol.
- 2) Sandblast or abrade using clean fine grit abrasives (180 grit or finer).
- 3) Wipe again with solvent to remove loose particles.
- 4) If a primer is used, it should be applied within 4 hours after surface preparation (or see instructions pertinent to a specific primer).

**Note:** Aluminum may also be acid etched. Follow the manufacturer's precautions and directions for this procedure.

### Plastic/Rubber

- 1) Wipe with isopropyl alcohol.\*
- 2) Abrade using fine grit abrasives (180 grit or finer).
- 3) Remove residue by wiping again with isopropyl alcohol.\*

**\*Note:** When using solvents, extinguish all ignition sources and follow the manufacturer's precautions and directions for use.

# 3M™ Scotch-Weld™

## Low Odor Acrylic Adhesives

DP810 • DP810 Black • DP810NS

---

<b>Storage</b>	For maximum shelf life, store Duo-Pak cartridges and bulk containers at 32°F (0°C) to 40°F (4°C). Do not freeze.
<b>Shelf Life</b>	When stored at the recommended temperatures in the original unopened containers, this product has a shelf life of 18 months from date of manufacture.
<b>Precautionary Information</b>	Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.
<b>Technical Information</b>	The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.
<b>Product Selection and Use</b>	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.
<b>Warranty, Limited Remedy, and Disclaimer</b>	Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
<b>Limitation of Liability</b>	Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

---



### Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
www.3M.com/structuraladhesives

3M and Scotch-Weld are trademarks of  
3M Company.  
©3M 2011