3M Self-Extinguishing Hot Melt Adhesive 3748 VO

	3M TM Hot Melt Adhesive 3748 VO is a tough, flexible, thermoplastic hot melt, 100% solids adhesive which exhibits good peel adhesion and thermal shock properties along with higher heat resistance. It features excellent electrical properties which make it ideal for use on printed wiring board and other electronic bonding applications.		
	Hot Melt Adhesive 3748 VO is self-extinguishi addition to electronic applications, it is also user bonding and sealing applications where a self-er required.	ful in many general industrial	
	 Excellent Adhesion Good Electrical Properties Non Corrosive to Metal 		
reatures	•		
Features Typical Physical Properties	•		
Typical Physical	Non Corrosive to Metal Note: The following technical information and da		
Typical Physical	Non Corrosive to Metal Note: The following technical information and da or typical only and should not be used for space.	specification purposes.	
Typical Physical	Non Corrosive to Metal Note: The following technical information and da or typical only and should not be used for s Base Resin:	Polyolefin	
Typical Physical	 Non Corrosive to Metal Note: The following technical information and da or typical only and should not be used for space Base Resin: Color: 	Polyolefin Light Yellow	
Typical Physical	 Non Corrosive to Metal Note: The following technical information and da or typical only and should not be used for specific Gravity: 	Polyolefin Light Yellow 1.09	
Typical Physical	 Non Corrosive to Metal Note: The following technical information and da or typical only and should not be used for sy Base Resin: Color: Specific Gravity: Ball and Ring Softening Point: Viscosity: @ 356°F (180°C) @ 392°F (200°C) 	Polyolefin Light Yellow 1.09 305°F (152°C) 8,500 cps 5,000 cps	

3M[™] Self-Extinguishing Hot Melt Adhesive 3748 VO

Typical Performance Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.			
	Two Pound Dead Load Heat Resistance (3M TM C 3093) ⁽¹⁾	175°F (79°C)		
	Overlap Shear Strength @ 70°F (21°C) (3M TM C 3096) ⁽²⁾ FR-4 to FR-4 Fir to Fir Polypropylene to Polypropylene Polyethylene to Polyethylene	215 psi 275 psi 250 psi 220 psi		
	180° Peel Adhesion (3M TM C 3168) ⁽¹⁾ Wire Mesh to FR-4 to PP to PE to Fir	38 piw 35 piw 27 piw 26 piw		
	Weight Loss by TMA (In Air) Temperature of weight loss at 5°C/min	1% @ 459°F (237°C) 5% @ 621°F (327°C) 10% @ 673°F (356°C)		
	Thermal Coefficient of Expansion by TMA Over -100 to -40°C temperature range Over -20 to 25°C temperature range	-34.0 x 10 ⁻⁶ units/units/°C 154.5 x 10 ⁻⁶ units/units/°C		
	Thermal Conductivity (@ 41°C [107°F] on .020" samples) BTU-ft./ft ² -hr °F Cal./sec cm - °C Watt/m - °C J/cm - sec - °C	1.11 x 10 ⁻¹ 4.58 x 10 ⁻⁴ 1.92 x 10 ⁻¹ 1.92 x 10 ⁻³		
	Thermal Shock Resistance Potted Washer Olyphant test (3M TM C3167) + 100°C (air) to -40°C (liquid)	Passes 5 cycles w/o cracking		

- (1) 1" x 4" Douglas Fir specimens are bonded with hot melt adhesive using a 1" overlap shear configuration. Bonds are then conditioned for 24 hours at 70°F (22°C), 50% relative humidity before testing. Bonds are subjected to 2 lbs. per square inch load at 100°F (49°C) for 30 minutes. Temperature of the bond line is raised every 30 minutes until failure. Heat resistance recorded is the last temperature prior to bond failure.
- (2) 1" x 4" Douglas Fir specimens are bonded with hot melt adhesive using a 1" overlap and 13 mil wire spacer to set bond line thickness. Bonds are then conditioned for 24 hours at 70°F (22°C), 50% relative humidity before testing. Bonds are pulled in shear at a separation bond speed of 2 inch a minute recording strength at failure.
- (3) Test involves bonding .020" wire mesh (galvanized window screen type) to substrate using hot melt adhesive. Wire mesh is encapsulated with adhesive. After conditioning, bond is tested by 180° peel back method using Instron at 10 inches per minute peel speed.

3M[™] Self-Extinguishing Hot Melt Adhesive 3748 VO

Typical Electrical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

	100 Hz	1 kHz	10 kHz	100 kHz	1 MHz	100 MHz
Dielectric Constant (ASTM D 150)	2.3	2.3	2.3	2.3	2.3	2.3
Dissipation Factor (ASTM D 150)	.002	.001	.001	.001	.001	.001
Dielectric Strength (ASTM D 149)		1400	volts/mil	(11 mil sai	mple)	
Volume Resistivity (ASTM D 257)			6.0 x 10 ¹	⁷ ohm-cm		
Surface Resistivity (ASTM D 257)	4.5 x 10 ¹⁷ ohm/sq.					

Typical Corrosion Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Per ASTM D 3482 (35°C/96% RH/45 v.d.c/15 days)	Pass – No electrolytic corrosion.
Per TM C 708* (45°C/96% RH/250 v.d.c/5 days)	Pass – No electrolytic corrosion. Very minor surface oxidation of test wire.
Per Mil S-46163 (10 days/50% RH/23°C)	Pass – No aluminum, brass or steel corrosion or discoloration.

*Test involves placing two #36 AWG (.005") oxygen free bare copper wires on clean 1" x 4" glass slides in fixed position 1/4" apart. Adhesive is coated over the wires and over the area between the wires in a uniform manner and cured/set. The test specimen is then subjected to 45°C / 96% relative humidity / 250 volts d.c. for 5 days. The aged specimen is then visually examined for corrosion/attack of the copper surface

Typical Solvent Resistance

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

	1 Hour	30 Days
Acetone	A	В
Isopropyl Alcohol	A	В
Freon [®] TF	В	С
Freon [®] TMC	В	С
1, 1, 1 - trichloroethylene	В	С
RMA Flux	A	В

Key: A = No attack

B = Slight Surface Attack/Softness

C = Severe Attack/Breakup

3M[™] Self-Extinguishing Hot Melt Adhesive 3748 VO

Storage	Store below 120°F (49°C).
Shelf Life	When stored at the recommended conditions, this product has a shelf life of 2 years from the date of manufacture.
Precautionary Information	Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.
Product Use	All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.
Warranty and Limited Remedy	Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.
Limitation of Liability	Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.
	This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.

ЗМ

Industrial Business Industrial Adhesives and Tapes Division

3M Center, Building 21-1W-10, 900 Bush Avenue St. Paul, MN 55144-1000 800-362-3550 • 877-369-2923 (fax) www.3M.com/Adhesives



3M is a trademark of 3M. Freon is a registered trademark of E.I. DuPont de Nemours Co. Printed in U.S.A. ©3M 2015 78-6900-9915-1 (8/06)