3M[™] Nitrile High Performance Rubber & Gasket Adhesive 847 • 847H

Technical Data			May, 2019			
Features	 3M[™] Nitrile High Performance Rubber & Gasket Adhesives 847 and 847H provide strong flexible bonds. 					
	 Rubber & gasket adhesive 847 is a medium viscosity grade adhesive for many brush or flow applications. 					
	• Rubber & gasket adhesive 847 meets the requirements of Mil-C-4003.					
	• Rubber & gasket adhesive 847H is a high viscosity grade adhesive for many brush or flow applications requiring gap filling or reduced soak-in.					
	• Quick drying.					
	• Excellent resistance to many fuels and oils.					
	• Bond leather, nitrile rubber, most plastics, and gasketing materials to a variety of substrates.					
	• May be heat cured to obtain improved physical properties.					
	May be heat cured to obtain im Note: The following technical infor typical only and should not b	rmation and data should be	considered representative of			
Fypical Physical Properties	Note: The following technical infor	rmation and data should be be used for specification pur 3M™ Nitrile High Pe	considered representative o			
	Note: The following technical infor	rmation and data should be be used for specification pur 3M™ Nitrile High Pe	considered representative of poses. erformance Rubber &			
	Note: The following technical infor	rmation and data should be be used for specification pur 3M™ Nitrile High Pe Gasket A	considered representative or poses. erformance Rubber & Adhesive 847H 35,000-90,000 cps.			
	Note: The following technical infortypical only and should not be viscosity (approx.):	rmation and data should be oe used for specification pur 3M™ Nitrile High Pe Gasket / 847 1500-3200 cps.	considered representative o poses. erformance Rubber & Adhesive 847H			
	Note: The following technical infor typical only and should not b Viscosity (approx.): Brookfield RVF @ 80°F (27°C)	rmation and data should be be used for specification pur 3M™ Nitrile High Pe Gasket / 847 1500-3200 cps. (#3 sp @ 20 rpm)	considered representative o poses. erformance Rubber & Adhesive 847H 35,000-90,000 cps. (#6 sp @ 4 rpm)			
	Note: The following technical infor typical only and should not b Viscosity (approx.): Brookfield RVF @ 80°F (27°C) Solids Content (by wt.):	rmation and data should be oe used for specification pur 3M™ Nitrile High Pe Gasket / 847 1500-3200 cps. (#3 sp @ 20 rpm) 33-39%	considered representative o poses. erformance Rubber & Adhesive 847H 35,000-90,000 cps. (#6 sp @ 4 rpm) 46-55%			
	Note: The following technical infortypical only and should not be sho	rmation and data should be oe used for specification pur 3M™ Nitrile High Pe Gasket / 847 1500-3200 cps. (#3 sp @ 20 rpm) 33-39% Nitrile Rubber	considered representative o poses. erformance Rubber & Adhesive 847H 35,000-90,000 cps. (#6 sp @ 4 rpm) 46-55% Nitrile Rubber			
	Note: The following technical infortypical only and should not be sho	rmation and data should be be used for specification pury 3M™ Nitrile High Pe Gasket / 847 1500-3200 cps. (#3 sp @ 20 rpm) 33-39% Nitrile Rubber Dark Brown	considered representative or poses. erformance Rubber & Adhesive 847H 35,000-90,000 cps. (#6 sp @ 4 rpm) 46-55% Nitrile Rubber Dark Brown			
	Note: The following technical infortypical only and should not be sho	rmation and data should be be used for specification pury 3M [™] Nitrile High Pe Gasket / 847 1500-3200 cps. (#3 sp @ 20 rpm) 33-39% Nitrile Rubber Dark Brown 7.4-7.8 lbs/gal	considered representative of poses. erformance Rubber & Adhesive 847H 35,000-90,000 cps. (#6 sp @ 4 rpm) 46-55% Nitrile Rubber Dark Brown 7.5-7.9 lbs/gal			

3M[™] Nitrile High Performance Rubber & Gasket Adhesive 847 • 847H

Handling/Application Information	Directions for Use:					
	 Surface Preparation: Remove all dust, dirt, oil, grease, wax, loose paint, etc. Wiping with a solvent such as methyl ethyl ketone (MEK) or 3M[™] Citrus Base Cleaner will aid in preparing the surface for bonding.* 					
	2. Application Temperature: For best results the temperature of the adhesive and surfaces to be bonded should be at least 65°F (18°C).					
	3. Application: Stir well before using					
	Porous Surface(s): Brush, flow or spray a thin, even coat of adhesive to one or both surfaces. Coating both surfaces is preferred since it gives greater strength and permits longer open time before bonding. Very absorbent materials may require more than one coat. Bond while adhesive is still wet or aggressively tacky. Join surfaces with firm pressure.					
	Non-Porous Surfaces: Brush, flow or spray a thin, even coat of adhesive to both surfaces. Allow adhesive to dry until tacky. Join surfaces with firm pressure.					
	4. Drying Time: Drying time depends on temperature, humidity, air movement, and porosity of the materials bonded. Greater immediate strength may be obtained by heat or solvent reactivation. See Reactivation below.					
	5. Reactivation: To solvent reactivate, coat both surfaces with adhesive. Allow to dry tack-free. Lightly wipe one surface with a solvent such as methyl ethyl ketone (MEK).* Complete bond within 30 seconds.					
	To heat activate, coat both surfaces with adhesive. Allow adhesive to dry completely. Reactivate by heating one or both surfaces to a minimum of 180°F (82°C). Assemble immediately (while hot), using firm pressure to ensure contact.					
	6. Curing: 3M [™] Nitrile High Performance Rubber & Gasket Adhesives 847 and 847H may be heat cured to obtain improved physical properties. Cure assembled parts at time and temperature listed using 100 psi pressure on the bond line.					
	Temperature of Bondline 200°F (93°C) 240°F (115°C) 280°F (138°C) 320°F (160°C) 360°F (182°C) 400°F (204°C)	Time for Minimum Cure 120 minutes 40 minutes 12 minutes 8 minutes 5 minutes 2 minutes				
	7. Cleanup: Excess adhesive may be removed with a solvent such as methyl ethyl ketone (MEK) or acetone, preferably while adhesive is still wet.*					

*When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

3M[™] Nitrile High Performance Rubber & Gasket Adhesive 847 • 847H

Application Equipment Suggestions	 Note: Appropriate application equipment can enhance adhesive performance. We suggest the following application equipment for the user's evaluation in light of the user's particular purpose and method of application. 1. Pumping: 3MTM Nitrile High Performance Rubber & Gasket Adhesives 847 and 847H 5 Gallon Pail Dispensing System: Pump – 4:1 double acting ball type check pump, 4 cu. in./cycle 3 in. air motor. Pail cover required to reduce solvent loss. 55 Gallon Drum Dispensing System: Pump – 4:1 ratio double acting ball type check pump, 4 cu. in./cycle 3 in. air motor. Pump – 4:1 ratio double acting ball type check pump, 4 cu. in./cycle 3 in. air motor, bung style pump. Accessories: Hose – nylon lined, 500 psi working pressure minimum. Spray: Rubber & Gasket Adhesive 847 Production Type Spray Equipment 					
	Spray Applicator	Air Cap	Fluid Tip	Air Pressure	Approximate Air Requirement*	Fluid Flow**
	DeVilbiss JGA or MSA	777	FX	50 psi	14 ¹ /2 CFM	3 fl. oz./min.
	Binks No. 95 or 2001	63PB	63BSS	40 psi	121/2 CFM	1-2 fl. oz./min.
	 Airless Spray: This adhesive is not recommended for airless spraying. *2 H.P. Compressor for intermittent use. 3 H.P. Compressor for continuous use. **To Measure Fluid Flow: Pressurize fluid source only; pull trigger; flow material into measuring device for 60 seconds; increase or decrease fluid source pressure to obtain desired fluid flow. All material hoses should be nylon or PVA lined. 3. Brush: Typical brushes designed for oil based paints may be used. 					
Typical Adhesive Performance Characteristics	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. rubber & gasket adhesive 847 and 847H					
	Overlap Shear Strength 180° Peel Strength 1/8 in. / 1/8 in. Birch Canvas/Steel (Room temperature aged for 3 weeks)					

180° Peel Strength Canvas/Steel			Overlap Shear Strength 1/8 in. / 1/8 in. Birch (Room temperature aged for 3 weeks)		
Time @ 75°F (14°C)	Test Temp	Value (piw)	Test Temp	Value (psi)	
1 day	75°F (14°C)	13	30°F (1°C)	152	
3 days	75°F (14°C)	23.5	75°F (14°Ć)	200	
5 days	75°F (14°C)	27.5	150°F (66°C)	20	
7 days	75°F (14°C)	31	180°F (82°C)	9	
2 weeks	75°F (14°C)	35			
3 weeks	75°F (14°C)	40			
3 weeks	30°F (1°C)	20			
3 weeks	150°F (66°Ć)	16			
3 weeks	180°F (82°C)	9			

3M[™] Nitrile High Performance Rubber & Gasket Adhesive 847 • 847H

Storage	ge Store product at 60-80°F (15-27°C) for maximum storage life. Higher ten reduce normal storage life. Lower temperatures cause increased viscosity temporary nature. Rotate stock on a "first in-first out" basis.				
Shelf Life	When stored in the original unopened container, under the conditions recommended, these products have a shelf life from date of manufacture as follows:				
	3M™ Nitrile High Performance Rubber & Gasket Adhesive 847 3M™ Nitrile High Performance Rubber & Gasket Adhesive 847H	24 months 24 months			
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of su information is not guaranteed.				
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and c and performance of a 3M product in a particular application. Given the variety the use and performance of a 3M product, user is solely responsible for evalua determining whether it is fit for a particular purpose and suitable for user's met	of factors that can affect ating the 3M product and			
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product literature, 3M warrants that each 3M product meets the applicable 3M product 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIO IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY CO MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR If the 3M product does not conform to this warranty, then the sole and exclusive option, replacement of the 3M product or refund of the purchase price.	specification at the time NS, EXPRESS OR OR CONDITION OF (IMPLIED WARRANTY USAGE OF TRADE.			
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage ar whether direct, indirect, special, incidental or consequential, regardless of the including warranty, contract, negligence or strict liability.				
	This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system regis	tered to ISO 9001:2000 standards.			