

## 3M™ Dyneon™ Fluoroplastic THV 500GZ

### Product Description

3M™ Dyneon™ Fluoroplastic THV 500GZ is a fluorothermoplastic containing tetrafluoroethylene, hexafluoropropylene and vinylidene fluoride. Because of its well-balanced profile of low temperature processing, low flammability, thermal stability and melt processability, this product should preferably be used for extruded film, profiles, wire coatings, and tubes, for example in automotive fuel hoses.

### Special Features

- Excellent flexibility
- Excellent chemical resistance
- Excellent permeation resistance to fuels
- Bondable to itself and other substrates (for multi-layer constructions)
- Processing profile allows co-processing with olefinic plastics and hydrocarbon elastomers
- Low flammability
- High transparency
- Excellent UV stability
- Low refractive index

Properties	Test method	Unit	Value*
Melting Point	DIN EN ISO 12086	°C	165
Glass Transition (T <sub>g</sub> )	ASTM D 4591	°C	26
Melt Flow Index	DIN EN ISO 1133	g/10 min	10
Specific Gravity	DIN EN ISO 12086	g/cm <sup>3</sup>	2.01
Tensile at Break	DIN EN ISO 527-1	MPa	26
Elongation at Break	DIN EN ISO 527-1	%	520
Flexural Modulus	ASTM D 790	MPa	210
Limiting Oxygen Index	ASTM D 2863	%	> 75
Refractive Index	ASTM D 542	n <sub>D</sub>	1.36
UV-Vis Light Transmission (100µm film)	300 nm	%	85
	600 nm	%	93
Dielectric Constant (23°C)	ASTM D 150, @ 1MHz		4.82
	ASTM D 150, @ 9.4GHz		2.48
Dissipation Factor	ASTM D 150, @ 1MHz		0.10
	ASTM D 150, @ 9.4GHz		0.08
Dielectric Breakdown Strength	ASTM D 149	kV/mm	48

\* typical values

## 3M™ Dyneon™ Fluoroplastic THV 500GZ

### Typical Properties

3M™ Dyneon™ Fluoroplastic THV 500GZ provides a balance of low temperature processing, low flammability, thermal stability, and melt processability. This product exhibits excellent weatherability and good anti-soiling properties.

### Typical Applications

3M™ Dyneon™ Fluoroplastic THV 500GZ can be used for extruded films, tubes, profiles, and wire coating, and for applications that require flexibility, low temperature processing and good chemical resistance. Its present applications range from barrier layer in automotive hoses and seals in chemical containment to protective layers in photovoltaic backsheets.

### Processing Recommendations

The processing recommendations depend on a variety of factors and it is best advised to contact a technical service person before embarking on extrusion trials. However, one can use the following as a starting point for the extrusion of THV 500GZ.

Cooling on the feed throat of the extruder to maintain a temperature of 30 – 70 °C, Zone 1 180 °C, Zone 2 220 °C, Zone 3 260 °C, the die and other tooling around 260 °C. Typical processing temperatures for injection moulding are around 260 – 280 °C for the nozzle temperature and 50 – 100 °C for the mould. A screen pack of 1000 µm / 500 µm / 200 µm is recommended. Corrosion resistant equipment and an air exhausting system are highly recommended for safe processing.

### Storage and Handling

3M™ Dyneon™ Fluoroplastic THV 500GZ has an unlimited shelf life provided it is stored in a clean, dry place. THV 500GZ is hydrophobic, and generally does not require drying before processing unless high humidity conditions create surface moisture adsorption.

### Safety Instructions

Follow the normal precautions observed with all fluorothermoplastic materials.

Please consult the Material Safety Data Sheet and Product Label for information regarding the safe handling of the material. By following all precautions and safety measures, processing these products poses no known health risks. General handling/processing precautions include: 1) Process only in well-ventilated areas. 2) Do not smoke in areas contaminated with powder/residue from these products. 3) Avoid eye contact. 4) If skin comes into contact with these products during handling, wash with soap and water afterwards. 5) Avoid contact with hot fluoropolymer.

Potential hazards, including release of toxic vapours, can arise if processing occurs under excessively high temperature conditions. Vapour extractor units should be installed above processing equipment. When cleaning processing equipment, do not burn off any of this product with a naked flame or in a furnace.

### Delivery Form

3M™ Dyneon THV 500GZ is delivered in pellet form.

Packaging size is:

- 50 kg cardboard box, containing two PE-bags each with 25 kg content
- 200 kg plastic drums
- 500 kg big bag

## 3M™ Dyneon™ Fluoroplastic THV 500GZ

### Important Notice

All information set forth herein is based on our present state of knowledge and is intended to provide general notes regarding products and their uses. It should not therefore be construed as a guarantee of specific properties of the products described or their suitability for a particular application. Because conditions of product use are outside Dyneon's control and vary widely, user must evaluate and determine whether a Dyneon product will be suitable for user's intended application before using it.

The quality of our products is warranted under our General Terms and Conditions of Sale as now are or hereafter may be in force.

Technical information, test data, and advice provided by Dyneon personnel are based on information and tests we believe are reliable and are intended for persons with knowledge and technical skills sufficient to analyze test types and conditions, and to handle and use raw polymers and related compounding ingredients.

No license under any Dyneon or third party intellectual rights is granted or implied by virtue of this information.

General recommendations on health and safety in processing, on work hygiene and on measures to be taken in the event of accident are detailed in our material safety data sheets.

You will find further notes on the safe handling of fluoropolymers in the brochure "[Guide for the safe handling of Fluoropolymers Resins](#)" (download link) by PlasticsEurope, Box 3, B-1160 Brussels, Tel. +32 (2) 676 17 32.

You can also download it with your smartphone using the QR code below.



#### Customer Service

Europe  
Phone: 00 800 396 366 27  
Fax: 00 800 396 366 39  
Italy  
Phone: 800 7 910 18  
Fax: 800 7 810 19  
USA  
Phone: +1 800 810 8499  
Fax: +1 800 635 8061

#### Technical Service Fluoroplastics

Dyneon GmbH  
3M Advanced Materials Division  
Industrieparkstraße 1  
84508 Burgkirchen  
Germany  
Phone: +49 8679 7 4709  
Fax: +49 8679 7 5037

#### Technical Service Fluoroelastomers & Polymer Processing Additives

3M Belgium N.V.  
3M Advanced Materials Division  
Canadastraat 11,  
Haven 1005  
2070 Zwijndrecht  
Belgium  
Phone: +32 3 250 7868  
Fax: +32 3 250 7905

#### Technical Service PTFE Compounds

Dyneon B.V.  
3M Advanced Materials Division  
Tunnelweg 95  
6468 EJ Kerkrade  
The Netherlands  
Phone: +31 45 567 9600  
Fax: +31 45 567 9619

We will gladly supply further contact details for our full network of global sales offices. Alternatively, find them [here](#).



Web Site: [www.dyneon.eu](http://www.dyneon.eu)

Printed in Germany  
© Dyneon 2013  
Status: Aug. 2013

3M, Dyneon and Dynamar are Trademarks of 3M Company.  
All Rights reserved. The present edition replaces all previous versions. Its content is being continuously adjusted to reflect the current level of knowledge. Please make sure and inquire if in doubt whether you have the latest edition.