

3M™ Dyneon™ Ultra High Purity PFA FLEX8515UHPZ

Product Description

3M™ Dyneon™ Ultra High Purity PFA FLEX8515UHPZ exhibits improved environmental stress crack resistance (ESCR) to stress cracking chemicals or such agents that specifically contain fluorosurfactants. In addition, the product offers ultra-low levels of extractable ions, making it suitable for critical wet chemical processes in the semiconductor industry.

Special Features

- Significantly longer life in fluorosurfactant containing fluids
- Smoother surfaces
- Improved flexibility
- Extreme stress crack resistance
- Extremely low level of extractable ions
- Improved clarity
- Service temperature range up to 240 °C

Properties	Test method	Unit	Value*
Specific Gravity	DIN EN ISO 12086	g/cm ³	2.15
Melting Point	DIN EN ISO 12086	°C	290
Melt Flow Index (372 °C/5 kg)	DIN EN ISO 1133	g/10 min	15
Limiting Oxygen Index (LOI)	ASTM D2863	%	> 95
Hardness Shore D	ASTM D2240/ISO 868	-	60
Tensile Strength at Break (23 °C)	ASTM D638	MPa	35
Elongation at Break (23 °C)	DIN EN ISO 527-1	%	330
Flexural Modulus	DIN EN ISO 527-1	MPa	600

* typical values

3M™ Dyneon™ Ultra High Purity PFA FLEX8515UHPZ

Typical Properties

In comparison to the T and UHP grades 3M Dyneon Fluoroplastic PFA Flex Ultra High Purity grades are a new series of ultra-high purity fluorothermoplastics with improved flex life / environmental stress crack resistance (ESCR) to stress cracking chemicals or such agents that specifically contain fluorosurfactants. In addition, these products offer ultra-low levels of extractable ions, making them suitable for critical wet chemical processes in the semiconductor industry.

Typical Applications

Generally, 3M Dyneon Fluoroplastic PFA Flex Ultra High Purity grades can be compression-moulded, transfer-moulded, extruded or injection-moulded. 3M Dyneon Ultra High Purity PFA FLEX8515UHPZ, with a Melt-Flow-Index (372 °C/5 kg) of 15 g/10 min, is a material with a low viscosity and is used in high shear processes like wire and cable extrusion and injection moulding, especially when improved flex life / ESCR needs to be combined with ultra-low levels of extractable ions, making it suitable for critical wet chemical processes in the semiconductor industry.

Processing Recommendations

3M Dyneon Ultra High Purity PFA Flex8515UHPZ can be processed according to the known processing methods for thermoplastic polymers. All machine parts coming into contact with the melt or fumes of 3M Dyneon Ultra High Purity PFA Flex8515UHPZ should be made from highly corrosion resistant materials – usually high-nickel alloys such as Inconel® 625, Haynes® 242, Hastelloy® C, and Reiloy®. Off-gases and decomposition products during processing shall be managed via an appropriate exhaust fume management system, especially at the extruder die. For safe processing of Dyneon PFA please also check safety instructions below.

Typical processing temperatures for 3M Dyneon Fluoroplastic PFA Flex Ultra High Purity grades lie between 340 °C and 370 °C. The medium melt viscosity makes 3M Dyneon Ultra High Purity PFA Flex8515UHPZ a standard material for injection moulding and wire & cable extrusion.

Injection moulding: Detailed processing information with typical processing parameters and processing equipment recommendations please find in Dyneon's "Injection Moulding Guide".

Wire and cable extrusion: For the wire & cable extrusion a 25 - 30 mm D extruder with a cylinder L/D ratio of 20 - 30:1 is required. The cylinder should have 3 - 4 heating zones that are independent from each other. High line speeds can be obtained with a high draw down ratio of up to 150:1. The draw down balance should be maintained between 0.95 – 1.05.

Hastelloy®, Haynes® 242, and Reiloy® are registered trademarks of Haynes International.
Inconel® is a registered trademark of Special Metals Corporation.

Storage and Handling

3M™ Dyneon™ Ultra High Purity PFA FLEX8515UHPZ can be stored for a relatively long period of time provided it is stored in a clean, dry place. 3M™ Dyneon™ Ultra High Purity PFA FLEX8515UHPZ is hydrophobic and generally does not require drying before processing unless high humidity conditions create surface moisture absorption (opened containers should be tightly resealed to prevent dust contamination from static charge accumulation and moisture ingress).

Safety Instructions

Follow the normal precautions observed with all fluorothermoplastic materials.

Please consult the Material Safety Data Sheet and Product Label for information regarding the safe handling of the material. By following all precautions and safety measures, processing these products poses no known health risks. General handling/processing precautions include: 1) Process only in well-ventilated areas. 2) Do not smoke in areas contaminated with powder/residue from these products. 3) Avoid eye contact. 4) If skin comes into contact with these products during handling, wash with soap and water afterwards. 5) Avoid contact with hot fluoropolymer.

Potential hazards, including release of toxic vapours, can arise if processing occurs under excessively high temperature conditions. Vapour extractor units should be installed above processing equipment. When cleaning processing equipment, do not burn off any of this product with a naked flame or in a furnace.

Delivery Form

3M™ Dyneon Ultra High Purity PFA FLEX8515UHPZ is delivered in pellet form.

Packaging sizes are:

- 50 kg cardboard box, containing two PE-bags with 25 kg content each

3M™ Dyneon™ Ultra High Purity PFA FLEX8515UHPZ

Important Notice

All information set forth herein is based on our present state of knowledge and is intended to provide general notes regarding products and their uses. It should not therefore be construed as a guarantee of specific properties of the products described or their suitability for a particular application. Because conditions of product use are outside Dyneon's control and vary widely, user must evaluate and determine whether a Dyneon product will be suitable for user's intended application before using it.

The quality of our products is warranted under our General Terms and Conditions of Sale as now are or hereafter may be in force.

Technical information, test data, and advice provided by Dyneon personnel are based on information and tests we believe are reliable and are intended for persons with knowledge and technical skills sufficient to analyze test types and conditions, and to handle and use raw polymers and related compounding ingredients.

No license under any Dyneon or third party intellectual rights is granted or implied by virtue of this information.

General recommendations on health and safety in processing, on work hygiene and on measures to be taken in the event of accident are detailed in our material safety data sheets.

You will find further notes on the safe handling of fluoropolymers in the brochure "[Guide for the safe handling of Fluoropolymers Resins](#)" (download link) by PlasticsEurope, Box 3, B-1160 Brussels, Tel. +32 (2) 676 17 32.

You can also download it with your smartphone using the QR code below.



Customer Service

Europe
Phone: 00 800 396 366 27
Fax: 00 800 396 366 39
Italy
Phone: 800 7 910 18
Fax: 800 7 810 19
USA
Phone: +1 800 810 8499
Fax: +1 800 635 8061

Technical Service Fluoroplastics

Dyneon GmbH
3M Advanced Materials Division
Industrieparkstraße 1
84508 Burgkirchen
Germany
Phone: +49 8679 7 4709
Fax: +49 8679 7 5037

Technical Service Fluoroelastomers & Polymer Processing Additives

3M Belgium N.V.
3M Advanced Materials Division
Canadastraat 11,
Haven 1005
2070 Zwijndrecht
Belgium
Phone: +32 3 250 7868
Fax: +32 3 250 7905

Technical Service PTFE Compounds

Dyneon B.V.
3M Advanced Materials Division
Tunnelweg 95
6468 EJ Kerkrade
The Netherlands
Phone: +31 45 567 9600
Fax: +31 45 567 9619

We will gladly supply further contact details for our full network of global sales offices. Alternatively, find them [here](#).



Web Site: www.dyneon.eu

Printed in Germany
© Dyneon 2013
Status: Jul. 2013

3M, Dyneon and Dynamar are Trademarks of 3M Company.
All Rights reserved. The present edition replaces all previous versions. Its content is being continuously adjusted to reflect the current level of knowledge. Please make sure and inquire if in doubt whether you have the latest edition.