

## 3M™ Dyneon™ TFM™ Modified PTFE Compound TFM 6221

### Product Description

3M™ Dyneon™ TFM™ Modified PTFE Compound TFM 6221 is a free-flowing compound based on modified suspension PTFE of the 2<sup>nd</sup> generation containing conductive, FDA\*-approved fillers for compression and automatic moulding.

### Special Features

- Increased thermal dimensional stability
- Increased surface hardness
- Improved deformation under load
- Reduced friction & wear
- Good chemical stability
- High limiting oxygen index (LOI)
- Low friction behaviour
- Very good mechanical properties
- Exceptional temperature resistance
- FDA-approved filler

Product Properties	Test method	Unit	Value
Bulk Density	ASTM D 4894-07	g/l	650
Shrinkage	ASTM D 4894-07	%	4.6
Specific Gravity	ASTM D 4745-06	g/cm <sup>3</sup>	2.150
Volume Resistivity	IEC 60093	Ω*cm	<10 <sup>4</sup>

Mechanical Properties	Test method	Unit	Value
Tensile Strength	ASTM D 4745-06	MPa	30.0
Elongation at Break	ASTM D 4745-06	%	385
Hardness	DIN 53505	Shore 'D'	66

\* U. S. Food and Drug Administration

## 3M™ Dyneon™ TFM™ Modified PTFE Compound TFM 6221

### Typical Properties

This Modified PTFE compound moulding powder is the preferred grade for shaped parts requiring very good free-flowing, good mechanical properties, a denser polymer structure, significantly lower deformation under load and improved weldability.

### Typical Applications

3M™ Dyneon™ TFM™ Modified PTFE Compound TFM 6221 can be used in seal and gasket applications in the chemical processing (CPI) and automotive industries.

### Processing Recommendations

If transport or storage temperatures are too high the material can agglomerate in its container. In such cases, it is advisable to store the material for 48 hours at below 23 °C and then to sieve it (mesh size 4 mm) before filling the mould. To achieve optimum properties, compression moulding should be carried out within a temperature range of 23 °C to 26 °C and a humidity range of 45 % to 55 % and a pressure of 35 MPa. The maximum sintering temperature should be 365 °C.

### Storage and Handling

3M™ Dyneon™ TFM™ Modified PTFE Compound TFM 6221 can be stored for a relatively long period of time. It should preferably be stored in a clean, dry place at a temperature of less than 30 °C. Before processing it is advisable to store the material in the sealed boxes for 24 hours in the production area. This is particularly important when ambient temperature is low; in such cases the material should be conditioned for up to 72 hours in the production area in the recommended temperature range.

### Safety Instructions

Follow the normal precautions observed with all fluorothermoplastic materials.

Please consult the Material Safety Data Sheet and Product Label for information regarding the safe handling of the material. By following all precautions and safety measures, processing these products poses no known health risks. General handling/processing precautions include: 1) Process only in well-ventilated areas. 2) Do not smoke in areas contaminated with powder/residue from these products. 3) Avoid eye contact. 4) If skin comes into contact with these products during handling, wash with soap and water afterwards. 5) Avoid contact with hot fluoropolymer.

Potential hazards, including release of toxic vapours, can arise if processing occurs under excessively high temperature conditions. Vapour extractor units should be installed above processing equipment. When cleaning processing equipment, do not burn off any of this product with a naked flame or in a furnace.

### Delivery Form

3M™ Dyneon™ TFM™ Modified PTFE Compound TFM 6221 is supplied in moisture- and dust-tight plastic boxes.

Packaging sizes are:

- Capacity per box: 25 kg
- Order quantity per pallet: 300 kg

## 3M™ Dyneon™ TFM™ Modified PTFE Compound TFM 6221

### Important Notice

All information set forth herein is based on our present state of knowledge and is intended to provide general notes regarding products and their uses. It should not therefore be construed as a guarantee of specific properties of the products described or their suitability for a particular application. Because conditions of product use are outside Dyneon's control and vary widely, user must evaluate and determine whether a Dyneon product will be suitable for user's intended application before using it.

The quality of our products is warranted under our General Terms and Conditions of Sale as now are or hereafter may be in force.

Technical information, test data, and advice provided by Dyneon personnel are based on information and tests we believe are reliable and are intended for persons with knowledge and technical skills sufficient to analyze test types and conditions, and to handle and use raw polymers and related compounding ingredients.

No license under any Dyneon or third party intellectual rights is granted or implied by virtue of this information.

General recommendations on health and safety in processing, on work hygiene and on measures to be taken in the event of accident are detailed in our material safety data sheets.

You will find further notes on the safe handling of fluoropolymers in the brochure "[Guide for the safe handling of Fluoropolymers Resins](#)" (download link) by PlasticsEurope, Box 3, B-1160 Brussels, Tel. +32 (2) 676 17 32.

You can also download it with your smartphone using the QR code below.



#### Customer Service

Europe  
Phone: 00 800 396 366 27  
Fax: 00 800 396 366 39  
Italy  
Phone: 800 7 910 18  
Fax: 800 7 810 19  
USA  
Phone: +1 800 810 8499  
Fax: +1 800 635 8061

#### Technical Service Fluoroplastics

Dyneon GmbH  
3M Advanced Materials Division  
Industrieparkstraße 1  
84508 Burgkirchen  
Germany  
Phone: +49 8679 7 4709  
Fax: +49 8679 7 5037

#### Technical Service Fluoroelastomers & Polymer Processing Additives

3M Belgium N.V.  
3M Advanced Materials Division  
Canadastraat 11  
Haven 1005  
2070 Zwijndrecht  
Belgium  
Phone: +32 3 250 7868  
Fax: +32 3 250 7905

#### Technical Service PTFE Compounds

Dyneon B.V.  
3M Advanced Materials Division  
Tunnelweg 95  
6468 EJ Kerkrade  
The Netherlands  
Phone: +31 45 567 9600  
Fax: +31 45 567 9619

We will gladly supply further contact details for our full network of global sales offices. Alternatively, find them [here](#).



Web Site: [www.dyneon.eu](http://www.dyneon.eu)

Printed in Germany  
© Dyneon 2013  
Status: Oct. 2013

3M, Dyneon and Dynamar are Trademarks of 3M Company.  
All Rights reserved. The present edition replaces all previous versions. Its content is being continuously adjusted to reflect the current level of knowledge. Please make sure and inquire if in doubt whether you have the latest edition.