







Leave conventional abrasives in the past and do more than you thought possible with Cubitron™ II Fibre Discs.

- Disc 982C: Your complete mild steel solution
- Disc 987C: Your complete stainless steel solution


Cubitron Il Fibre Discs are made with revolutionary 3M precision-shaped ceramic grain technology, engineered with ultra-sharp, fast-cutting points that wear evenly, run cool and optimise mineral breakdown to maximise disc life.

Get More


- More productivity
- More throughput
- · More disc life
- More comfort
- · More grinding speed

For Less

Projected Grinding Force*



*Projected due to standardisation of the data based on actual internal grinding force tests. 1 Lbs = $0.45\,\text{Kgs}$



Triangular-shaped grain (right image) is electrostatically oriented to form sharp peaks, each acting like individual cutting tools that slice through metal, wear evenly and provide super-long life and consistency at any grinding pressure.

Unique + Grades for revolutionary products

Multiple grading systems have been created as mineral technology evolves, and Cubitron™ II abrasives are no exception.

Engineered triangular shapes can't be boxed into the screens used for grading today. Precision-shaped grain is bigger, better, faster and longer lasting than ANSI-graded abrasives thanks to the clean cut provided by the sharp minerals that cut through metal.

You can count on 3M to meet or beat your current grinding process time.

Target applications

- Weld removal
- Mill scale removal
- Removing pits and surface imperfections
- Beveling
- Edge chamfering




Cubitron™ II Fibre Disc 982C: Works harder so you don't have to


You have too much to do
to settle for a disc that
can't keep up. With the
982C, you get a disc
that cuts faster, lasts
longer and requires
less grinding pressure
than conventional
abrasives. In fact, 982C
works harder so you don't
have to. Without increasing


the grinding force you currently use, 3M guarantees you'll get longer life and more parts with a Cubitron $^{\sim}$ II fibre disc.

982C Customer test results

Application	Material	Previous Disc Type	982C Results	Operator Comments
Weld (edge & flat)	Mild Steel	Ceramic, Grade 36	2 - 3 times more life experienced by ALL operators	"Much better cut"
Flame cut	Mild Steel	Ceramic, Grade 24	2 times life	"A lot better; cuts faster longer"
Weld prep (flat)	Mild Steel	Ceramic, Grade 36	2 times life	"Don't have to push as hard; tougher material"
Weld removal	Mild Steel	Ceramic, Grade 36	4 hot welds/ disc	"Cuts into a hot weld where other discs won't"
Edge work	Mild Steel	Ceramic, Grade 36	2 - 3 times life	"Got life from disc without having to push hard at the end"







Cubitron™ II Fibre Disc 987C: The coolest way to increase productivity

If you work with heat-sensitive materials like stainless steel, you'll appreciate the way the 987C disc digs in and cuts faster, lasts longer and requires less grinding pressure than conventional abrasives.

When you've doubled your standard part count with a single disc, you'll be tempted to


get a new disc. But keep grinding. Some customers have seen up to 5 times the life.


Try 987C for yourself and we'll guarantee you'll see improvement over your existing fibre disc.


987C Customer Test Results

Application	Material	Previous Disc Type	Grade Replaced	Results
Plate grinding	High Nickel Alloy	Ceramic	24	2.5 times life
Plate grinding	Stainless Steel	Ceramic	24	2 times life
Removing Mill Scale	Mild Steel	Ceramic	36	2-4 times life
Gate removal	718 Inconel	Ceramic blend	24	2-3 times life
Weld removal	Stainless Steel	Aluminium oxide	36	5 times life

Actual results will vary based on end user manufacturing processes.











Speed Up The Entire Grinding Process.

Start with CubitronTM II fibre discs for heavy stock removal and use the same tool/accessories to quickly change over to Scotch-BriteTM Light Grinding and Blending Discs for your finishing needs. Designed to easily blend and refine a grade 36 scratch, LGB discs can prepare surfaces for finishing (where greater than a 3 mil / 75 micron paint thickness is being applied) and eliminate the final DA sanding step.

Grinding 3M™ Cubitron™ II Fibre Disc 982C - Mild Steel Diameter (mm) Ordering Code Max Operating Speed Grade 60440230021 36+ 60440230039 13,300rpm 100 60+ 100 **80**+ 60440230047 36+ 60440229288 115 60+ 60440229353 13,300rpm 100 80+ 60440229395 60440229270 36+ 60440229361 12,000rpm 100 125 60+ 80+ 60440229403 36+ 60440229262 60440229379 8,600rpm 100 180 60 +60440229411 80+


3M™ Cubitron™ II Fibre Disc 987C - Stainless Steel				
Diameter (mm)	Grade	Ordering Code	Max Operating Speed	Carton QTY
	36+	60440230054		
100	60+	60440230062	13,300rpm	100
	80+	60440230070		
	36+	60440229312		
115	60+	60440229577	13,300rpm	100
	80+	60440229619		
	36+	60440229304		
125	60+	60440229585	12,000rpm	100
	80+	60440229627		
	36+	60440229296		
180	60+	60440229593	8,600rpm	100
	80+	60440229635		



Accessories

3M™ Back-Up Pads					
Diameter (mm)	Face Type	Ordering Code Max Operating Speed		Carton QTY	
100	Flat	XC003410104	15,300rpm	5	
115	Ribbed	XC003410039	13,300rpm	10	
125	Ribbed	XC003410047	12,200rpm	10	
180	Ribbed	DC272921404	8,500 rpm	5	

Everything you need for your toughest grinding applications on mild or stainless steel in grades 36+, 60+ and 80+. Join the Cubitron II abrasive revolution and take your productivity to the next level.



Product Use: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty: Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M makes no other warranties, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose or any implied warranty arising out of a course of dealing, custom or usage of trade. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application.

Limitation of Liability: Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



"The annual R&D 100 Award identifies and celebrates the top technologies, products and processes of the year. The Awards, widely recognised as the "Oscars of Innovation", identifies and celebrates the top high technology products of the year." (www.rdmag.com)



3M Australia Pty Limited Abrasive Systems Division Bldg A, 1 Rivett Road

North Ryde NSW 2113 Australia Ph: 136 136

Fax: (02) 9495 9247 Email: auindmkt@mmm.com www.3M.com.au

3M New Zealand Ltd **Abrasive Systems Division**

94 Apollo Drive, Albany Auckland, New Zealand Phone: 0800 362 886 Fax: 0800 362880

Email: 3mnzib2@mmm.com www.3M.com/abrasives

3M and Cubitron are trademarks of 3M.

Please recycle. Printed in Australia © 3M 2011. All rights reserved.