

Closures — Pre-cut Strips & Rolls Selection Guide

Flexform Closures

Product Number	Color	Width	Minimum Length	Maximum Length	Wires per Strip	Strips per Sheet
9823D	Blue	1 1/16" (17.5mm)	5" (13cm)	48" (122cm)	8	5
9779W	White	0.34" (8.7mm)	N/A	350 yds. (320m)	2	roll
9779B	Blue	0.34" (8.7mm)	N/A	350 yds. (320m)	2	roll

#9823D, Flexform Wire Tape Strips, Blue

Each part consists of eight wires, encased in blue plastic, with a pressure sensitive adhesive applied to the smooth side. The strips are supplied as sheeted parts (5 strips/sheet) on clear polyester release liner.

#9779W, Flexform Tape Rolls, White

Each part consists of two wires, encased in white plastic, with a pressure sensitive adhesive applied to the smooth side. The tape is wound with the paper liner wound on the inside of the roll.

#9779B, Flexform Tape Rolls, Blue

Each part consists of two wires, encased in blue plastic, with a pressure sensitive adhesive applied to the smooth side. The tape is wound with the paper liner wound on the inside of the roll.

Flexfoam Closures/Clips

Product Number	Color	Width	Total Clip Length	Adhesive Length	Clips per Sheet	Minimum Order Quantity
9818B	White	1 1/32" (8.7mm)	5.25" (133.4mm)	2.5" (63.5mm)	10	25M
9818D	Tan	1 1/32" (8.7mm)	4.5" (115mm)	2.0" (50mm)	10	30M
9818G	Tan	1 1/32" (8.7mm)	5.25" (133.4mm)	2.5" (63.5mm)	10	30M
9818J	White	1 1/32" (8.7mm)	6.4" (162mm)	3.0" (76mm)	10	30M

* For custom colors and lengths, contact your 3M Account Representative.

#9818X, Flexfoam Closures/Clips

The individual part consists of soft polyethylene foam laminated to four wires encased in polyolefin. A portion of the foam laminate is coated with a pressure sensitive adhesive protected by a release liner. The product is supplied as multiple clips or closures as a sheet.