

Communication Markets Division

# 3M™ Pedestal Cabinets 4220VB, 4220VC & 4220VDS Series

The 3M™ Pedestal Cabinets 4220VB, 4220VC & 4220VDS Series are 3M's low-count cross-connect cabinets, available in up to 900-pair. These cabinets are modular in design and can be used in pad-, stake- handhole, or pole-mount applications. All 3M Pedestal Cabinets are almond color and meet specific requirements for North American content.

The Pedestal Cabinets are equipped with the 3M™ Quick Connect System (QCS) 2810 Blocks for tool-less, quick, consistent field termination. The wiring harness includes 3M™ MS<sup>2</sup>™ Splicing Modules or 3M™ 710 Splicing Modules for easy splicing and maintenance. The 4220VDS cabinet can also mount the 3M™ Fiber Frame.



3M™ Pedestal Cabinet 4220VDS with 3M™ Fiber Frame



3M™ Pedestal Cabinet 4220VB, 300 pair



3M™ Pedestal Cabinet 4220VC, 600 pair

Feature	Benefit
Small footprint and pair count	Ideal for multi-tenant or rural applications
Heavy-gauge steel construction/powder-coat paint finish	Reliability and durability consistent with 3M Cross Connect Cabinets
Cabinets designed to be pad, pole, handhole or stake mounted	Flexibility, less inventory required
Standard 3M block frames	Efficient design and costs
Standard pad/stake mount cabinets feature an open base design that can be upgraded with available bread pan and/or discreet cable ports	Easy to adapt to individual job requirements
3M™ Pedestal Cabinet 4220VDS Series can accommodate either copper or 3M™ Fiber Frames	Utilize standard cabinet to deploy fiber networks

### 3M™ Pedestal Cabinets 4220VB, 4220VC & 4220VDS Series Ordering Information

Product Number	Product Description	3M ID	Min. Order
4220VB-QCSHC/300-100/20GBM-A	100 pair 3M™ Cross Connect Cabinet 4220VB with 3M™ MS² Module (20 in. tail)	80-6113-9689-8	1 each
4220VB-QCSHC/300-200/20GBM-A	200 pair 3M Cross Connect Cabinet 4220VB with 3M MS² Module (20 in. tail)	80-6113-9690-6	1 each
4220VC-QCSHC/600-300/20GBM-A	300 pair 3M™ Cross Connect Cabinet 4220VC with 3M MS² Module (20 in. tail)	80-6113-9691-4	1 each
4220VC-QCSHC/600-400/20GBM-A	400 pair 3M Cross Connect Cabinet 4220VC with 3M MS² Module (20 in. tail)	80-6113-9692-2	1 each
4220VC-QCSHC/600-500/20GBM-A	500 pair 3M Cross Connect Cabinet 4220VC with 3M MS² Module (20 in. tail)	80-6113-9693-0	1 each
4220VC-QCSHC/600-600/20GBM-A	600 pair 3M Cross Connect Cabinet 4220VC with 3M MS² Module (20 in. tail)	80-6113-9694-8	1 each
4220VCP-QCSHC/600-100/20GBM-BPORT-A	100 pair 3M™ Cross Connect Pole Mount Cabinet 4220VCP with 3M MS² Module (20 in. tail)	80-6113-9705-2	1 each
4220VCP-QCSHC/600-200/20GBM-BPORT-A	200 pair 3M Cross Connect Pole Mount Cabinet 4220VCP with 3M MS² Module (20 in. tail)	80-6113-9706-0	1 each
4220VCP-QCSHC/600-300/20GBM-BPORT-A	300 pair 3M Cross Connect Pole Mount Cabinet 4220VCP with 3M MS² Module (20 in. tail)	80-6113-9707-8	1 each
4220VCP-QCSHC/600-400/20GBM-BPORT-A	400 pair 3M Cross Connect Pole Mount Cabinet 4220VCP with 3M MS² Module (20 in. tail)	80-6113-9708-6	1 each
4220VDSPM/H-QCS/900-900/20GBM-A	900 pair 3M™ Cross Connect Pole Mount Cabinet 4220VDSPM with 3M MS² Module (20 in. tail)	80-6114-8855-4	1 each
4220VDSPM/H-QCS/900-900/20T-A	900 pair 3M Cross Connect Pole Mount Cabinet 4220VDSPM with 3M™ 710 Module (20 in. tail)	80-6114-8856-2	1 each
4220VDSPM-MBK	Pole Mount Bracket Kit for 3M Cross Connect Cabinets 4220VDSPM	80-6116-2137-8	1 each
4220VDS-QCSHC/900-000/A	3M™ Cross Connect Cabinet 4220VDS (Empty)	80-6114-8553-5	1 each
4220VDS-QCSHC/900-600/20GBM-A	600 pair (900 pair capacity) 3M Cross Connect Cabinet 4220VDS with 3M MS² Module (20 in. tail)	80-6113-8434-0	1 each
4220VDS-QCSHC/900-600/20T-A	600 pair (900 pair capacity) 3M Cross Connect Cabinet 4220VDS with 3M 710 Module (20 in. tail)	80-6113-8436-5	1 each
4220VDS-QCSHC/900-600/48GBM-A	600 pair (900 pair capacity) 3M Cross Connect Cabinet 4220VDS with 3M MS² Module (48 in. tail)	80-6114-8552-7	1 each
4220VDS-QCSHC/900-600/48T-A	600 pair (900 pair capacity) 3M Cross Connect Cabinet 4220VDS with 3M 710 Module (48 in. tail)	80-6114-8551-9	1 each
4220VDS-QCSHC/900-900/20GBM-A	900 pair 3M Cross Connect Cabinet 4220VDS with 3M MS² Module (20 in. tail)	80-6113-8378-9	1 each
4220VDS-QCSHC/900-900/20T-A	900 pair 3M Cross Connect Cabinet 4220VDS with 3M 710 Module (20 in. tail)	80-6113-8435-7	1 each

## Accessories Ordering Information

Product Number	Product Description	3M ID	Min. Order
4220VCP-PMK-BTM	Bottom pole-mount entry kit for 600-pair cabinet	80-6113-9712-8	1 each
4220VCP-PMK-TOP	Top pole-mount entry kit for 600-pair cabinet	80-6113-9711-0	1 each
4297FPE	Flexible Port Entry Kit (bread pan)	80-6109-3667-8	1 each
4430F	Sealing tape foam kit	80-6101-1020-9	1 kit
4411-A	Size A 96 GM pedestal base sealant	80-6101-0166-1	16 each
4097-F	2 5/8 inches split port gland kit	80-6109-3680-1	1 kit
4056S	Stake mount kit	80-6100-3164-5	1 each

3M is a trademark of 3M Company.

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.



### Communication Markets Division

6801 River Place Blvd.  
Austin, TX 78726-9000 USA

Phone 1-800-426-8688  
Fax 1-800-626-0329  
Web 3M.com/Telecom

Please recycle. Printed in USA © 3M 2018.  
All rights reserved. 80-6113-8675-8