

Communication Markets Division

# 3M™ Pre-terminated Fiber Cable Assemblies - Trunk & Horizontal

3M offers pre-terminated cable assemblies to ease and speed installation for indoor singlemode fiber networking applications. The product range includes assemblies designed especially for use with the 3M™ Passive Optical LAN System (POLS) of products. This includes simplex, duplex and multi-fiber cables. Low smoke zero halogen, plenum rated and armored plenum rated assemblies are available.

Multi-fiber trunk cable assemblies are designed with straight-through fiber polarity to work with 3M multi-fiber MPO fan-out modules and our 19" 1RU MPO fan-out shelves. This provides easy configuration and plug-and-play connectivity for backbone network configurations. Horizontal cable assemblies utilize SC/APC terminations to interconnect 3M POLS splitter outputs to workstation outlets. All singlemode assemblies are designed with bend insensitive fiber and low loss connectors so network design and high performance installations are made easy.



3M™ Singlemode Simplex Horizontal Bulk Cable



3M™ Singlemode Multi-fiber MPO to SC/APC Trunk Cable Assembly

Product overview	
<b>Application</b>	Indoor singlemode fiber networking applications that require simplex, duplex, 8 or 12-fiber connectivity between equipment and telecom rooms or for fiber-to-the-enclosure zone configurations.
<b>Trunk assemblies</b>	8 fiber and 12 fiber, terminated on both ends with female MPO or terminated on one end with female MPO and the other end with furcated legs to SC/APC connectors.
<b>Cabled fiber flame ratings</b>	Flame retardant - Plenum or Aluminum Armored Plenum (OFNP/OFCP/FT-6) Zero halogen – Low Smoke, Zero Halogen (LSZH)
<b>Fiber specifications</b>	9/125 μm OS2, G.657.A2/B2 7.5 mm bend radius fibers
<b>RoHS</b>	RoHS compliant.*
<b>Horizontal assemblies</b>	Simplex and duplex fiber cable terminated at one or both ends with SC/APC connectors.

\*RoHS 2011/65/EU means that the product or part does not contain any of the substances in excess of the maximum concentration values ("MCVs") in EU RoHS Directive 2011/65/EU. The MCVs are by weight in homogeneous materials. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

# 3M™ Singlemode Multi-fiber Trunk Cable Assemblies

3M Singlemode Multi-fiber Trunk Cable Assemblies are factory prepared with pulling eye and protected connector covering, providing easy and quick installation. Multi-fiber trunk assemblies are used typically in office installations as backbone interconnects or distribution cabling between floors or telecom rooms or to a zone area telecom enclosure.

Features	Benefits
Fully tested, labeled and documented	Consistent quality, no need for cable preparation
Factory installed pulling eyes	Ready for quick installation on arrival
Produced to industry specifications	Ensures system compatibility and interoperability
Trunk cables designed with OS2, G.657.A2 Bend Insensitive Fiber	Bend insensitive fiber provides low macro bending loss
G.652.D backward compatible	Allows interworking with existing fiber plant
Straight-through fiber polarity	Easy configuration for simplex fiber networking

## Attenuation and Return Loss Specifications

Products - Trunk & Horizontal Assemblies	Insertion Loss Maximum (dB)	Insertion Loss Typical (dB)	Return Loss Minimum (dB)
<b>Connectors</b>			
MPO	0.7 dB	0.3 dB	55
SC/APC	0.4 dB	0.15 dB	60

General Cable Assembly Specifications	
Cable ratings/listings	OFNP, OFCP, CSA FT-6 or LSZH
Pulling grip performance	8- and 12-fiber trunks can be pulled up to 50 lbf using the pulling grip

## Mechanical Specifications

Products	Cable Outer Diameter	Pulling Grip Outer Diameter	Cable Weight (lbs/1000 ft)
<b>Non-armored Multi-fiber Trunk Cable Assemblies</b>			
8 fiber cable assemblies	0.15" (2.9 mm)	1.0"	5.8
12 fiber cable assemblies	0.15" (2.9 mm)	1.0"	5.8
<b>Armored Multi-fiber Trunk Cable Assemblies</b>			
8 fiber cable assemblies	0.55" (13.9 mm)	2.0"	105
12 fiber cable assemblies	0.55" (13.9 mm)	2.0"	105
<b>Simplex and Duplex Horizontal Assemblies</b>			
Simplex	0.08" (2.0 mm)	n/a	2.7
Duplex	0.08" (2.0 mm)	n/a	5.4

# 3M™ Multi-fiber Trunk Cable Assemblies – MPO to MPO



- 8 or 12 fiber MPO to MPO
- Low Smoke Zero Halogen, Plenum or Armored Plenum fire rating
- Provide quick and easy installation between floors or from floor distributor to the horizontal zone area distribution

## 3M™ Multi-fiber Trunk Cable Assemblies MPO to MPO Ordering Information


Product Number	Description	3M ID	Packaging	Min. Order
<b>8 Fiber Assemblies Plenum</b>				
DMEME-SPYL015	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 15 m (50 ft)	80-6114-8406-6	1/pkg	1 pkg
DMEME-SPYL030	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 30 m (100 ft)	80-6114-8407-4	1/pkg	1 pkg
DMEME-SPYL046	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 46 m (150 ft)	80-6114-8408-2	1/pkg	1 pkg
DMEME-SPYL061	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 61 m (200 ft)	80-6114-8409-0	1/pkg	1 pkg
DMEME-SPYL076	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 76 m (250 ft)	80-6114-8410-8	1/pkg	1 pkg
DMEME-SPYL091	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 91 m (300 ft)	80-6114-8411-6	1/pkg	1 pkg
<b>8 Fiber Assemblies Plenum Armored</b>				
DMEME-SAYL015	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 15 m (50 ft)	80-6114-8412-4	1/pkg	1 pkg
DMEME-SAYL030	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 30 m (100 ft)	80-6114-8413-2	1/pkg	1 pkg
DMEME-SAYL046	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 46 m (150 ft)	80-6114-8414-0	1/pkg	1 pkg
DMEME-SAYL061	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 61 m (200 ft)	80-6114-8415-7	1/pkg	1 pkg
DMEME-SAYL076	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 76 m (205 ft)	80-6114-8416-5	1/pkg	1 pkg
DMEME-SAYL091	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 91 m (300 ft)	80-6114-8417-3	1/pkg	1 pkg
<b>8 Fiber Assemblies Low Smoke Zero Halogen</b>				
DMEME-ELYL015	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, yellow, LSZH, 15 m (50 ft)	80-6114-9716-7	1/pkg	1 pkg
DMEME-ELYL046	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, yellow, LSZH, 46 m (150 ft)	80-6114-9717-5	1/pkg	1 pkg
DMEME-ELYL091	Trunk cable, MPO to MPO unpinned, 8-fiber SM A2/B2, yellow, LSZH, 91 m (300 ft)	80-6114-9718-3	1/pkg	1 pkg

### 3M™ Multi-fiber Trunk Cable Assemblies MPO to MPO Ordering Information (continued)

Product Number	Description	3M ID	Packaging	Min. Order
<b>12 Fiber Assemblies Plenum</b>				
DMPMP-RPYL015	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 15 m (50 ft)	80-6114-8382-9	1/pkg	1 pkg
DMPMP-RPYL030	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 30 m (100 ft)	80-6114-8383-7	1/pkg	1 pkg
DMPMP-RPYL046	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 46 m (150 ft)	80-6114-8384-5	1/pkg	1 pkg
DMPMP-RPYL061	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 61 m (200 ft)	80-6114-8385-2	1/pkg	1 pkg
DMPMP-RPYL076	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 76 m (250 ft)	80-6114-8386-0	1/pkg	1 pkg
DMPMP-RPYL091	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 91 m (300 ft)	80-6114-8387-8	1/pkg	1 pkg
<b>12 Fiber Assemblies Plenum Armored</b>				
DMPMP-RAYL015	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 15 m (50 ft)	80-6114-8388-6	1/pkg	1 pkg
DMPMP-RAYL030	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 30 m (100 ft)	80-6114-8389-4	1/pkg	1 pkg
DMPMP-RAYL046	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 46 m (150 ft)	80-6114-8390-2	1/pkg	1 pkg
DMPMP-RAYL061	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 61 m (200 ft)	80-6114-8391-0	1/pkg	1 pkg
DMPMP-RAYL076	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 76 m (250 ft)	80-6114-8392-8	1/pkg	1 pkg
DMPMP-RAYL091	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 91 m (300 ft)	80-6114-8393-6	1/pkg	1 pkg
<b>12 Fiber Assemblies Low Smoke Zero Halogen</b>				
DMPMP-RLYL015	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 15 m (50 ft)	80-6114-9713-4	1/pkg	1 pkg
DMPMP-RLYL030	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 30 m (100 ft)	80-6114-8765-5	1/pkg	1 pkg
DMPMP-RLYL046	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 150 m (150 ft)	80-6114-9714-2	1/pkg	1 pkg
DMPMP-RLYL061	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 61 m (200 ft)	80-6114-8766-3	1/pkg	1 pkg
DMPMP-RLYL076	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 76 m (250 ft)	80-6114-8767-1	1/pkg	1 pkg
DMPMP-RLYL091	Trunk cable, MPO to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 91 m (300 ft)	80-6114-9715-9	1/pkg	1 pkg

# 3M™ Multi-fiber Trunk Cable Assemblies – MPO to SC/APC

- 8 or 12 fiber MPO to SC/APC
- Plenum or Armored Plenum fire rating
- Provide quick and easy installation between floors or from floor distributor to the horizontal zone area distribution



## 3M™ Multi-fiber Trunk Cable Assemblies MPO to SC/APC Ordering Information

Product Number	Description	3M ID	Packaging	Min. Order
<b>8 Fiber Assemblies Plenum</b>				
DEPME-SPYL015	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 15 m (50 ft)	80-6114-8418-1	1/pkg	1 pkg
DEPME-SPYL030	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 30 m (100 ft)	80-6114-8419-9	1/pkg	1 pkg
DEPME-SPYL046	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 46 m (150 ft)	80-6114-8420-7	1/pkg	1 pkg
DEPME-SPYL061	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 61 m (200 ft)	80-6114-8421-5	1/pkg	1 pkg
DEPME-SPYL076	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 76 m (250 ft)	80-6114-8422-3	1/pkg	1 pkg
DEPME-SPYL091	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum, yellow, 91 m (300 ft)	80-6114-8423-1	1/pkg	1 pkg
DEPME-SPYL183	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum round, yellow, 183 m (600 ft)	80-6114-8145-0	1/pkg	1 pkg
DEPME-SPYL274	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum round, yellow, 274 m (898 ft)	80-6114-8146-8	1/pkg	1 pkg
DEPME-SPYL365	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum round, yellow, 365 m (1197 ft)	80-6114-8147-6	1/pkg	1 pkg
<b>8 Fiber Assemblies Plenum Armored</b>				
DEPME-SAYL015	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 15 m (50 ft)	80-6114-8424-9	1/pkg	1 pkg
DEPME-SAYL030	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 30 m (100 ft)	80-6114-8425-6	1/pkg	1 pkg
DEPME-SAYL046	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 46 m (150 ft)	80-6114-8426-4	1/pkg	1 pkg
DEPME-SAYL061	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 61 m (200 ft)	80-6114-8427-2	1/pkg	1 pkg
DEPME-SAYL076	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 76 m (250 ft)	80-6114-8428-0	1/pkg	1 pkg
DEPME-SAYL091	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 91 m (300 ft)	80-6114-8429-8	1/pkg	1 pkg
DEPME-SAYL183	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 183 m (600 ft)	80-6114-8148-4	1/pkg	1 pkg
DEPME-SAYL274	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 274 m (898 ft)	80-6114-8149-2	1/pkg	1 pkg
DEPME-SAYL365	Trunk cable, SC/APC to MPO unpinned, 8-fiber SM A2/B2, Plenum armored, yellow, 365 m (1197 ft)	80-6114-8150-0	1/pkg	1 pkg

### 3M™ Multi-fiber Trunk Cable Assemblies MPO to SC/APC Ordering Information (continued)

Product Number	Description	3M ID	Packaging	Min. Order
<b>12 Fiber Assemblies Plenum</b>				
DEPMP-RPYL015	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 15 m (50 ft)	80-6114-8394-4	1/pkg	1 pkg
DEPMP-RPYL030	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 30 m (100 ft)	80-6114-8395-1	1/pkg	1 pkg
DEPMP-RPYL046	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 46 m (150 ft)	80-6114-8396-9	1/pkg	1 pkg
DEPMP-RPYL061	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 61 m (200 ft)	80-6114-8397-7	1/pkg	1 pkg
DEPMP-RPYL076	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 76 m (250 ft)	80-6114-8398-5	1/pkg	1 pkg
DEPMP-RPYL091	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum, yellow, 91 m (300 ft)	80-6114-8399-3	1/pkg	1 pkg
DEPMP-RPYL183	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum round, yellow, 183 m (600 ft)	80-6114-8139-3	1/pkg	1 pkg
DEPMP-RPYL274	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum round, yellow, 274 m (898 ft)	80-6114-8140-1	1/pkg	1 pkg
DEPMP-RPYL365	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum round, yellow, 365 m (1197 ft)	80-6114-8141-9	1/pkg	1 pkg
<b>12 Fiber Assemblies Plenum Armored</b>				
DEPMP-RAYL015	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 15 m (50 ft)	80-6114-8400-9	1/pkg	1 pkg
DEPMP-RAYL030	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 30 m (100 ft)	80-6114-8401-7	1/pkg	1 pkg
DEPMP-RAYL046	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 46 m (150 ft)	80-6114-8402-5	1/pkg	1 pkg
DEPMP-RAYL061	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 61 m (200 ft)	80-6114-8403-3	1/pkg	1 pkg
DEPMP-RAYL076	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 76 m (250 ft)	80-6114-8404-1	1/pkg	1 pkg
DEPMP-RAYL091	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 91 m (300 ft)	80-6114-8405-8	1/pkg	1 pkg
DEPMP-RAYL183	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 183 m (600 ft)	80-6114-8142-7	1/pkg	1 pkg
DEPMP-RAYL274	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 274 m (898 ft)	80-6114-8143-5	1/pkg	1 pkg
DEPMP-RAYL365	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, Plenum armored, yellow, 365 m (1197 ft)	80-6114-8144-3	1/pkg	1 pkg
<b>12 Fiber Assemblies Low Smoke Zero Halogen</b>				
DEPMP-RLYL015	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 15 m (50 ft)	80-6114-8770-5	1/pkg	1 pkg
DEPMP-RLYL030	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 30 m (100 ft)	80-6114-8771-3	1/pkg	1 pkg
DEPMP-RLYL046	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 46 m (150 ft)	80-6114-8772-1	1/pkg	1 pkg
DEPMP-RLYL061	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 61 m (200 ft)	80-6114-8773-9	1/pkg	1 pkg
DEPMP-RLYL076	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 76 m (250 ft)	80-6114-8774-7	1/pkg	1 pkg
DEPMP-RLYL091	Trunk cable, SC/APC to MPO unpinned, 12-fiber SM A2/B2, yellow, LSZH, 91 m (300 ft)	80-6114-8775-4	1/pkg	1 pkg

### 3M™ Horizontal Cable Assemblies (Patch Cords) Ordering Information

Product Number	Description	3M ID	Packaging	Min. Order
<b>Simplex Round Plenum</b>				
AEPEP-CXIV003	Patch cord, SC/APC-SC/APC A2 simplex OFNP 2.0 jacket, ivory, 3 m (10 ft)	80-6114-7908-2	16/pkg	1 pkg
AEPEP-CXIV010	Patch cord, SC/APC-SC/APC A2 simplex OFNP 2.0 jacket, ivory 10 m (33 ft)	80-6114-7909-0	16/pkg	1 pkg
AEPEP-CXIV025	Patch cord, SC/APC-SC/APC A2 simplex OFNP 2.0 jacket, ivory, 25 m (82 ft)	80-6114-7910-8	8/pkg	1 pkg
AEPEP-CXIV030	Patch cord, SC/APC-SC/APC A2 simplex OFNP 2.0 jacket, ivory, 30 m (100 ft)	80-6114-7911-6	8/pkg	1 pkg
AEPEP-CXIV060	Patch cord, SC/APC-SC/APC A2 simplex OFNP 2.0 jacket, ivory, 60 m (197 ft)	80-6114-7912-4	4/pkg	1 pkg
AEPEP-CXIV075	Patch cord, SC/APC-SC/APC A2 simplex OFNP 2.0 jacket, ivory, 75 m (246 ft)	80-6114-7913-2	1/pkg	1 pkg
AEPEP-CXIV090	Patch cord, SC/APC-SC/APC A2 simplex OFNP 2.0 jacket, ivory, 90 m (295 ft)	80-6114-7914-0	1/pkg	1 pkg
AEPEP-CXIV150	Patch cord, SC/APC-SC/APC A2 simplex OFNP 2.0 jacket, ivory, 150 m (492 ft)	80-6114-7915-7	1/pkg	1 pkg
<b>Duplex Zipcord Plenum</b>				
AEPEP-CSIV003	Patch cord, SC/APC-SC/APC A2 duplex ZIP OFNP 2.0 jacket, ivory, 3 m (10 ft)	80-6114-7936-3	16/pkg	1 pkg
AEPEP-CSIV010	Patch cord, SC/APC-SC/APC A2 duplex ZIP OFNP 2.0 jacket, ivory, 10 m (33 ft)	80-6114-7937-1	16/pkg	1 pkg
AEPEP-CSIV025	Patch cord, SC/APC-SC/APC A2 duplex ZIP OFNP 2.0 jacket, ivory, 25 m (82 ft)	80-6114-7938-9	8/pkg	1 pkg
AEPEP-CSIV030	Patch cord, SC/APC-SC/APC A2 duplex ZIP OFNP 2.0 jacket, ivory, 30 m (100 ft)	80-6114-7939-7	8/pkg	1 pkg
AEPEP-CSIV060	Patch cord, SC/APC-SC/APC A2 duplex ZIP OFNP 2.0 jacket, ivory, 60 m (197 ft)	80-6114-7940-5	1/pkg	1 pkg
AEPEP-CSIV075	Patch cord, SC/APC-SC/APC A2 duplex ZIP OFNP 2.0 jacket, ivory, 75 m (246 ft)	80-6114-7941-3	1/pkg	1 pkg
AEPEP-CSIV090	Patch cord, SC/APC-SC/APC A2 duplex ZIP OFNP 2.0 jacket, ivory, 90 m (295 ft)	80-6114-7942-1	1/pkg	1 pkg
AEPEP-CSIV150	Patch cord, SC/APC-SC/APC A2 duplex ZIP OFNP 2.0 jacket, ivory, 150 m (492 ft)	80-6114-7943-9	1/pkg	1 pkg
<b>Simplex Low Smoke Zero Halogen</b>				
AEPEP-CLIV025	Patch cord, SC/APC - SC/APC A2 simplex LSZH 2.0 jacket, ivory, 25 m (82 ft)	80-6114-9719-1	8/pkg	1 pkg
AEPEP-CLIV030	Patch cord, SC/APC - SC/APC A2 simplex LSZH 2.0 jacket, ivory, 30 m (100 ft)	80-6114-9720-9	8/pkg	1 pkg
AEPEP-CLIV060	Patch cord, SC/APC - SC/APC A2 simplex LSZH 2.0 jacket, ivory, 60 m (197 ft)	80-6114-9721-7	4/pkg	1 pkg
AEPEP-CLIV075	Patch cord, SC/APC - SC/APC A2 simplex LSZH 2.0 jacket, ivory, 75 m (246 ft)	80-6114-9722-5	1/pkg	1 pkg
AEPEP-CLIV090	Patch cord, SC/APC - SC/APC A2 simplex LSZH 2.0 jacket, ivory, 90 m (295 ft)	80-6114-9723-3	1/pkg	1 pkg
AEPEP-CLIV150	Patch cord, SC/APC - SC/APC A2 simplex LSZH 2.0 jacket, ivory, 150 m (492 ft)	80-6114-9724-1	1/pkg	1 pkg

### 3M™ Horizontal Cable Assemblies (Pigtails) Ordering Information

Product Number	Description	3M ID	Packaging	Min. Order
<b>Simplex Round Plenum</b>				
AEP00-CXIV003	Pigtail, SC/APC A2/B2 simplex OFNP 2.0 jacket, ivory, 3 m (10 ft)	80-6114-7944-7	16/pkg	1 pkg
AEP00-CXIV010	Pigtail, SC/APC A2 simplex OFNP 2.0 jacket, ivory, 10 m (33 ft)	80-6114-7945-4	16/pkg	1 pkg
AEP00-CXIV025	Pigtail, SC/APC A2 simplex OFNP 2.0 jacket, ivory, 25 m (82 ft)	80-6114-7946-2	8/pkg	1 pkg
AEP00-CXIV030	Pigtail, SC/APC A2 simplex OFNP 2.0 jacket, ivory, 30 m (100 ft)	80-6114-7947-0	8/pkg	1 pkg
AEP00-CXIV060	Pigtail, SC/APC A2 simplex OFNP 2.0 jacket, ivory, 60 m (197 ft)	80-6114-7948-8	4/pkg	1 pkg
AEP00-CXIV075	Pigtail, SC/APC A2 simplex OFNP 2.0 jacket, ivory, 75 m (246 ft)	80-6114-7949-6	1/pkg	1 pkg
AEP00-CXIV090	Pigtail, SC/APC A2 simplex OFNP 2.0 jacket, ivory, 90 m (295 ft)	80-6114-7950-4	1/pkg	1 pkg
AEP00-CXIV150	Pigtail, SC/APC A2 simplex OFNP 2.0 jacket, ivory, 150 m (492 ft)	80-6114-7951-2	1/pkg	1 pkg

<b>Duplex Zipcord Plenum</b>				
AEP00-CSIV003	Pigtail, SC/APC A2/B2 duplex OFNP 2.0 jacket, ivory, 3 m (10 ft)	80-6114-7952-0	16/pkg	1 pkg
AEP00-CSIV010	Pigtail, SC/APC A2 duplex OFNP 2.0 jacket, ivory, 10 m (33 ft)	80-6114-7953-8	16/pkg	1 pkg
AEP00-CSIV025	Pigtail, SC/APC A2 duplex OFNP 2.0 jacket, ivory, 25 m (82 ft)	80-6114-7954-6	8/pkg	1 pkg
AEP00-CSIV030	Pigtail, SC/APC A2 duplex OFNP 2.0 jacket, ivory, 30 m (100 ft)	80-6114-7955-3	8/pkg	1 pkg
AEP00-CSIV060	Pigtail, SC/APC A2 duplex OFNP 2.0 jacket, ivory, 60 m (197 ft)	80-6114-7956-1	1/pkg	1 pkg
AEP00-CSIV075	Pigtail, SC/APC A2 duplex OFNP 2.0 jacket, ivory, 75 m (246 ft)	80-6114-7957-9	1/pkg	1 pkg
AEP00-CSIV090	Pigtail, SC/APC A2 duplex OFNP 2.0 jacket, ivory, 90 m (295 ft)	80-6114-7958-7	1/pkg	1 pkg
AEP00-CSIV150	Pigtail, SC/APC A2 duplex OFNP 2.0 jacket, ivory, 150 m (492 ft)	80-6114-7959-5	1/pkg	1 pkg

3M is a trademark of 3M Company.

#### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

#### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



#### Communication Markets Division

6801 River Place Blvd.  
Austin, TX 78726-9000 USA

Phone 1-800-426-8688  
Fax 1-800-626-0329  
Web 3M.com/Telecom

Please recycle. Printed in USA © 3M 2016.  
All rights reserved. 80-6116-2041-2