3M Welding and Spark Deflection Paper 05916

Technical Data Sheet

June, 2013

3M Part No.(s)	3M Part Descriptor(s)
05916	3M™ Welding and Spark Deflection Paper

Product Description 3MTM Welding and Spark Deflection Paper is a flame-retardant, repositionable, adhesive-backed paper product used to help protect vertical surfaces from damage caused by welding spatter and grinding sparks.

Features, Advantages, Benefits	Features	Advantages	Benefits
	• Flame retardant	• Protects vertical surfaces from welding spatter and grinding sparks	• Helps to prevent potential replacement due to damage from spatter and sparks
	 Repositionable 	• Easily adjusted to insure correct positioning	• Less product waste
	• Easy to install	• Cut to fit repair size	• Helps save time and reduces product waste

Typical Physical N Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Container	Plastic Bag
Base	1 roll
Density Ibs/Gallon (Appx.)	NA
Color	Brown paper with 3M printing
Flash Point - °F	NA
Viscosity (CPS) Brookfield Viscometer	NA
Solids Content (Appx.)	100%
Consistency	Solid paper
Solvent	NA
Service Temperature - °F	Normal shop conditions
Weight per Area	95 g/m²
Size of Roll	24 in. wide x 150 ft. long
Rolls per Case	2

3M[™] Welding and Spark Deflection Paper 05916

Product Uses	 Product is designed for use on vertical surfaces, such as automotive glass painted sheet metal automotive light fixtures many other vertical surfaces The product is <u>not</u> designed for installation on horizontal surfaces, such as roofs, deck lids, hoods, carpeting on floorboards. It is not designed to prevent heat transfer from sparks or spatter that are allowed to sit in one position on the paper, these will burn through. It is recommended to use 3MTM High Performance Welding Drape (PN 05919) for 		
	horizontal surfaces or any area where sparks will remain on the surface until cooled. Allowing sparks to remain on horizontal surfaces may result in burning or damage to the protected area.		
Performance Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.		
	3M AT-177 burn test (12 second flame exposure, burn length): 5.4 inches 3M AT-174 peel test: 31.9 grams piw		
Directions for Use	 Install 3M[™] Welding and Spark Deflection Paper (PN 05916) in its designated dispenser, PN 05912. 		
	2. Pull and tear off an appropriately-sized piece for the application.		
	3. Install by pressing in place on the surface to be protected. If more than one sheet will be used, install from the bottom first and then continue installing new sheets above it, overlapping by at least 1 inch. This is to insure that any seams between sheets will allow sparks to roll over easily and not get caught, which could cause a burn.		
	4. Be sure the sheets are free from wrinkles. Wrinkles can provide ledges for sparks to catch on, allowing them to burn through and damage the substrate underneath.		
	5. When the work is complete, remove the paper. Do not allow the paper to sit for more than 1 week, to be exposed to prolonged direct sunlight, or to get wet. These conditions may cause some adhesive to transfer to the substrate, and this will need to be removed with a solvent such as 3M TM General Purpose Adhesive Cleaner (PN 08984, 08986, 08987).		
	6. Reusing the paper on different substrates may work until the adhesive is no longer tacky, but for best results use each piece for 1 application and discard.		
	Please note: If 'Directions for Use' reference P.N.'s 08984, 08986, or 08987, please read. Federal and local air quality regulations may regulate or prohibit the use of surface preparation and cleanup solvents based on VOC content. Consult your local and Federal air quality regulations for information. When using solvents, use in a well ventilated area. Extinguish all sources of ignition in the work area and observe precautionary measures for handling these materials. Refer to product label and MSDS for P.N. 8984, 8986, or 8987 for detailed precautionary information.		

3M[™] Welding and Spark Deflection Paper 05916

Applications	 Product is designed for use on vertical surfaces, such as automotive glass painted sheet metal automotive light fixtures many other vertical surfaces 	
Storage and Handling	Store at room temperature. Rotate stock on a "first-in-first-out" basis. When stored at the recommended conditions in original, unopened containers, this product has a shelf life of 24 months.	
Precautionary Information	Refer to Product Label and Material Safety Data Sheet for Health and Safety Information before using this product. See Link Below.	
	http://solutions.3m.com/wps/portal/3M/en_US/MSDS/Search/?gsaAction=msdsSRA &msdsLocale=en_US	
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.	
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.	
Warranty, Limited Remedy, and Disclaimer	 Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. 	
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arisin from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.	

For Additional Health and Safety Information



Automotive Aftermarket Division

3M Center, Building 223-6N-01 St. Paul, MN 55144-1000 1-877-666-2277 (1-877-MMM-CARS) www.3MCollision.com