

Product Bulletin

Rx Limitations 8 Base Wrap Frames



V1000 Jet



ZT25 Black



Mean Street Black

Total Power (Sphere + Cylinder)

- 4.00 D to +4.00 D Total Power

Pupillary Distance (PD)

- Minimum 61 mm

Best Opportunity PALs

- In most cases the following PALs have more cut-out area for the 8 Base frames; check the specific PAL cut-out chart to be sure

Level 2: Image

Level 3: Natural

Level 3+: Comfort

Level 4: Ellipse

Why is this important?

- If you follow these guidelines your jobs will be completed faster
- Avoids jobs on hold
- Avoids having to call the worker back to select another frame
- Helps all involved to get it right the first time

Frames

- 3M V1000 8 Base Group F
- 3M Mean Street 8 Base Group F
- 3M ZT25 8 Base Group F