

3M™ MDT-A Heat Shrink Tubing, Polyolefin with hot melt adhesive

Product Description

3M™ MDT-A is a medium wall, Halogen Free, Heat Shrink Tubing range, offering tough and flexible insulation, and is designed to provide protection to electrical splices, connections, and terminations up to 1kV as well as mechanical and environmental protection. MDT-A Heat Shrink Tubes have a Halogen free polyolefin crosslinked outer wall and have a factory-applied adhesive inner layer, for excellent sealing properties. The product is RoHS Compliant.

Product Selection

ID		Tube Wall Thickness	Adhesive Wall Thickness
(mm)		(mm)	(mm)
Supplied Min.	Recovered Max.	Recovered (Minimum)	Recovered (Minimum)
12.0	3.0	2.3	0.7
19.0	6.0	3.2	0.8
27.0	7.5	3.3	0.8
32.0	7.5	3.3	0.8
38.0	12.0	3.3	0.8
50.0	18.0	3.3	0.8
70.0	26.0	3.3	0.8
90.0	36.0	3.3	0.8
120.0	40.0	3.3	0.8

Typical Properties

Physical Properties	Value	Requirement	Test Method
Colour	Black		
Shrink ratio	up to 4.5:1		
Tensile strength	22 N/mm ²	>13	IEC 60684-2-19.1
Elongation at break	650%	>350	IEC 60684-2-19.2
Longitudinal change	-10<>+0%	-15<>+5	IEC 60684-2-9
Concentricity supplied (total wall)	50%	>50	IEC 60684-2-3
Concentricity fully recovered (outer wall)	85%	>85	IEC 60684-2-3
Secant Modulus	85 N/mm ²	80<>160	IEC 60684-2-19.4
Relative Density ⁽¹⁾	1.01 g/cm ³	-	IEC 60684-2-4

Thermal Tests			
Continuous Operating Temperature ⁽¹⁾	-55<>130°C		
Shrink Temperature	135<>280°C		
Heat Shock	20 N/mm ² 650%	4 hrs @ 200°C	IEC 60684-2-6
Tensile strength Elongation at break		>10 >200	IEC 60684-2-19 IEC 60684-2-19
Low Temperature Flexibility	Pass	4 hrs @ -40°C No cracking after bending	IEC 60684-2-14
Copper Corrosion	Pass	No Corrosion	IEC 60684-2-33
Flammability ⁽¹⁾	Not self-extinguishing		IEC 60684-2-26
Electrical Tests			
Volume resistivity	10 ¹³ Ωm	>10 ¹² room temp.	IEC 60684-2-23
Dielectric Strength	16 kV/mm	explD 10-25 >12 26-50 >10 51-120 >8 >=121 >6	IEC 60684-2-21
Chemical Tests			
Chemical Resistance		-	
Insulating oil (mineral based) @ 23°C Cleaning fluid (Isopropyl alcohol) @ 23°C Water (de-ionized) @ 85°C	Pass	Tensile Strength >10N/mm ² Elongation >200%	IEC 60684-2-36

¹⁾ Outer wall only

Agency Approvals & Self Certifications

- Halogen Free
- RoHS Compliant
- Lloyds Register Certificate 95/30032

Shelf Life & Storage

This product has a 5 year shelf life from date of manufacture when stored in a humidity controlled storage (-5°C to +27°C and <75% relative humidity).

Safety and Handling

3M provides its customers a separate MSDS for the Heat Shrink tubing to cover potential health effects, safe handling, storage, use and disposal information. 3M strongly encourages its customers to review the MSDS on its products prior to their use. Avoid skin contact with hot material.

Product Stewardship

3M has a fundamental concern for all who make, distribute and use its products, and for the environment in which we live. This concern is the basis of our philosophy and policies by which

we assess the health and environmental information on our products and then take the appropriate steps to protect employee, the public health and the environment.

Customer Notice

3M encourages its customers and potential users of 3M products to review their applications for such products from the standpoint of human health and environmental quality. To help ensure that 3M products are not used in ways for which they were not intended or tested. 3M personnel are available to assist customers in dealing with ecological and product safety considerations. Your 3M sales representative can arrange for the proper contacts.

Important Notice: Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.



Electrical Markets Division
3M UK PLC, 3M Centre, Cain Rd,
Bracknell RG12 8HT, United Kingdom
0870 609 4639
www.3m.co.uk/electrical

Electrical Markets Division
3M Ireland Ltd, The Iveagh Building, The
Park, Carrickmines, Dublin 18, Ireland
1 800 812 732
www.3m.co.uk/electrical

3M and is a trademarks of the 3M
company.
© 3M 2021. All rights reserved.

Issue 3