Scotch® Box Sealing Tape 315



Technical Data			March 2014
Product Description	Scotch® Box Sealing Tape 315 is a high performance packaging tape used for critical box sealing applications. This product has a strong, conformable film backing and a high coating weight, pressure sensitive acrylic adhesive system. This construction provides a good closure for heavier weight boxes, boxes exposed to distribution hazards and boxes sealed at cold temperatures.		
Product Construction	Backing	Adhesive	Colors
	Biaxially orientated polyprop	ylene Pressure sensitive acrylic	Clear and Tan
Typical Physical Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. ASTM Test Method		
	Adhesion to Steel:	38 oz./in. width (41.5 N/100 mm)	D-3330
	Tensile Strength: Machine Direction: Cross Direction:	23 lbs./in. width (402 N/100 mm) 40 lbs./in. width (700 N/100 mm)	D-3759 D-3759
	Elongation at Break:	200%	D-3759
	Tape Thickness - Backing: Total:	2.3 mil (0.058 mm) 3.5 mil (0.089 mm)	D-3652
Features	Adheres instantly to a v	ariety of surfaces	
	Strong conformable backing		
	• Excellent tear and split resistance		
	Good aging in sunlight and fluorescent lighting		
	Reliable closures for difficult and extreme temperature applications		
	• Long life in use		
Available Sizes	Standard Widths:	48 mm, 72 mm	
	Core Size (ID):	3 in.	

50 m, 100 m, 914 m

Lengths:

Scotch® Box Sealing Tape

315

Storage Conditions	Store in a clean, dry place. Temperature of 40-80°F (4-26°C) and 40-50% relative humidity.	
Shelf Life	To obtain best performance, use this product within 18 months from the date of manufacture.	
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.	
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.	
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.	
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.	

whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



