

3M™ EMI Absorber AB5000S Series

Product Description

3M™ EMI Absorber AB5000S Series consists of flexible, soft metal flakes filler in polymer resin with acrylic pressure sensitive adhesive. It is supplied on a removable liner for easy handling and die-cutting.

3M absorber AB5000S series is available in sheets.

Features and Benefits

- Polymer resin and metal flakes filler
- Acrylic pressure sensitive adhesive
- Supplied on a removable liner for easy handling and die-cutting

Applications

3M absorber AB5000S series is typically used for applications requiring electromagnetic absorbing performance. It is designed to suppress radiated noise from electrical devices for broadband radio frequency range.

Common uses include mobile phone, computer, digital still camera, military equipment and other electronics for EMI reduction.

Attenuation and Power Loss

Many factors determine the true attenuation of an electromagnetic absorbing material, including shape and thickness, intimacy of substrate contact, smoothness of application surface, strength, and frequency of the EMI signal, etc. However, using standard tests and fixtures, it is possible to determine a value for the signal attenuation.

3M absorber AB5000S series' typical attenuation range is dependent on thickness.

3M™ EMI Absorber AB5000S Series Typical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Properties	Typical Value				
Type of Backing	Polymeric resin with magnetic metal flake filler				
Type of Adhesive	Acrylic non-conductive pressure sensitive adhesive (PSA)				
Product Number	AB5010S	AB5030S	AB5020S	AB5050S	AB5100S
Thickness ¹	0.10mm	0.20mm	0.30mm	0.50mm	1.00mm
Standard Packaging	210mm x 297mm				
Temperature Range	-25 ~ 85°C				
Surface Resistivity ²	1 x 10 ⁶ Ω (min)				
Thermal Conductivity	0.7 W/mK				
Tensile Strength ³	6.0 MPa (min)				
Attenuation (S11 Reflection Loss) and Power Loss ⁴	Refer to attached chart				

¹This value does not contain a double side adhesive tape thickness. Typical adhesive tape thickness is 50 µm (AB5010S contains 30 µm adhesive).



²Test method: ASTM D257.

³Test method: JIS K 6521.

⁴Attenuation measured by 7mm coaxial verification kit under short fixed condition. Power loss measured by 50 Ω microstrip line.

3M™ EMI Absorber AB5000S Series Typical Properties (continued)

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Reflection**Power Loss**

Storage and Shelf Life

The shelf life of 3M™ EMI Absorber AB5000S Series is 12 months from the shipment date from the manufacturing location when stored in original packaging at 21°C (70°F) and 50% relative humidity.

Safety Data Sheet

Please consult Safety Data Sheet prior to use.

Regulatory

For regulatory information about this product, contact your 3M representative.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Electronics Materials Solutions Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle.
©3M 2014. All rights reserved.
60-5002-0719-0

