

3 Marine Application Profile

Surface Protection Products



3M offers many high quality products to protect equipment and other surfaces during the construction, repair and operation of ships.

Protecting critical surfaces throughout the build cycle will reduce cost, increase profitability and potential delays caused by re-work activities.


3M offers unique dispensing systems that significantly increase productivity over traditional masking processes.

Quality 3M masking and duct tapes compliment your surface protection needs. Tapes are designed for extended applications (indoor/ outdoor) without slivering or adhesive transfer.

3M Marine

Your First Choice for Service, Solutions and Satisfaction

877-3M-Marine
(877-366-2746)



Product Description

3M™ Hand-Masker™ Products

3M™ Polymask Carpet Protection Film 4F92

Sandblast Stencil

3M™ Masking Papers

3M™ Polyurethane Protective Tapes

3M™ Paintable Plastic Sheeting

3M™ Overspray Protective Sheeting

Key Attributes

Extremely efficient method of dispensing masking films.

Flame retardant film used to protect carpeting during ship construction, repair and operations.

Heavy duty rubber material used to protect glass and other critical surfaces.

High density treated paper used in conjunction with masking tapes for gross masking applications.

Extremely tough and durable, puncture and tear resistant.

Reduces masking labor time by eliminating a paint masking step.

High density, tear resistant, clear film that is treated on both sides for excellent paint overspray adhesion.



3M Surface Protection Product Offering

Product	Product Description	Features & Benefits
3M™ Hand-Masker™ Products	Handheld dispensers that apply masking tape to masking film or paper in one continuous application. Compact and lightweight. Pre-folded, high-density film for paint masking and paint overspray protection. Available in fan-fold widths from 6” to 108.”	Micro-etched flake resistant surface. Significantly increase in productivity.
3M™ Masking Papers	High-density treated paper used in conjunction with masking tapes for gross masking applications. Available in widths from 6” to 36.”	Table-top or rolling dispensers are available to apply masking tape to paper in one continuous application.
3M™ Polymask Carpet Protection Film 4F92	4F92 Polymask is a 4 mil fire retardant carpet protective film. The film meets or exceeds IMO Resolution A.653(16) and Resolution MSC.61(67)	Cost effective. A light-tack adhesive makes this an excellent film to protect carpets during construction, repair or routine ship operation.
Sandblast Stencil	Abrasion resistant rubber backing coated with rubber adhesives. Available in 40 mils (510 Stencil), 32 mils (1532 Stencil) and 18 mils (1520 Stencil).	Used to protect glass or other critical areas from damage.
3M™ Polyurethane Protective Tapes	Polyurethane protective tapes are quickly and easily applied to form a long lasting protective surface for your product and/or equipment. These tapes are extremely tough and durable, puncture and tear resistant. Available in widths from 6” to 36”	Extremely effective at preventing damage caused by abrasion, erosion, minor impact, and fluids.
3M™ Paintable Plastic Sheeting	Uniquely formulated ½ mil micro etched film that provides excellent paint adherence.	This sheeting has a center seam for easy alignment and the fold pattern allows for easy application
3M™ Overspray Protective Sheeting	12 foot film folded to three feet for easy one-person application. 16 foot width accommodates larger surface areas for more effective overspray protection.	A high density, tear resistant, clear film that is treated on both sides for excellent paint overspray adhesion.

For Additional Information: To request additional product information or to arrange for sales assistance, please call 1-877-366-2746 (1-877-3M MARINE). Address correspondence to: 3M Marine, 3M Center Bldg. 223-6S-06, St. Paul, MN 55144-1000. To send a fax, please call 651-737-9658.

Warranty and Limited Remedy: 3M warrants this product will be free from defects in materials and manufacture for 12 months from the purchase date. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If the product is proved to be defective within the warranty period, your exclusive remedy and 3M’s and seller’s sole obligation will be, at 3M’s option, to replace the product or refund the purchase price.

Limitation of Liability: 3M and seller will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, of contract, negligence or strict liability.

The foregoing Warranty and Limited Remedy and Limitation of Liability language may be changed only by a written agreement signed by authorized officers of 3M and seller.