



Scotch-Weld™

Concrete Repair

DP-600, Self-Leveling, Gray

Technical Data

July, 2006

Product Description 3M™ Scotch-Weld™ Concrete Repair DP-600 is a self-leveling, gray, rapid setting, two-component polyurethane. It is packaged as 1:1 ratio liquids in a duo-pak cartridge. With the squeeze of the trigger, the components are automatically mixed and easily dispensed as a bubble-free self-leveling liquid.

- Suggested Applications:**
- Rapid repair of spalled or cracked concrete floors or pool decks in high traffic areas
- Building & Construction Maintenance & Repair**
- Re-installing posts and rails
 - Custom tapping of bolts and screws into wood, concrete and masonry
- Pool Maintenance & Repair**
- Tough, non-brittle bonding of wood, metal, glass and plastic
 - Fixturing of hand/grabrails into pool decks
 - Rapid repair of pool decks prior to being coated

Typical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Test	Conditions	Test Method	Properties
Appearance	Cured	PEC	Gray mass
Viscosity Part A	77°F (25°C)	HBDVI+CP	4050 cps
Viscosity Part B	77°F (25°C)	HBDVI+CP	2500 cps
Work Life	10 g, 1/4" thick @ 77°F (25°C)	PEC	70 seconds
Tack-free Time	10 g, 1/4" thick @ 77°F (25°C)	PEC	4 minutes
Full Cure Time	10 g, 1/4" thick @ 77°F (25°C)	PEC	1 hour
Hardness After Full Cure	1 hour at 77°F (25°C)	ASTM D2240-91	70 Shore D
Lap Shear Strength	7 days at 77°F (25°C)	ASTM D1002-72	2,300 psi
Temperature Range	Continuous	PEC	-60°F (-51°C) to 250°F (121°C)

3M

Scotch-Weld™

Concrete Repair

DP-600, Self-Leveling, Gray

Prepare the Cartridge for Dispensing:

1. Select the desired dispenser (manual or pneumatic) and mix tip.
2. Cut the blind-end off of the cartridge orifice or remove the plugs and place the cartridge in the dispenser.
3. Dispense just enough material so that both components dispense equally.
4. Assemble the mix tip onto the cartridge with a half-twist.

CONCRETE REPAIR, SELF-LEVELING:

Section 1: Preparation

General Preparation for Concrete Repairs

1. Prepare a cavity, depression, groove, saw-cut, or crack by removing all loose aggregate, dust, old caulks, grease or other compounds from the repair surface.
2. For maximum relief of stresses in large concrete sections, it is best to create a 1/4-inch saw cut entirely through the concrete. However, first determine that there are no other structural limitations including rebar, plumbing and electrical installations. The use of a foam backer embedded to within 1/4-inch of the surface is recommended for maximum stress relief.
3. For tracing cracks for stress relief, it is best to use a tapered grinder to create a taper starting at 1/4-inch at the top and tapering deeply into the concrete.
4. Use a bristle brush to remove the debris. Then use moisture-free and oil-free compressed air to blow out the fine dust.
5. Mask off the areas surrounding the repair allowing approximately a 1-inch overlap of 3M™ Scotch-Weld™ Concrete Repair DP-600 around the periphery of the prepared cavity.

Preparing for Damage from Corrosion:

1. Apply a pre-coat of concrete corrosion inhibitor or protectant exclusively to corroded areas.
2. Allow the pre-coat to dry thoroughly.

3M

Scotch-Weld™

Concrete Repair

DP-600, Self-Leveling, Gray

Section 2: Procedures

General Procedure for Doing Concrete Repairs

1. Keeping the mixer tip at the deepest portion of the repair area, dispense into the prepared cavity, depression, void, groove or crack.
2. Slightly over-fill the prepared cavity.
3. 3M™ Scotch-Weld™ Concrete Repair DP-600 will self-level and set approximately within one minute and leave a slight meniscus. If desired, one can create a repair flush and level to the concrete floor on smaller areas up to 6 inches square by overlaying a slightly stiff polyethylene sheet (approximately the modulus of a plastic spreader) just prior to the set of Scotch-Weld concrete repair DP-600.
4. Overfilling Scotch-Weld concrete repair DP-600 and allowing it to overlap approximately one inch along the edges of the repair tapering to just a few mils thickness provides a substantial tie into the concrete and increases the lifetime of the repair.
5. At 75°F (24°C), a 1/4"-thick section sets and becomes tack-free within 4 minutes and will cure within one hour. **Note:** Thicker masses or substrates at higher temperature take less time to cure. Thinner masses or substrates at lower temperature take more time to cure.

Section 3: Clean-up and Finishing

1. Remove the masking tape surrounding the repair areas.
2. If desired, grind the cured product with 36 to 50 grit sanding disks or sandpaper to take off any rough edges and achieve the desired shape. Sand with finer grit sandpaper to the desired finish.

3M
Scotch-Weld™
Concrete Repair
 DP-600, Self-Leveling, Gray

CUSTOM TAPPING AND FASTENING

The flanges of posts and rails, auditorium and stadium seats, pallet racks, and other load-bearing structures are usually secured into concrete floors by shooting nails or screwing lag bolts into shields embedded within cored holes. Custom tapping provides the advantage that these structures can be easily removed and relocated to other locations without having to grind down the protruding nails or fill the remaining cored holes.

Custom Tapping is done by molding the threads of bolts and screws into 3M™ Scotch-Weld™ Concrete Repair DP-600. The tough molding properties of Scotch-Weld concrete repair DP-600 allows it to form and maintain a high-strength, non-brittle interlock between holes cored into concrete (or wood, ceramic or masonry) and the threads of the inserted bolt or screw. The release characteristics, upon removal, are achieved by simply spraying the bolt or screw with 3M™ 5-Way Penetrant (or other release agent) before the bolt or screw is inserted into the liquid Scotch-Weld concrete repair DP-600 prior to its setting. To achieve a more permanent fixture, the bolts and screws simply are not lubricated before imbedding into the liquid Scotch-Weld concrete repair DP-600 prior to setting.

Section 1: Preparation For Custom-Tapping:

1. Drill holes into the concrete, wood or masonry to the specified depth using the chart below.

Bolt Width (in.)	Minimum Hole Diameter (in.)	Minimum Hole Depth (in.)
1/4	3/8	2
3/8	1/2	3-1/2
1/2	5/8	4-1/4
5/8	3/4	5
3/4	7/8	6-3/8
7/8	1	7-1/2
1	1-1/8	8-1/4
1-1/8	1-1/4	9
1-1/4	1-3/8	9-3/4
1-3/8	1-1/2	10-1/2
1-1/2	1-5/8	11-1/4

2. Use a round bristle brush to clean the cored holes if they have not been freshly drilled. Use moisture-free and oil-free compressed air to blow out the debris.
3. Lightly coat the bolts or screws with 3M 5-Way Penetrant.

3M

Scotch-Weld™

Concrete Repair

DP-600, Self-Leveling, Gray

Section 2: Procedures

Procedure for Custom Tapping Concrete:

1. Dispense 3M™ Scotch-Weld™ Concrete Repair DP-600 into the hole nearly halfway full. To obtain a consistent fill, judge for under-fill or overfill by counting the number of squeezes of the trigger.
2. Insert the bolt or screw within the first 20 seconds after dispensing. The paste characteristic of Scotch-Weld concrete repair DP-600 will hold the bolt or screw in place until it cures. Once the work life has been exceeded, do not disturb the bolt.
3. Move to the next hole to keep Scotch-Weld concrete repair DP-600 flowing in the mixer tip. If material sets in the mixer tip, replace the tip and start dispensing again.
4. Scotch-Weld concrete repair DP-600 will become tack-free within 4 minutes and cure within one hour. **Note:** It is best to wait one full hour before extracting the bolt or screw for securing the cupboards, wall hangers or other cabinetry in place.
5. Allow Scotch-Weld concrete repair DP-600 to fully cure before applying a load. The maximum torque recommended is 9.0 pounds.

Note: Not for use in repairing or anchoring diving boards.

RE-ANCHORING HANDRAILS AND GRABRAILS

Section 1A: Preparation of Hand/Grabrails

1. Bore a hole through the base of the hand/grabrail just above grade level to allow introduction of the product.
2. Using 80 grit sandpaper, roughen the footing surface of the hand/grabrail which is to be imbedded below the concrete grade.
3. Refer to instructions on cartridge for dispensing.

Section 1B: Preparation of Concrete for Re-anchoring

1. Chip away the cracked or broken concrete to allow removal of the hand/grabrail.
2. Leave the concrete as close as possible around the hand/grabrail. It is best to allow the concrete to remain intact as close as possible (within 1/2 to 1 inch all around) to the base of the hand/grabrail.
3. Dig down to the base of the concrete, typically 4- to 6-inches deep.
4. Expose any rebar, if possible, in order to create a ground connection to the rebar.
5. Create as much as a 1-inch undercut under the concrete in a smooth taper from the concrete surface.
6. Remove all of the loose concrete particles and dust prior to encasing the replacement hand/grabrail.
7. Attach the replacement hand/grabrail to surrounding rebar using a copper wire. Cinch the connection down tightly, allowing a slight amount of slack in the wire connection.
8. Create a shield to corrosion at the base of the hand/grabrail by laying a piece of polyethylene plastic at the base of the hole.
9. Insert the hand/grabrail in the hole. Align the hand/grabrail for its elevation and vertical plumb.

3M

Scotch-Weld™

Concrete Repair

DP-600, Self-Leveling, Gray

Section 2 Encasement Procedure

1. Dispense 3M™ Scotch-Weld™ Concrete Repair DP-600 into the concrete hole. Product will remain liquid for approximately 50 seconds, and fully cure in 1 hour. Dispense more cartridges as necessary to bring the fill level up to the concrete surface level.
2. Dispense Scotch-Weld concrete repair DP-600 into the inside of the hand/grabrail. Fill with product up to and slightly above the grade level. (Filling the inside of the post provides extra strength and protection against corrosion.)
3. Apply cement dust or sand, if desired, to blend the surface appearance into the surrounding concrete.
4. If Scotch-Weld concrete repair DP-600 is applied in a traffic area, apply sand or some type of grit to repaired surface area.

Section 3: Repair Clean-up and Finishing

1. Shave or grind cured product with 36 grit sandpaper to achieve desired shape.

3M

Scotch-Weld™

Concrete Repair

DP-600, Self-Leveling, Gray

Storage This product has a shelf life of 6 months when properly stored in unopened packages at temperatures of 65°F to 85°F (18°C to 30°C). Do not expose to excessive cold or moisture.

Maintenance No maintenance is required. However, if repairs become damaged, simply reapply 3M™ Scotch-Weld™ Concrete Repair DP-600.

Precautionary Information Refer to Product Label and Material Safety Data Sheet (MSDS) for health and safety information before using this product. For environmental information, refer to MSDS. Always wear gloves, eye protection, appropriate respiratory protection, and work in a well-ventilated area. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

Product Use All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Business Industrial Adhesives and Tapes Division

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M and Scotch-Weld are trademarks of 3M.
Printed in U.S.A.
©3M 2006 78-9236-7100-8 (7/06)