

3M

Polyethylene Tape

483

Technical Data

October, 2009

Product Description 3M™ Polyethylene Tape 483 has a polyethylene backing with a rubber adhesive for many general purpose applications including sealing, color coding, protecting, moisture proofing. Black tape has excellent U.V. resistance and can be used outdoors for up to 12 months.

Product Construction	Backing	Adhesive	Color	Standard Roll Length
	Polyethylene	Rubber	Transparent, red, blue, white, black, yellow	36 yds. (33 m)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	12 oz./in. width (13 N/100 mm)	D-3330
Tensile Strength:	10 lbs./in. width (175 N/100 mm)	D-3759
Elongation at Break:	300%	D-3759
Backing Thickness:	3.9 mils (0.10 mm)	D-3652
Total Tape Thickness:	5.0 mils (0.13 mm)	D-3652
Temperature Use Range:	Up to 200°F (93°C)	
Low Leachable Halogens and Sulfur (black tested):	Pass	MIL STD 2041D(SH)
Outdoor Weathering (black only):	Up to 12 months	ASTM G155 Cycle 1

Features

- Tape stretches easily and is highly conformable for a tight seal around irregular surfaces.
- Polyethylene backing provides good solvent and alkali resistance properties.
- Remains flexible to -20°F (-29°C).

Note: Should not be exposed to temperatures which exceed 170° to 200°F (77° to 93°C). Exposure to such temperatures may result in softening of backing.

- Vivid colors and smooth backing provide excellent glossy appearance.
- Low sulfur and halogen content.
- Low water vapor transmission rate.
- Best results are attained when applied to a clean, dry surface at temperatures between 60° to 80°F (16° to 27°C).

3M™ Polyethylene Tape

483

Application Ideas

- General sealing of containers and irregular shaped objects.
- Electroplating and P.C. board masking.
- Silicone chip holding.
- Decorative, safety marking and color coding.
- Nuclear power plant construction and maintenance - (because of low chloride and halogen content).
- Corrosion sensitive applications - (because of low chloride and halogen content).
- Outdoor applications of sealing, protecting, and preserving (black colored tape only).

Storage

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M company.
Printed in U.S.A.
©3M 2009 70-0709-5021-0 (10/09)