

3M™ Digital Projector S15i



- Create a lasting impression
- Ideal for smaller rooms in the office
- 3-year Standard Warranty
- Lightweight for portable use
- Whisper Mode helps minimize noise



CONNECTIONS

COMPUTER

- RGB
- Serial Control
- PC Audio


VIDEO

- S Video
- RCA Composite
- Audio (Stereo)
- Component through RGB with special cable

BASIC SPECS

- S15i: 1500 lumens*
- SVGA (800 x 600)
- 5.18 lbs / 2.34 kg
- 300:1 contrast ratio
- Whisper Mode
- Vertical Digital Keystone

* indicates maximum lumens rating



S15i Order Number: 78-9236-6897-0





OPTICAL

- Brightness: typical: 1500 lumens* (1,200 whisper mode)
- Imager Set: 0.55" Polysilicon LCD
- Resolution (native): SVGA (800 x 600 pixels)
- Resolution (maximum): SXGA (1280 x 1024 pixels)
- Aspect Ratio: 4:3 native, 16:9
- Colors: 16.7 million
- Screen Size (range): 40 - 300 inches
- Digital Zoom: 1.2 times
- Projection Lens: F1.8 (f=21.4 mm)
- Optional Lenses: No
- Contrast Ratio (peak): 300:1
- Lamp: 165w UHB
- Lamp Life (average): 2000 hrs

*indicates maximum lumens rating

ELECTRICAL

- Video Compatibility: NTSC, NTSC 4.43, PAL, PAL-M, PAL-N, SECAM
- HDTV: 480i, 480p, 525i, 525p, 720p, 1080i**
- Digital Keystone Correction: Vertical: ±15°
- Audio: 1 x 1w
- Noise Level: normal (whisper): 38 (33) dB
- Feature Set: Auto off, 4x digital magnification, blank
- Horizontal Scan: 31.5 - 91 kHz
- Vertical Scan: 56 - 120 kHz
- Power Consumption: 240w
- Power Supply: Universal: 100 - 120V/220 - 240V AC, 50/60 Hz
- Regulatory Approvals: UL, cUL, FCC part 15 Class B, CE, EN60950
- Operating Temperature: 32 - 95 F (0 - 35 C)
- Storage Temperature: -4 140 F (-20 - 60 C)

**Component Video is available through computer input, using a VGA to RCA component video cable.

SIZE

- Dimensions (W x H x D): 11.2 x 2.9 x 7.9 in. (285 x 73 x 202 mm)
- Weight: 5.18 lbs/2.349 kg

WARRANTIES

- Projector: 3 Years Standard
- Ultra Value Warranty available—includes free lamp and free loaner while unit is repaired and expedited service. (see Optional Accessories)
- Lamp: 1 Year Prorated

ACCESSORIES INCLUDED

- Power Cords (3x - US, UK, Euro)
- RGB computer cable
- Remote Control w/ 2AA batteries
- Multilanguage Quick Start Guide
- Multilanguage Operator's Guide CD
- Lens Cap
- Soft Case

OPTIONAL ACCESSORIES

- Ultra Value Warranty S15i (WS15i) 78-6969-9869-5
- Lamp for S15i (LKS15i) 78-6969-9812-5
- Soft Side Case with Shoulder Strap - Projector & Notebook Computer (SSC10/40/50) 78-6969-9715-0
- Soft Rolling Luggage Case - Projector & Notebook Computer (SSC10/40/50) 78-6969-9716-8
- Ceiling Mount (CMS15i) 78-6969-9813-3

PROJECTION DISTANCE CHARTS AT 4:3 SCREEN— 3M S15i

(a) Screen size [inch (m)]	(b) Projection distance [m inch]
40 (1.0)	1.5 (60)
50 (1.3)	1.9 (75)
60 (1.5)	2.3 (90)
70 (1.8)	2.7 (105)
80 (2.0)	3.1 (121)
90 (2.3)	3.4 (136)
100 (2.5)	3.8 (151)
120 (3.0)	4.6 (182)
150 (3.8)	5.8 (227)
200 (5.1)	7.7 (303)
250 (6.4)	9.6 (380)
300 (7.6)	11.6 (456)

Note: These sizes are ±10 percent. This is due to variations in the manufacture of the lens. If you are close to one of the endpoints you should verify with your unit that the image is the proper size at the proper distance.

www.3m.com/meetings

Important Notice

All statements, technical information, and recommendations related to 3M's products are on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publication, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture for a period of 3 years from the date of purchase. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.

Hg—LAMP CONTAINS MERCURY. Manage in accord with disposal laws. See www.lamprecycle.org or call 1-800-328-1371 (USA), 1-800-364-3577 (Canada). For product disposal see www.eiae.org (USA).

Specifications subject to change without notice. 3M is a trademark of 3M Company. Used under license in Canada. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

3M Projection Systems

Building A147-5N-01
6801 River Place Blvd.
Austin, TX 78726-9000

3M Mexico, S.A. de C.V.

Apartado Postal 14-139
Mexico, D.F. 07070
Mexico

3M Canada

P.O. Box 5757
London, Ontario, Canada
N6A 4T1

© 3M 2008 V113007

78-6970-8629-2