

3M™ SelfCheck™ System (S-Series)

The affordable, reliable automated check-in system

As a complete check-in and sorting system that is both affordable and reliable, the 3M™ SelfCheck™ System S-Series helps libraries increase circulation and maintain a more accurate catalogue, while improving productivity and customer service. With its real-time check-in feature, easy-to-use interface and return receipt, customers are sure each item is returned correctly. In addition, staff can quickly separate exceptions and send materials to the shelves - and customers can immediately check out high demand items. Along with a scalable 3 or 5 bin

design, the SelfCheck™ S-Series lets libraries customise the sort matrix so bins are equally distributed. The system notifies staff when bins are full and sends an instant e-mail if the circulation system goes offline or the printer is out of paper. Libraries can also monitor the number of processed items and schedule staff during peak periods, when the return rate is highest. More importantly, the SelfCheck™ S-Series allows staff to spend more time helping customers.

Real-Time Check-In

- Items are instantly checked in upon return
- Customers receive return receipts
- Speeds the return of items to the shelves
- Reduces the number of claims returned

Automatic Staff Hold Receipts

- Quickly separates exceptions

E-mail Notifications

- Instant notification if the circulation system goes offline or the printer is out of paper

Easy-To-Use Interface

- Customers and staff can easily learn how to use the system

Statistics

- Monitor the return rate
- Schedule staff during peak periods

Customised Sorting

- Set the sort matrix for your library
- Equally distribute items among bins
- Scalable 3- or 5-bin design
- System automatically stops sorting to full bins

Dimensions

• Wall Unit

57.3"d x 39.3"h x 62.8"w
(1456 mm x 1000 mm x 1596 mm)

• Sorter (3-bin)

64"d x 41.8"h x 57.6"w
(1626 mm x 1060 mm x 1464 mm)

• Sorter (5-bin)

64"d x 41.8"h x 95"w
(1626 mm x 1060 mm x 2413 mm)

Energy Profile

• Wall Unit

220–240 VAC, single phase
50–60 Hz 3A

• Sorter

220–240 VAC, single phase
50–60 Hz 2.5A

Weight (Approximate)

• Wall Unit

880 lbs (400 Kg)

• Sorter (3-bin)

440 lbs (200 Kg)

• Sorter (5-bin)

620 lbs (282 Kg)



Sorter (3 OR 5 BIN)



Wall Unit

Library Systems

3M United Kingdom PLC
3M Centre, Cain Rd
Bracknell, Berkshire
RG12 8HT

Free phone: 0800 389 6686
Free fax: 0800 587 8975

email: library-uk@mmm.com
www.3m.com/uk/library

3M Ireland

3M House, Adelphi Centre
Upper Georges Street,
Dun Laoghaire, Co. Dublin

Tel: (01) 280 3555
Fax (01) 280 3509