


3M Application Profile

Market: General Industrial

Application Description: Holding rivets in place prior to and during riveting.



Key Application Requirements

Must hold rivets securely in place until riveted. Must remove easily from the surface after completion of riveting.

Benefits/Advantages To Customer

Uncoated center “window”: Tape does not adhere to rivets and leaves no adhesive residue behind on the rivet heads. This window also offers easy visibility of the rivets during the riveting process.

Pressure-sensitive adhesive: Coated on the edges of the film; has good initial adhesion to most surfaces and is strong enough to hold the rivets in place.

Strong backing film: Resists stretching induced by the bucking bar that might lead to film entrapment under rivet heads; reduces rework and ensures ease of application.

PRODUCT

3M™ Riveters Tape 685

3M™ Riveters Tape 695

3M™ Riveters Tape 696W

Additional Product Information

3M™ Riveters Tape 685: Transparent with green adhesive.

3M™ Riveters Tape 695: Yellow with with white adhesive.

3M™ Riveters Tape 696W: Transparent.

Other Markets to Consider

Aerospace, Marine & Specialty Vehicle, Transportation, MRO.

For Additional Information

To request additional product information or to arrange for sales assistance, call 1-800-362-3550. Address correspondence to: 3M Industrial Business Customer Response Center, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55106. Our fax number is 651-733-9175. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Product Use

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy

Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. **3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability

Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence, or strict liability.



Industrial Business

Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55106

Printed in the USA
Giriv685.pdf
© 3M 2005