

# 3M™ Digital Library Assistant

## Actively manage your library collection

As a component of the 3M™ RFID System, this cordless, handheld device instantly reads 3M™ RFID Tags on library materials, turning shelf-reading, shelving, sorting, searching, weeding and exception-finding into routine tasks. Compact and easy to use, the Digital Library Assistant can hold information on more than one million items. The ergonomic design and swivel antenna maximize comfort and minimize stooping. No more bending or stretching to read high or low shelves. And because it simultaneously performs shelf-reading, searching and inventory scans, it can save time, increase productivity and discover errors that might otherwise go unnoticed. The device can also quickly identify items that were not properly checked out, and it instantly detects the security status of materials. Start actively managing your library collection today with the state-of-the-art Digital Library Assistant from 3M.

### Easy To Use

- Ideal for shelf-reading, re-shelving, searching, weeding and exception-finding
- Simultaneously performs shelf-reading, searching and inventory scans
- Increases productivity and creates a more orderly library

### Ergonomic, Handheld Design

- Comfortable
- Cordless
- Compact
- Lightweight

### 3M Tag Data Manager

- Freedom to move to ISO Tag Data Standard in the future
- Empowers the 3M™ RFID System to read country specific data formats (Danish, Dutch, Finnish and French)

### High Storage Capacity

- Holds information for more than one million items
- Stores information effectively and easily

### Enhanced Security

- Instantly detects materials that cause an alarm
- Identifies items not properly checked out or in
- Corrects errors quickly and easily

### Dimensions

- Handheld unit: 9.5" x 7" x 4" (240 mm x 180 mm x 100 mm)
- Antenna portion: 9.5" x 4" x 0.5" (240 mm x 100 mm x 12.5 mm)

### Energy Profile

- Handheld unit: 7.4 volt rechargeable battery
- Battery life: 4 hours read time between recharges – typically 6-8 hours of use (dependent on application)

### Weight (Approximate)

- Handheld unit: 25 oz (700 g) (includes battery)
- Shipping container weight: 11 lbs (5 Kg)

UL-Certified

Meets the EU  
WEEE and RoHS  
Directives



**3M Library Systems**  
3M Center, Bldg. 225-4N-14  
St. Paul, MN 55144-1000  
USA  
1-800-328-0067  
www.3M.com/us/library

Please recycle. Printed in USA.  
© 3M 2008. All rights reserved.  
3M, SelfCheck and Tattle-Tape  
are trademarks of 3M.

