

ORDERING INFORMATION

Large Panel Repair

Sanding

3M™ Hookit™ II Finishing Film Discs

Part No.	Description	Size	Grade	Discs/Box	Boxes/Case
00868	3M™ Hookit™ II Finishing Film Discs	6 in.	P1200	50	4
00850	3M™ Hookit™ II Finishing Film Discs	6 in.	P1500	50	4
00707	3M™ Hookit™ II Finishing Film Discs	3 in.	P1500	50	4
00708	3M™ Hookit™ II Finishing Film Discs	3 in.	P1200	50	4

Scratch Refinement

3M™ Trizact™ Hookit™ II Foam Discs

Part No.	Description	Size	Grade	Discs/Box	Boxes/Case
02075	3M™ Trizact™ Hookit™ II Foam Discs	6 in.	P3000	15	4
02077	3M™ Trizact™ Hookit™ II Foam Discs	3 in.	P3000	15	4

3M™ Hookit™ II Abrasive Accessories

3M™ Hookit™ II Abrasive Accessories

Part No.	Description	Size	Pads/Case
05251	3M™ Hookit™ II Painter's Disc Pad	6 in.	10
05274	3M™ Hookit™ II Soft Interface Pad	6 in.	10
05271	3M™ Hookit™ II Soft Interface Pad	3 in.	10
05269	3M™ Hookit™ II Disc Pad (female)	3 in.	5
05270	3M™ Hookit™ II Disc Pad (male)	3 in.	5

Compounding

Pads

Part No.	Description	Type	Items/Unit	Qty./Case
05703	3M™ Superbuff™ III Buffing Pad	100%Wool	1 pad/bag	6 bags
05704	3M™ Superbuff™ III Buffing Pad	100%Wool	1 pad/bag	6 bags
05721	3M™ Perfect-It™ Hookit™ II Compounding Pad	--	--	6
05723	3M™ Perfect-It™ Foam Compounding Pad	Foam	2 pads/bag	12 bags
05737	3M™ Perfect-It™ Foam Compounding Pad	Foam	1 pad/bag	6 bags

Compounds

Part No.	Description	Items/Unit	Qty./Case
06060	3M™ Perfect-It™ 3000 Extra Cut Rubbing Compound	1 qt.	6 qts.
06062	3M™ Perfect-It™ 3000 Rubbing Compound	1 qt.	6 qts.
06061	3M™ Perfect-It™ 3000 Extra Cut Rubbing Compound	1 gal.	4 gals.
06063	3M™ Perfect-It™ 3000 Rubbing Compound	1 gal.	4 gals.

Machine Glazing

Pads

Part No.	Description	Size	Items/Unit	Qty./Case
05722	3M™ Perfect-It™ Hookit™ II Polishing Pad	3 in.	--	6
05725	3M™ Perfect-It™ Foam Polishing Pad	8 in.	2 pads/bag	12 bags
05738	3M™ Perfect-It™ Plus Foam Polishing Pad	8 in.	1 pad/bag	6 bags

Glazes

Part No.	Description	Items/Unit	Qty./Case
06064	3M™ Perfect-It™ 3000 Swirl Mark Remover	1 qt.	6 qts.
06065	3M™ Perfect-It™ 3000 Swirl Mark Remover	1 gal.	4 gals.

Accessories

Part No.	Description	Items/Unit	Qty./Case
05718	3M™ Perfect-It™ Backup Pad	1 pad	1
05710	3M™ Superbuff™ Adapter	1 adapter	1

Paint Protection

Pads

Part No.	Description	Size	Items/Unit	Qty./Case
05739	3M™ Perfect-It™ Hookit™ II Foam DA Glazing Pad		2 pads/bag	12 bags
05251	3M™ Hookit™ II Painter's Disc Pad	6 in.	1 pad	10

Glazes

Part No.	Description	Items/Unit	Qty./Case
06066	3M™ Perfect-It™ 3000 Final Glaze	1 qt.	6 qts.
06067	3M™ Perfect-It™ 3000 Final Glaze	1 gal.	4 gals.

Wipes

Part No.	Description	Items/Unit	Qty./Case
06016	3M™ Perfect-It™ Detailing Cloths	6 cloths/pack	6 packs
06017	3M™ Perfect-It™ Detailing Cloths	50 cloths/pack	1 pack

Spot Repair

Sanding

3M™ Hookit™ II Finishing Film Discs

Part No.	Description	Size	Grade	Discs/Box	Boxes/Case
00850	3M™ Hookit™ II Finishing Film Discs	6 in.	P1500	50	4
00868	3M™ Hookit™ II Finishing Film Discs	6 in.	P1200	50	4
00707	3M™ Hookit™ II Finishing Film Discs	3 in.	P1500	50	4
00708	3M™ Hookit™ II Finishing Film Discs	3 in.	P1200	50	4

Scratch Refinement

3M™ Trizact™ Hookit™ II Foam Discs

Part No.	Description	Size	Grade	Discs/Box	Boxes/Case
02075	3M™ Trizact™ Hookit™ II Foam Discs	6 in.	P3000	15	4
02077	3M™ Trizact™ Hookit™ II Foam Discs	3 in.	P3000	15	4

3M™ Hookit™ II Abrasive Accessories

3M™ Hookit™ II Abrasive Accessories

Part No.	Description	Size	Pads/Case
05251	3M™ Hookit™ II Painter's Disc Pad	6 in.	10
05271	3M™ Hookit™ II Soft Interface Pad	3 in.	10
05274	3M™ Hookit™ II Soft Interface Pad	6 in.	10
05269	3M™ Hookit™ II Disc Pad (female)	3 in.	5
05270	3M™ Hookit™ II Disc Pad (male)	3 in.	5

Machine Glazing

Pads

Part No.	Description	Items/Unit	Qty./Case
05722	3M™ Perfect-It™ 3000 Hookit™ II Polishing Pad	--	6
05725	3M™ Perfect-It™ Foam Polishing Pad	2 pads/bag	12 bags
05738	3M™ Perfect-It™ Plus Foam Polishing Pad	1 pad/bag	6 bags

Glazes

Part No.	Description	Items/Unit	Qty./Case
06070	3M™ Perfect-It™ 3000 Trizact™ Spot Finishing Material	1 qt.	6 qts.
06071	3M™ Perfect-It™ 3000 Trizact™ Spot Finishing Material	1 gal.	4 gals.

Accessories

Part No.	Description	Items/Unit	Qty./Case
05718	3M™ Perfect-It™ Backup Pad	1 pad	1
05710	3M™ Superbuff™ Adapter	1 adapter	1

Paint Protection

Pads

Part No.	Description	Size	Items/Unit	Qty./Case
05739	3M™ Perfect-It™ Hookit™ II Foam DA Glazing Pad		2 pads/bag	12 bags
05251	3M™ Hookit™ II Painter's Disc Pad	6 in.	1 pad	10

Glazes

Part No.	Description	Items/Unit	Qty./Case
06066	3M™ Perfect-It™ 3000 Final Glaze	1 qt.	6 qts.
06067	3M™ Perfect-It™ 3000 Final Glaze	1 gal.	4 gals.

Wipes

Part No.	Description	Items/Unit	Qty./Case
06016	3M™ Perfect-It™ Detailing Cloths	6 cloths/pack	6 packs
06017	3M™ Perfect-It™ Detailing Cloths	50 cloths/pack	1 pack

Large Panel and Spot Repair



PERFECT-IT™ 3000

THE NEXT GENERATION IN PAINT FINISHING

3M

Automotive Aftermarket Division

3M Center, Building 223-6N-01

St. Paul, MN 55144-1000

1-877-MMM-CARS (1-877-666-2277) or 651-737-6501

www.3M.com/automotive

NASCAR and NASCAR PERFORMANCE is a trademark of the National Association for Stock Car Racing, Inc.

3M is a trademark of 3M
© 3M 2004. All rights reserved.
60-4400-9980-6

Large Panel Repair

Spot Repair

STEP 1



Sanding

1a. To remove nibs, runs or sags

Sand with DA.
3M™ Hookit™ II Finishing Film Discs Grade P1500, PN 00850*
Use with 3M™ Hookit™ II Painter's Disc Pad PN 05251

1b. Texture matching

Sand with DA and interface pad.
3M™ Hookit™ II Soft Interface Pad, PN 05274
*3M™ Hookit™ II Finishing Film Discs Grade P1500, PN 00850
*For harder paints use Grade P1200, PN 00868



1c. Scratch refinement on fresh and cured clear coats

Using a spray bottle, apply enough water to dampen the 3M™ Trizact™ abrasive scratches. Sand damp with DA until Grade P1500 sand scratches are removed. Surface should appear semi-polished.

Note: When sanding contours, use interface pad.
3M™ Trizact™ Hookit™ II Foam Disc Grade P3000, PN 02075
3M™ Hookit™ II Soft Interface Pad, PN 05274

STEP 1



Sanding

1a. To remove nibs, runs or sags

Sand with DA.
3M™ Hookit™ II Finishing Film Discs Grade P1500, PN 00850* / 00707
*Use with 3M™ Hookit™ II Painter's Disc Pad, PN 05251 / 05269 / 05270
*For harder paints use Grade P1200, PN 00868 / 00708

STEP 2



Compounding

2a. Fresh (soft) clear coats

Buff to remove sand scratches completely.
3M™ Perfect-It™ 3000 Rubbing Compound, PN 06062 / 06063
3M™ Perfect-It™ Foam Compounding Pad, 8 inch, PN 05723 / 05737
3M™ Superbuff™ III Buffing Pad, PN 05704*

OR

2b. Cured (hard) clear coats

Buff to remove sand scratches completely.
3M™ Perfect-It™ 3000 Extra Cut Rubbing Compound, PN 06060 / 06061
3M™ Superbuff™ III Buffing Pad, PN 05703*
*Use with 3M™ Superbuff™ Adaptor PN 05710

STEP 2



Scratch Refinement

2a. Fresh and cured clear coats

Using a spray bottle, apply enough water to dampen the 3M™ Trizact™ foam disc before using to remove abrasive scratches. Sand damp with DA until Grade P1500 sand scratches are removed. Surface should appear semi-polished.

Note: When sanding contours, use interface pad.
3M™ Trizact™ Hookit™ II Foam Disc 6" Grade P3000, PN 02075
3M™ Trizact™ Hookit™ II Foam Disc 3" Grade P3000, PN 02077
3M™ Hookit™ II Soft Interface Pad, PN 05274, 6 inch
3M™ Hookit™ II Soft Interface Pad, PN 05271, 3 inch

STEP 3



Machine Glazing

3a. To remove swirl marks

Apply medium pressure.
3M™ Perfect-It™ 3000 Swirl Mark Remover PN 06064 / 06065
3M™ Perfect-It™ Foam Polishing Pad, PN 05725 / 05738
3M™ Perfect-It™ Backup Pad, PN 05718*
*Use with 3M™ Superbuff™ Adaptor, PN 05710

3b. To polish

Apply light pressure. Suggested buffer speed: 1400-1800 RPM.
3M™ Perfect-It™ III 3000 Swirl Mark Remover, PN 06064 / 06065

STEP 3



Machine Glazing

3a. To remove swirl marks

Apply medium pressure.
3M™ Perfect-It™ 3000 Trizact™ Spot Finishing Material, PN 06070 / 06071
3M™ Perfect-It™ Backup Pad, PN 05718*
*Use with 3M™ Superbuff™ Adaptor, PN 05710

3b. To polish

Apply light pressure. Suggested buffer speed: 1400-1800 RPM.
3M™ Perfect-It™ 3000 Trizact™ Spot Finishing Material PN 06070 / 06071
3M™ Perfect-It™ Foam Polishing Pad, PN 05725 / 05738

STEP 4



Paint Protection

4a. Apply final glaze

Make one pass with DA or by hand.
3M™ Perfect-It™ 3000 Final Glaze, PN 06066 / 06067
3M™ Perfect-It™ Hookit™ II Foam DA Glazing Pad, PN 05739*
*Use with 3M™ Hookit™ II Painter's Disc Pad, PN 05251

4b. Wipe clean immediately

3M™ Perfect-It™ Detailing Cloths, PN 06016

STEP 4



Paint Protection

4a. Apply final glaze

Make one pass with DA or by hand.
3M™ Perfect-It™ 3000 Final Glaze, PN 06066 / 06067
3M™ Perfect-It™ Hookit™ II Foam DA Glazing Pad, PN 05739*
*Use with 3M™ Hookit™ II Painter's Disc Pad, PN 05251

4b. Wipe clean immediately

3M™ Perfect-It™ Detailing Cloths, PN 06016