

3M™ SelfCheck™ System (R-Series)

[CHECKOUT]

Self-service with the power of RFID

The 3M™ SelfCheck™ System R-Series helps libraries increase self-service while improving productivity and customer service. With its multiple-item checkout feature and easy-to-use interface, customers and staff can be sure items are checked out and returned correctly. A system so intuitive your customers will be using it in no time. Designed and tested with the help of librarians, the R-Series features a flexible modular design that is compatible with a wide range of architectural models. The system automatically continues to function and retain information if the network or integrated library system goes offline. And with web-based remote monitoring and diagnostics, staff can troubleshoot and obtain system statistics from any location. With the R-Series, libraries can monitor the number of checkouts and schedule staff during peak periods, when the system has the highest checkout rate.

Intuitive User Interface

- Easy to use
- Requires very little configuration
- Reliable software architecture

Reliable Checkout

- Customers are sure items are checked in/out correctly
- Customers can quickly check out many items
- Easy-load fast receipt printer
- Patron selectable e-mail, printed, or no receipt

Contemporary Design

- Kiosk counter comes in a variety of laminate and Corian® tops
- Cabinet comes in a wide variety of finishes to fit the look of any library
- Flexible modular design compatible with a wide range of architecture models

Web-Based Remote Monitoring and Diagnostics

- Instant e-mail notification if the circulation system goes offline or the printer is out of paper
- Monitor check-in/checkout rates
- Troubleshoot and obtain statistics from any location
- Quick problem resolution

Flexible Options

- Fines and fees payments: credit/debit, cash or both
- Store and forward
- Customer/staff selectable checkout/in
- Multiple languages

3M Tag Data Manager

- Freedom to move to ISO Tag Data Standard in the future
- Empowers the 3M™ RFID System to read country specific data formats (Danish, Dutch, Finnish and French)

Dimensions

26" d x 36" h x 44" w
(660 mm x 914 mm x 1118 mm)

- Monitor:
 - High resolution
 - 15" (381 mm) diagonal
 - LCD touch screen
 - Flat panel display
- Printer:
 - 8.5" d x 5.9" h x 6.25" w
(216 mm x 149 mm x 159 mm)
 - Thermal, built into kiosk or stand-alone Ithaca® Model I-Therm 280

Energy Profile

100–120 or 200–240 VAC
50–60 Hz
3.0/1.5 A

Shipping Weight (Approximate)

330 lbs (149 Kg) with laminate top
205 lbs (93.18 Kg) for Corian® top



3M

3M Library Systems

3M Center, Bldg. 225-4N-14
St. Paul, MN 55144-1000
USA
1-800-328-0067
www.3M.com/us/library

Please recycle. Printed in USA.
© 3M 2008. All rights reserved.
3M, SelfCheck and Tattle-Tape
are trademarks of 3M.

UL-Certified

Meets the EU
WEEE and RoHS
Directives