



**3M**

# Commercial Graphics

February 2009

## **3M announces improvements to 3M™ Scotchlite™ Reflective Graphic Films 680CR, IJ680CR**

We are pleased to announce an improved version of 3M™ Scotchlite™ Removable Reflective Graphic Film with Comply™ Adhesive Series 680CR/IJ680CR. The enhancements made to these films provide simpler, faster bubble-free installations and easier removal resulting in productivity savings for you.

**The only retro-reflective graphic film with air release adhesive...  
And positionability...**

**Now with additional improvements:**

- Better slideability to allow for smooth positioning of the graphic prior to adhesion.
- Better air release. Channels stay open longer for easier, smoother application and fewer outgassing issues.
- Better and faster removability.

The improved film 680CR and film IJ680CR inventory will be phased in over the next few months. There is no need to change your ordering process.

### **Shorter Rolls Are Available at no added up-charge**

We are pleased to offer 48 inch by 10 yard rolls of the improved material for purchase with no added up-charge.

- Film IJ680CR-10 48 inches X 10 Yards
- Film 680CR-10 48 inches X 10 Yards

Thank you for your continued interest in 3M products. If you have any questions please contact your 3M Commercial Graphics Account Representative.