

Detection System

Model 8900

Enhanced security coverage with style and versatility

The 3M™ Detection System Model 8900 combines flexibility and style with state-of-the-art technology to provide excellent detection and reliable performance. The system is available in a variety of finishes to match your library's décor. Compliant with ADA requirements, the Model 8900 has a variety of flexible mounting options—direct mount or base plate to better meet your needs.

Excellent Detection Performance

- Utilises the latest RFID technology to provide enhanced detection performance
- Adjustable audio and visual alarms
- Integrated patron counter to monitor your traffic patterns

Attractive Design

- Slim elegant pedestal design allows for excellent visibility of patron in corridor
- Available with the same wood laminate finishes as the 3M™ SelfCheck™ System products to enhance decor matching capabilities
- Neutral finish options also available

Mounting Options

- Direct mount or base plate
- Fits into a variety of floor plans
- Corridor width complies with ADA requirements

The following specifications are for the Model 8900 single-corridor with baseplate.

Dimensions

1040 mm x 1780 mm x 660 mm

Energy Profile

100-240 VAC
50-60 Hz
0.5 A

Weight (Approximate)

61Kg

CE-Certified

UL-Certified



3M Library Systems

3M Gulf
Dubai, UAE +971-4-3670777
Riyadh, Saudi Arabia +966-1-2171324
Kuwait +965-2481957
Beirut, Lebanon +961-1-373771

3M Egypt Cairo +202-25259007
3M Morocco Casablanca +212-22-977977
3M (Tunis Office) +216-71860833

For more information:

Please contact us at Gulf.TrackandTrace@mmm.com
Or visit 3M website www.3M.com/ae/library
© 3M 2008