

3M™ Detection System (Model 500)

Reliable Protection, Versatile Performance

The 3M™ Detection System Model 500 is a reliable and versatile way to protect your library's valuable collection. The Model 500 is available in single and dual corridor systems.

Design/Install Options

- Stylish silver painted wood finish
- Good protection
- Cost effective solution
- Direct mount, buried cable and base plate installation options
- Corridor specific alarm light

Good Security

- Cost effective security solution
- Designed for 3M™ Tattle-Tape™ Security Strips
- Completely safe for magnetic media

Versatile Performance

- 36" corridor width
- Single- or dual-corridor
- Electronics mounted remotely
- Meets ADA requirements

Low Frequency Technology

- Minimizes interference with electronic equipment

The following specifications are for the Model 500 single-corridor with baseplate.

Dimensions

28" d x 62" h x 42" w
(711 mm x 1600 mm x 1070 mm)


Energy Profile

115 or 230 VAC
50/60 Hz
1.8/0.9 A
150 VA

Shipping Weight (Approximate)

88 lbs (40 Kg)

UL-Certified



3M

3M Library Systems
3M Center, Bldg. 225-4N-14
St. Paul, MN 55144-1000
USA
1-800-328-0067
www.3M.com/us/library

Please recycle. Printed in USA.
© 3M 2008. All rights reserved. 3M
and Tattle-Tape are trademarks of 3M.

A Checkpoint product offered by 3M
to libraries.