



## Whole Vehicle

Like most people your concerns about water quality have probably increased over the past few years. Daily, there are new reports on water contaminations. In addition, you face special challenges: every time you reach a new location and hook up to the water supply, you meet a new set of water conditions.


Therefore you need a solution that addresses your concerns wherever you get your potable water from.

## Features

- Easy to install system
- Installs in cold water supply line after tank
- Can be installed vertically or horizontally
- Easy to change filter cartridge
- Patented carbon block
- Patented Interconnect
- Connectors to 22mm pipe
- Clearer, cleaner drinking water on tap
- Taste and odour reduction
- Microbial reduction
- Scale inhibition

## Benefits

- Cleaner, clearer drinking water on tap and inhibition of scale growth on taps and in boilers
- Filters all water on boat
- Helps installation in confined spaces
- A quarter turn to take out and a quarter turn to replace
- Improved absorption of chlorine taste and odour
- Ease of use and positive sealing
- Connection to standard pipe work size
- No need to buy and store bulky, bottled water
- Cleaner, better tasting and smelling water with greater than 95% of chlorine removed and sediment, dirt, rust and silt reduced to 5 microns
- Minimises concerns of biological contamination whilst improving the taste, smell and clarity of your water supply. Reduces up to 99.9% of bacteria, cysts, algae and mould spores as tested
- Reduces the ability of calcium and magnesium to build up as scale on taps, shower heads and in the boiler



## Physical specifications

- Includes a head assembly with integral mounting bracket and a single filter cartridge
- Fittings supplied are 1/2" to 22mm JG
- System Maximum operating pressure is 125 psi (8.62 BAR)
- System Maximum operating temperature 37.8°C
- Filter cartridges incorporate silverised carbon block media
- Pleated media prior to carbon block
- Cartridges are sanitary in design requiring no contact with filter media during cartridge change out
- Filter cartridges are ready to use
- Sanitising bypass plug supplied with each system

Market	Model No	Part No	Replacement Cartridge	Part No	Case size	Head	Fittings Included	Flow Rate	Capacity	Micron	Chlorine	(1)	(2)	(3)	(3)	Scale Inhibition
												Bacteria	Parasitic Cysts	Algae Spores	Mould	
Retail	WV-B3-S	70020210939	B3-S	70020210921	4	NH3 1/2" BSPT	1/2" to 22mm JG	12.6 lpm	56000 l	0.2	>95%	>99.9%	>99.9%	>99.9%	>99%	Y
OEM	WV-B3-SL	70020210947	B3-S	70020210921	4	NH3 1/2" BSPT	1/2" to 22mm JG	12.6 lpm	56000 l	0.2	>95%	>99.9%	>99.9%	>99.9%	>99.9%	Y
	Bypass Plug	70020160290	-	-	6											

(1) as tested with E.Coli and Pseudomonas Fluorescens

(2) as tested in accordance with NSF/ANSI Standard 53

(3) as tested with Dekkera bruxellensis ATCC (64276)

### IMPORTANT

Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system. Systems certified for cyst reduction may be used on disinfected water that may contain filterable cysts.

EPA Establishment Number 070595-CT-001

### CAUTION

This is not a water purifier

### CAUTION

To reduce the risks associated with water leakage, which if not avoided, may result in property damage – check with your local water provider to verify that water pressure is less than 100 psi

### IMPORTANT

Replace every six months or at the start of each season

### CAUTION

Remove cartridge and replace with bypass plug when winterizing or sanitizing



### Water Filtration 3M United Kingdom plc

3M Centre,  
Cain Road, Bracknell  
Berkshire RG12 8HT  
Tel: +44 (0) 1344 858000  
Fax: +44 (0) 1344 858559  
www.3M.com/waterfiltration

### 3M Ireland

3M House, Adelphi Centre  
Upper Georges Street  
Dun Laoghaire  
Co. Dublin, Ireland  
Tel: +353 1 280 3555  
Fax: +353 1 280 3509

### 3M Europe NV/SA

Hermeslaan 7  
1831 Diegem  
Belgium  
Tel: +32-2-7224500  
Fax: +32-2-7224518