















3M™ Earmuff Crossover



3M™ Muff Product				Comparable Peltor™/E-A-R™ Muff				
Product Code	Description	NRR	Case Qty	Product Code	Description	NRR	Case Qty	Features
1425	Plastic, over-the-head earmuff 	22	20 ea	H9A	Peltor™ Optime™ 98-Over-the-head earmuff 	25	10 ea	- High quality, steel head band construction - Foam and liquid filled cushions provide exceptional comfort
1427	Plastic, 3 position earmuff 	27	20 ea	330-3002	E-A-R™ Model 3000 muff - Plastic, three position (behind-the-head & under-the-chin) 	26/25	24 ea	- Three position muff can be worn over-the-head, behind-the-head or under-the-chin - Dielectric - Higher NRR
1435	Plastic, over-the-head earmuff 	23	20 ea	H9A	Peltor™ Optime™ 98 - Over-the-head earmuff 	25	10	- High quality, steel head band construction - Foam and liquid filled cushions provide exceptional comfort
				330-3002	E-A-R™ Model 3000 muff - Plastic, three position (behind-the-head & under-the-chin) 	26/25	24 ea	- Three position muff offers greater flexibility - Dielectric - Higher NRR
1440	Premium, plastic, over-the-head earmuff 	24	20 ea	H9A	Peltor™ Optime™ 98 - Over-the-head earmuff 	25	10 ea	- High quality, steel head band construction - Foam and liquid filled cushions provide exceptional comfort
				330-3002	E-A-R™ Model 3000 muff - Plastic, three position (behind-the-head & under-the-chin) 	26/25	24 ea	- Three position muff offers greater flexibility - Dielectric - Higher NRR

*These ear plug safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulations.

3M™ Earmuff Crossover

3M™ Muff Product				Comparable Peltor™/E-A-R™ Muff				
Product Code	Description	NRR	Case Qty	Product Code	Description	NRR	Case Qty	Features
1450	Plastic, helmet attached earmuff 	23	20 ea	H9P3E	Peltor™ Optime™ 98 - Cap mount earmuff 	23	10 ea	- High quality, steel head band construction - Foam and liquid filled cushions provide exceptional comfort
				330-3031	3E-A-R™ Model 2000H Cap Mount Muff 	21	24 ea	<i>Recommend this muff if customer requires dielectric and is willing to accept slightly lower NRR</i>
				H7P3E-01	Peltor™ Optime™ 101 	24	10 ea	<i>Recommend this muff if customer requires dielectric and and requires an NRR of 23+</i>














Replacement Cushions/Hygiene Kits

1437	One pair of replacement cushions and foam inserts for the 1435 	n/a	10 ea	331-3010	One pair replacement cushions and foam inserts for all E-A-R earmuffs	n/a	6 pr	
1442	One pair of replacement cushions and foam inserts for the 1450 & 1440 	n/a	10 ea	HY3	Replacement hygiene kit for all H9 muffs - (1 pair cushions & 1 pair foam inserts/dampers)	n/a	20 ea	
				HY7	Replacement hygiene kit for all H7 muffs - (1 pair cushions & 1 pair foam inserts/dampers)	n/a	20 ea	

*These ear plug safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulations.

3M™ to E-A-R™/Peltor™ NEXT™

Earplug Crossover

3M Product					Comparable E-A-R or Peltor NEXT Product					
Product Code	Description	Image	NRR	Case Qty	Product Code	Description	Image	NRR	Case Qty	Comments
1120/37062	Soft and flexible earplug. Flexible design allows it to conform to the wearer's ear canal, enhancing comfort. Recommended for moderate to high noise (up to 100 dBA TWA). 200 pair/box, 5 boxes/case, 1000/case.		28	200 pr/box 5 box/case	312-1250	E-A-Rsoft™ Yellow Neon regular uncorded		33	200 pr/box 2,000 pr/case	Also available in large size (312-1251)
					P1000	Peltor™ NEXT™ Nitro uncorded (multicolor plugs)		32	200 pr/box 2,000 pr/case	
					312-1219	E-A-R™ TaperFit 2 regular uncorded		32	200 pr/box 2,000 pr/case	Also available in large size (312-1221)
1130/37063	Disposable PU plug with cloth cord.		28	100 pr/box 5 box/case	311-1250	E-A-Rsoft™ Yellow Neon regular corded		33	200 pr/box 2,000 pr/case	Also available in large size (311-1251)
					P1001	Peltor™ NEXT™ Nitro corded		33	200 pr/box 2,000 pr/case	
					312-1223	E-A-R™ TaperFit™ 2 regular corded		32	200 pr/box 2,000 pr/case	Also available in large size (312-1224)
1100-DP	Refillable foam ear plug dispenser with 1000 pair of 3M™ Foam Ear Plugs 1100. Dispenser is refilled from 3M™ Foam Ear Plugs 1100-R, Bulk Packaged (500 pair per bag, 4 bags per case).		29	500 pr/disp. 2,000 pr/case	391-1000 plus the 391-1004	One Touch Dispenser Base and E-A-Rsoft™ Yellow Neon Dispenser Refill	 	33	1 ea. 500pr/bottle 2,000 pr/case	Also available in large size (391-1005)
1100R	Foam ear plugs to refill the 3M™ Foam Ear Plug Dispenser 1100-DP. Not intended for use without the 3M dispenser. Bulk packaged.		29	500 pr/bag 2,000 pr/case	391-1004	E-A-Rsoft™ Yellow Neon One Touch Dispenser Refill Bottle		33	500pr/bottle 2,000 pr/case	Also available in large size (391-1005)

*These ear plug safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulations.

3M™ to E-A-R™/Peltor™ NEXT™







Earplug Crossover

3M Product					Comparable E-A-R or Peltor NEXT Product					
Product Code	Description	Image	NRR	Case Qty	Product Code	Description	Image	NRR	Case Qty	Comments
1120-DP/37151	3M™ Soft Foam Ear Plug Dispenser 1120-DP		28	500 pr/disp. 2,000 pr/case	391-1000 plus the 391-1004	One Touch Dispenser Base and E-A-Rsoft Yellow Neon One Touch Dispenser Refill	 	33	1 ea. 500pr/bottle 2,000 pr/case	Also available in large size (391-1005)
1120-R/37152	Foam ear plugs to refill the 3M™ Soft Foam Ear Plug Dispenser 1120-DP. Not intended for use without the 3M dispenser. Bulk packaged. 500 pair per bag, 4 bags/case.		28	500 pr/bag 2,000 pr/case	391-1004	E-A-Rsoft™ Yellow Neon One Touch Dispenser Refill Bottle		33	500pr/bottle 2,000 pr/case	Also available in large size (391-1005)
1260	Reusable, multi-flange ear plug		24	100 pr/box 500 pr/case	340-4003	Ultrafit™ Uncorded		25	100pr/box 400 pr/case	
1270	Reusable earplug with cloth cord		24	100 pr/box 500 pr/case	340-4036	Ultrafit™ w/Cloth Cord		25	100pr/box 400 pr/case	
1271	Reusable earplug with cloth cord and carrying case		24	50 pr/box 250 pr/case	340-4036 plus 390-9003	Ultrafit™ w/Cloth Cord and Carrying Case with Chain		25	Plugs: 100pr/box 400 pr/case Carry Case: 200 ea/case	Need to order both items separately
1290/37184	Flanged style reusable plug with braided cotton cord		25	100 pr/box 500 pr/case	340-4036	Ultrafit™ w/Cloth Cord		25	100pr/box 400 pr/case	
1291/37185	Flanged style reusable plug with braided cotton cord and case		25	50 pr/box 250 pr/case	340-4036 plus 390-9003	Ultrafit™ w/Cloth Cord and Carrying Case with Chain		25	Plugs: 100pr/box 400 pr/case Carry Case: 200 ea/case	Need to order both items separately
1292/37186	Flanged style reusable plug with plastic cord		25	100 pr/box 500 pr/case	340-4004	Ultrafit™ Corded		25	100pr/box 400 pr/case	
1293/37187	Flanged style reusable plug with plastic cord and case		25	50 pr/box 250 pr/case	340-4002	Ultrafit™ Corded with Case		25	50 pr/box 200 pr/case	
1310	Semi-aural with removable tips		21/20	10 ea	321-2101	E-A-Rcaps™ Banded Hearing Protector		17	10 ea/box 100 ea/case	
1311	Replacement tips for the 1310		21/20	20 pr	321-2103	E-A-Rcaps™ Replacement Pods		17	5 pr/box 500 pr/case	











*These ear plug safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulations.

3M™ to E-A-R™/Peltor™ NEXT™

Earplug Crossover

























3M Product					Comparable E-A-R or Peltor NEXT Product					
Product Code	Description	Image	NRR	Case Qty	Product Code	Description	Image	NRR	Case Qty	Comments
Other Products available from 3M to meet the customers' needs										
Foam Earplugs	Classic™ Plus, Classic™ Small, Classic™ SuperFit™ 30, Classic™ SuperFit™ 33, Classic™ Soft									
E-A-Rsoft Foam Earplugs	E-A-Rsoft™ yellow Neon Blasts™, E-Z Fit™, E-A-Rsoft™ SuperFit™, E-A-Rsoft™ FX™, E-A-Rsoft™ Grippers™									
Push-in style earplugs	EXPRESS™ pod plugs™, Push-Ins™, Push-Ins™ with Grip Rings									
Metal Detectable	Metal detectable versions of Classic™, E-A-RSoft™, EXPRESS™ Ultrafit™,									
UltraFit Premolded Earplugs	Combat Arms™, UltraFit™ Plus™, HiFi™ Earplugs									
Semi-Insert Hearing Protectors	E-A-Rflex™ Foam Tips, E-A-Rflex™ Premolded Tips, CABOFLEX™ Semi-insert Hearing Protectors, E-A-Rcaps™ Semi-Insert Hearing Protector									
<p align="center">*These ear plug safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulations.</p>										

3M™ Goggles Crossover

3M Eyewear - Goggles			AOSafety Eyewear - Goggles			
Product Group	Product Code	Description	Product Group	Product Code	Description	Features & Benefits
Classic Series	1620	Perforated Goggles 	332 Goggle	40650-00000	332 Impact Goggle, Clear Lens 	Flexible mask goggle for impact protection Complies with ANSI Z87.1-2003
Classic Series	1621	Splash proof Goggles 	334 Goggle	40660-00000	334 Chemical Splash Goggle 	Flexible mask goggle Indirect vent ports for dust and splash protection Complies with ANSI Z87.1-2003
Plus Series	1707 AF1	Grey Frame, Clear Lens 	Lexa GoggleGear	16618-00000	GoggleGear w/ Strap, Clear DX Anti-Fog Hard Coat Lens 	DX™ Anti-Fog Hard Coat Converts Lexa eyewear to a dust goggle Complies with ANSI Z87.1-2003, CSA Z94.3
Plus Series	1707 AF2	Smoke Frame, Smoke Lens 	No Crossover Available			
Plus Series	1707 AF3	Red, White and Blue Frame, Amber Lens 	No Crossover Available			
Pro Series	1623 AF	Blue Frame, Clear Anti-Fog Lens 	484 Goggle	40802-00000	484 Splash Goggle, Clear DX Anti-Fog Hard Coat Lens 	Flexible mask goggle Indirect vent ports for dust and splash protection DX™ Anti-Fog Hard Coat



















*These eyewear safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulations

3M™ Eyewear Crossover

Product Group	Product Code	Description		Product Group	Product Code	Description	Features & Benefits
Classic Series	1611	Visitor Specs, Clear Lens 		Tour-Guard	41120-00000	Tour-Guard Clear, Clear Lens 	Economical visitor spec Fits over most Rx glasses
Classic Series	1700AF	Black Frame, Clear Anti-Fog Lens 		Virtua™	11329-00000	Virtua Clear Temples, Clear Anti-Fog Lens 	Popular unisex styling Lightweight design Universal nose bridge Complies with ANSI Z87.1-2003
Classic Series	1700	Black Frame, Hard Coat Clear Lens 		Virtua™	11326-00000	Virtua Clear Temples, Clear Hard Coat Lens 	Popular unisex styling Lightweight design Universal nose bridge Complies with ANSI Z87.1-2003
Classic Series	1701	Smoke Frame, Smoke Hard Coat Lens 		Virtua™	11327-00000	Virtua Gray Temples, Gray Hard Coat Lens 	Popular unisex styling Lightweight design Universal nose bridge Complies with ANSI Z87.1-2003
Classic Series	1710	Black Frame, Clear Hard Coat Lens 		Nassau Plus	14347-00000	Nassau Plus Black Frame, Clear DX Anti-Fog Hard Coat 	Adjustable length temples DX™ Anti-Fog Hard Coat Complies with ANSI Z87.1-2003, CSA Z94.3
Classic Series	1712	Black Frame, Smoke Hard Coat Lens 		Nassau Rave	14453-00000	Nassau Rave Black Frame Clear DX Anti-Fog Hard Coat 	Vertically vented brow guard Lens angle adjustment Adjustable length temples DX™ Anti-Fog Hard Coat Complies with ANSI Z87.1-2003, CSA Z94.3
Classic Series	1770-1AF	Red Frame, Clear Anti-Fog Lens 		Virtua V8™	11702-00000	Virtua V8 Black Frame, Clear Anti-Fog Lens 	Integral side shields Soft-tipped temples relieve ear "hot-spots" Complies with ANSI Z87.1-2003
Classic Series	1770-3	Red Frame, Amber Hard Coat Lens 		Privo	12267-00000	Privo Silver Frame, Red Accent, Amber Anti-Fog Lens 	Sleek, European-inspired styling Soft molded nose bridge and temple tips Anti-Fog lens Complies with ANSI Z87.1-2003, CSA Z94.3
Classic Series	1780-1	Black Frame, Clear Hard Coat Lens 		Flywear	11200-00000	Flywear, Black Frame, Clear DX Anti-Fog Hard Coat Lens 	Sport-Grip temples optimize fit and comfort DX™ Anti-Fog Hard Coat Complies with ANSI Z87.1-2003, CSA Z94.3
Classic Series	1780-2	Black Frame, Smoke Hard Coat Lens 		Flywear	11201-00000	Flywear, Black Frame, Gray DX Anti-Fog Hard Coat Lens 	Sport-Grip temples optimize fit and comfort DX™ Anti-Fog Hard Coat Complies with ANSI Z87.1-2003, CSA Z94.3
Classic Series	1780-5	Black Frame, Blue Mirror Hard Coat Lens 		Flywear	11201-00000	Flywear, Black Frame, Gray DX Anti-Fog Hard Coat Lens 	Sport-Grip temples optimize fit and comfort DX™ Anti-Fog Hard Coat Complies with ANSI Z87.1-2003, CSA Z94.3
Plus Series	1720	Black Frame, Clear Hard Coat Lens 		Virtua™ V4	11670-00000	Virtua V4 Black Temple, Clear Hard Coat Lens 	Frameless design Soft Temple Tips Soft, universal fit nose bridge Complies with ANSI Z87.1-2003

















*These eyewear safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulation:

3M™ Eyewear Crossover

Product Group	Product Code	Description	Product Group	Product Code	Description	Features & Benefits
Plus Series	1721	Black Frame, Mirrored Hard Coat Lens 	Virtua™ V4	11674-0000	Virtua V4 Black Temple, Indoor/Outdoor Mirror Hard Coat Lens 	Frameless design Soft Temple Tips Soft, universal fit nose bridge Complies with ANSI Z87.1-2003
Plus Series	1722	RWB Frame, Clear Hard Coat Lens 	Lexa™	15258-0000	Lexa RWB Frame, Clear DX Anti-Fog Hard Coat 	Adjustable length temples Lens angle adjustment DX™ Anti-Fog Hard Coat Complies with ANSI Z87.1-2003, CSA Z94.3
Plus Series	1723	Black Frame, Amber Hard Coat Lens 	Virtua™ Sport	11545-0000	Virtua Sport, Light Amber Hard Coat Lens 	Sport styling for unique look Universal nose bridge Lens wrap provides added protection Complies with ANSI Z87.1-2003, CSA Z94.3
Plus Series	1790-10	Black Frame, Clear Lens +1.0 Magnification 	BX™ Series	11374-0000	BX Silver/Black Frame, Clear Lens with +1.5 Diopter 	Fully adjustable and high style Adjustable length temple Lens angle adjustment Adjustable nose bridge Complies with ANSI Z87.1-2003, CSA Z94.3
Plus Series	1790-15	Black Frame, Clear Lens +1.5 Magnification 	BX™ Series	11374-0000	BX Silver/Black Frame, Clear Lens with +1.5 Diopter 	Fully adjustable and high style Adjustable length temple Lens angle adjustment Adjustable nose bridge Complies with ANSI Z87.1-2003, CSA Z94.3
Plus Series	1790-20	Black Frame, Clear Lens +2.0 Magnification 	BX™ Series	11375-0000	BX Silver/Black Frame, Clear Lens with +2.0 Diopter 	Fully adjustable and high style Adjustable length temple Lens angle adjustment Adjustable nose bridge Complies with ANSI Z87.1-2003, CSA Z94.3
Plus Series	1790-25	Black Frame, Clear Lens +2.5 Magnification 	BX™ Series	11376-0000	BX Silver/Black Frame, Clear Lens with +2.5 Diopter 	Fully adjustable and high style Adjustable length temple Lens angle adjustment Adjustable nose bridge Complies with ANSI Z87.1-2003, CSA Z94.3
Pro Series	1744-1	Black Frame, Clear Hard Coat Lens 	Virtua™ V7	11691-0000	Virtua V7, Clear Temple, Clear Hard Coat Lens 	Frameless, unisex design Soft, universal fit nose bridge Soft temple tips Complies with ANSI Z87.1-2003
Pro Series	1744-4	Black Frame, In/Out Mirror Lens 	Virtua Sport	11388-0000	Virtua Sport Clear Temple I/O HC Lens 	Comfortable, Ultra light frame Sporty, sleek unisex styling 9 base curve lens High Impact polycarbonate filters 99.9% UV



















*These eyewear safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulation:

3M™ Eyewear Crossover

Product Group	Product Code	Description	Product Group	Product Code	Description	Features & Benefits
Pro Series	1744-5	Black Frame, Blue Mirror Lens 	Virtua	11331-00000	Virtua With Blue Mirror Lens 	Sleek Styling - Popular with men & women. Lightweight - less than 1 oz. Contoured flexible temples for comfortable fit Hard Coat guards against scratching, static and chemical attack.
Pro Series	1750 / 37113	Black Frame, Clear Hard Coat Lens 	Virtua™ V4	11670-00000	Virtua V4 Black Temple, Clear Hard Coat Lens 	Unisex styling Soft, dual-injected temples for increased comfort Soft, universal nose bridge Complies with ANSI Z87.1-2003
Pro Series	1751 / 37114	Black Frame, Smoke Hard Coat Lens 	Virtua V4	11671-00000	Virtua V4 Black Temple, Gray Hard Coat Lens 	Unisex styling Soft, dual-injected temples for increased comfort Soft, universal nose bridge Complies with ANSI Z87.1-2003
Pro Series	1752 / 37115	Blue Frame, In/Out Mirror Lens 	Virtua™ V4	11674-00000	Virtua V4 Black Temple, Indoor/Outdoor Lens 	Unisex styling Soft, dual-injected temples for increased comfort Soft, universal nose bridge Complies with ANSI Z87.1-2003
Pro Series	11753AF	Blue Frame, Clear Anti-Fog Lens 	Virtua™ V4	11672-00000	Virtua V4 Black Temple, Clear Anti-Fog Lens 	Unisex styling Soft, dual-injected temples for increased comfort Soft, universal nose bridge Complies with ANSI Z87.1-2003
Pro Series	1760 / 37116	Clear Frame, Clear Hard Coat Lens 	X.Sport	15182-00000	X.Sport Silver Frame, Clear Anti-Fog Lens 	Sport-Grip temples Adjustable nose bridge Complies with ANSI Z87.1-2003, CSA Z94.3
Pro Series	1761-2	Brown Frame, Smoke Hard Coat Lens 	Moon Dawg™	11215-00000	Moon Dawg Black Frame, Gray Anti-Fog Lens 	Surf-inspired design Excellent side coverage Complies with ANSI Z87.1-2003
Pro Series	1761-6	Brown Frame, Gold Mirror Lens 	Moon Dawg™	11215-00000	Moon Dawg Black Frame, Gray Anti-Fog Lens 	Surf-inspired design Excellent side coverage Complies with ANSI Z87.1-2003

*These eyewear safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulation:

3M™ Head Protection Products Crossover

Description	Product Code	Color	Case Qty.	Description	Product Code	Color	Case Qty.			
 Omega II Hard Hat 6PT Pinlock	1901	White	30	 XLR8 Hard Hat 6PT Pinlock	45964-00001	White	20			
	1902	Yellow			45963-00001	Yellow	20			
	1903	Orange			45968-00001	Hi-Viz Orange	20			
	1905	Red			45967-00001	Red	20			
	1906	Blue			45965-00001	Blue	20			
					45966-00001	Green	20			
 Omega II Hard Hat 6PT Ratchet	1911	White	30	 XLR8 Hard Hat 6PT Ratchet	45995-00001	White	20			
	1912	Yellow			45969-00001	Yellow	20			
	1913	Orange			45974-00001	Hi-Viz Orange	20			
	1915	Red			45998-00001	Burnt Orange	20			
	1916	Blue			45973-00001	Red	20			
					45971-00001	Blue	20			
Omega II 6PT Pinlock Suspension	1904	NA	10	XLR8 6PT Pinlock Suspension	45977-00001	NA	20			
Omega II 6PT Ratchet Suspension	1914	NA	10	XLR8 6PT Ratchet Suspension	45978-00001	NA	20			
 Hard Top Hard Hat 4PT Pinlock	1927-1	White	12	 LR50 Hard Hat 4PT Pinlock	46310-00000	White	20			
	1927-2	Yellow			46311-00000	Yellow	20			
	1927-5	Red			46312-00000	Red	20			
	1927-3	Orange			46313-00000	Hi-Viz Orange	20			
	1927-6	Blue			46314-00000	Blue	20			
	1927-7	Gray			46316-00000	Gray	20			
								46315-00000	Green	20
								46317-00000	White	20
								46318-00000	Yellow	20
								46319-00000	Red	20
					46320-00000	Hi-Viz Orange	20			
					46321-00000	Blue	20			
					46322-00000	Green	20			
Hard Top 4PT Pinlock Suspension	1927-RS	NA	10	LR50 4PT Pinlock Suspension	46324-00000	NA				
				LR50 4PT Ratchet Suspension	46325-00000	NA				
Omega Brow Pad	1940	NA	10	LR50 Replaceable Brow Pad	46730-00000	NA	50			
 Bump Cap 4PT Pinlock	1803	White	6	 Bump Cap 4PT Pinlock	46525-00000	White	30			
					46526-00000	Yellow	30			
 Classic Faceshield Kit, Polycarbonate Window	1631		5	 H4 Pinlock Headgear with Polycarbonate Window	82781-00000		5			
 Pro Faceshield Kit, Polycarbonate Anti-Fog	1633		6	 H8 Ratchet Headgear	82501-00000		10			
 WP96AF Clear Polycarbonate Anti-Fog Window				 WP96AF Clear Polycarbonate Anti-Fog Window	82704-00000		10			
 Polycarbonate Replacement Window	1632		10	 WP96R Std. Clear Polycarbonate Window	82579-00000		25			
 Pro Replacement Polycarbonate Anti-Fog Window	1634		6	 WP96AF Clear Polycarbonate Anti-Fog Window	82704-00000		10			

These head and face safety products must be used in accordance with warnings and user instructions accompanying product and applicable safety standards and regulation: