



# LEXA™

EYEWEAR SYSTEM



## A TRUE EYEWEAR SYSTEM

Lexa™ is a patented eyewear system with individual solutions to specific eye protection problems. The Lexa System includes task-specific lens tints and shades, including the Indoor/Outdoor Mirror lens with no backside reflection and the MinimIzeR™ lens that helps protect against welding “flash burn.” Lexa bifocal readers are available in three different magnification diopters (both Clear and MinimIzeR lenses) for workers who have difficulty reading small print or who are engaged in small detail work. Plus, Lexa can be transformed into a dust or splash goggle with GoggleGear™ accessories, which makes Lexa a true eyewear system.





**LEXA PUTS IT ALL TOGETHER.**

Lightweight, contoured coverage, available in two lens sizes and meets the requirements of ANSI Z87.1-2003 and CSA Z94.3-2007 high impact.

**Lens Angle Adjustment** - wearers can adjust Lexa to three different lens angles for a customized fit.

**Adjustable Temple Length** - temples adjust to four different lengths to correctly fit different faces.



**DX™ Anti-Fog Coating** - the anti-fog hard coat resists fogging, scratching, static and chemical attack.

**Contoured Coverage** - the patented aspheric lens follows and blends with the facial outline to provide protective coverage.

**Adjustable Universal-Fit Nosebridge** - nosebridge design is soft and pliable so wearers can shape it specifically for their noses.

**Task-Specific Lenses** - different lenses are available to meet a variety of job requirements or personal tastes.



## THE LEXA EYEWEAR SYSTEM - ONE FOR ALL.

One of the most versatile systems on the market, LEXA provides what you need. The patented aspheric lens provides protective coverage and offers a virtually unobstructed viewing range. That's just the beginning. By interchanging components, LEXA easily transforms into a variety of task-specific eye protectors. This one-for-all modularity isn't just a convenience plus for wearers. It's an economical advantage for safety budgets, too.



Lexa eyewear features include adjustable temples, DX Anti-Fog Hard Coat and Easy-Change™ lenses.



Dust GoggleGear for Lexa eyewear snaps on to comfortably help keep out particulates.



Splash GoggleGear for Lexa eyewear creates a lightweight, comfortable splash goggle.

Product Code	Description	Shipping UPC	Case Packaging	Carton Weight (lbs.)	Carton Dimensions (L x W x H)	Shipper Weight (lbs.)	Shipper Dimensions (L x W x H)
15100-00000-20	Lexa Black Temple, Clear DX Lens (Large)	10078371622777	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15101-00000-20	Lexa Blue Temple, Clear DX Lens (Large)	10078371622784	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15150-00000-20	Lexa Black Temple, MinimizeR DX Lens (Large)	10078371622814	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15200-00000-20	Lexa Black Temple, Clear DX Lens (Medium)	10078371622876	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15201-00000-20	Lexa Blue Temple, Clear DX Lens (Medium)	10078371622883	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15204-00000-20	Lexa Black Temple, Gray DX Lens (Medium)	10078371622890	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15208-00000-20	Lexa Black Temple, Amber DX Lens (Medium)	10078371622906	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15210-00000-20	Lexa Black Temple, Arc-Block DX Lens (Medium)	10078371622913	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15211-00000-20	Lexa Black Temple, Shade 3.0 IR, DX Lens (Medium)	10078371622920	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15212-00000-20	Lexa Black Temple, Shade 5.0 IR, DX Lens (Medium)	10078371622937	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15213-00000-20	Lexa Black Temple, Vermillion DX Lens (Medium)	10078371622944	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15214-00000-20	Lexa Black Temple, I/O Mirror DX Lens (Medium)	10078371622951	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15250-00000-20	Lexa Black Temple, MinimizeR DX Lens (Medium)	10078371622999	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
13353-00000-20	Lexa Reader, Black Temples, Clear DX Lens, +1.5 Diopter (Medium)	10078371622500	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
13354-00000-20	Lexa Reader, Black Temples, Clear DX Lens, +2.0 Diopter (Medium)	10078371622517	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
13355-00000-20	Lexa Reader, Black Temples, Clear DX Lens, +2.5 Diopter (Medium)	10078371622524	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
13415-00000-20	Lexa Reader, Black Temples, MinimizeR DX Lens, +1.5 Diopter (Medium)	10078371134157	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
13416-00000-20	Lexa Reader, Black Temples, MinimizeR DX Lens, +2.0 Diopter (Medium)	10078371134164	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
13417-00000-20	Lexa Reader, Black Temples, MinimizeR DX Lens, +2.5 Diopter (Medium)	10078371134171	1 eyewear/bag, 10 eyewear/carton, 2 cartons/shipper	1.10	6.00" x 6.75" x 6.00"	2.75	12.25" x 6.875" x 6.125"
15152-00000-100	Lexa Bulk Pack Fighter, Black Temple, Clear DX Lens (Medium)	10078371622821	1 eyewear/bag, 100 eyewear/shipper	NA	NA	8.84	18.875" x 15.875" x 10.50"
15153-00000-100	Lexa Bulk Pack Fighter, Black Temple, Gray DX Lens (Medium)	10078371622838	1 eyewear/bag, 100 eyewear/shipper	NA	NA	8.84	18.875" x 15.875" x 10.50"
15154-00000-100	Lexa Bulk Pack Fighter, Black Temple, Clear DX Lens (Large)	10078371622845	1 eyewear/bag, 100 eyewear/shipper	NA	NA	8.84	18.875" x 15.875" x 10.50"
15158-00000-100	Lexa Bulk Pack Fighter, Blue Temple, Clear DX Lens (Medium)	10078371622852	1 eyewear/bag, 100 eyewear/shipper	NA	NA	8.84	18.875" x 15.875" x 10.50"
15163-00000-100	Lexa Bulk Pack Fighter, American Red/White/Blue Temple, Clear DX Lens (Large)	10078371622869	1 eyewear/bag, 100 eyewear/shipper	NA	NA	8.84	18.875" x 15.875" x 10.50"
15258-00000-100	Lexa Bulk Pack Fighter, American Red/White/Blue Temple, Clear DX Lens (Medium)	10078371623019	1 eyewear/bag, 100 eyewear/shipper	NA	NA	8.84	18.875" x 15.875" x 10.50"
15145-00000-20	Lexa Replacement Lens, Clear DX (Large)	10078371622807	1 lens/bag, 20 lenses/carton, 1 carton/shipper	1.30	6.00" x 6.75" x 6.00"	1.72	6.875" x 6.125" x 6.125"
15245-00000-20	Lexa Replacement Lens, Clear DX (Medium)	10078371622975	1 lens/bag, 20 lenses/carton, 1 carton/shipper	1.30	6.00" x 6.75" x 6.00"	1.72	6.875" x 6.125" x 6.125"
15246-00000-20	Lexa Replacement Lens, Gray DX (Medium)	10078371622982	1 lens/bag, 20 lenses/carton, 1 carton/shipper	1.30	6.00" x 6.75" x 6.00"	1.72	6.875" x 6.125" x 6.125"
15251-00000-20	Lexa Replacement Lens, MinimizeR DX (Medium)	10078371623002	1 lens/bag, 20 lenses/carton, 1 carton/shipper	1.30	6.00" x 6.75" x 6.00"	1.72	6.875" x 6.125" x 6.125"
16615-00000-10	Lexa Dust GoggleGear, Black Frame with Temples, Clear DX Lens (Medium)	10078371623286	1 eyewear/bag, 10 eyewear/carton, 1 carton/shipper	1.45	6.00" x 6.75" x 8.00"	1.87	6.875" x 6.25" x 8.25"
16616-00000-10	Lexa Dust GoggleGear, Black Frame with Temples, Clear DX Lens (Large)	10078371623293	1 eyewear/bag, 10 eyewear/carton, 1 carton/shipper	1.45	6.00" x 6.75" x 8.00"	1.87	6.875" x 6.25" x 8.25"
16617-00000-10	Lexa Dust GoggleGear, Black Frame with Strap, Clear DX Lens (Medium)	10078371623309	1 eyewear/bag, 10 eyewear/carton, 1 carton/shipper	1.45	6.00" x 6.75" x 8.00"	1.87	6.875" x 6.25" x 8.25"
16618-00000-10	Lexa Dust GoggleGear, Black Frame with Strap, Clear DX Lens (Large)	10078371623316	1 eyewear/bag, 10 eyewear/carton, 1 carton/shipper	1.45	6.00" x 6.75" x 8.00"	1.87	6.875" x 6.25" x 8.25"
16644-00000-10	Lexa Splash GoggleGear with Clear Shroud, Clear DX Lens (Medium)	10078371623361	1 eyewear/bag, 10 eyewear/carton, 1 carton/shipper	1.45	6.00" x 6.75" x 8.00"	1.87	6.875" x 6.25" x 8.25"
16645-00000-10	Lexa Splash GoggleGear with Clear Shroud, Clear DX Lens (Large)	10078371623378	1 eyewear/bag, 10 eyewear/carton, 1 carton/shipper	1.45	6.00" x 6.75" x 8.00"	1.87	6.875" x 6.25" x 8.25"

**FOR ORDERING INFORMATION OR YOUR NEAREST STOCKING DISTRIBUTOR:**

	USA	Canada
Tel	1-800-225-9038	1-800-387-9681
Fax	1-800-488-8007	1-800-488-8007

Aero Technologies . 8001 Woodland Drive . Indianapolis, IN . 46278  
© 2009 3M Company. All rights reserved. 3M, Lexa, GoggleGear, MinimizeR, DX, and Easy-Change are trademarks of 3M Company. AOSafety is a trademark of American Optical IP Corporation, used under license.

**⚠ WARNING:**

These eye and face products help provide limited eye and face protection against flying particles. **Misuse or failure to follow warnings and instructions may result in serious personal injury, including blindness or death.** For proper use, see supervisor, read instructions and warnings on the package or call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.

