

e-Branch Library

Library access wherever your customers need it

With the 3M e-Branch Library system, your library can provide service 24 hours a day, 7 days a week. It's a quick, cost-effective way to expand your services without adding staff. Plus, you'll increase the visibility of your library within the community—seamlessly and effortlessly. This ATM-like workstation provides immediate library access wherever your customers need it. The system can be installed at convenient locations, including malls, supermarkets, retail stores and community centers, and is perfect for customers on the go. This free-standing terminal provides users a direct link to library databases, services and information—in the touch of a button. Most important, the e-Branch Library narrows the digital divide by providing quick, convenient internet access. Customers can log on and get everything from stock quotes to local weather to information about healthcare, government services, employment opportunities and education.

Computer (included)

- Pentium IV; 2.8 GHZ processor; 512 MB; 80GB Hard Drive; 24XCD-ROM
- Integrated Intel extreme graphics
- 17" LCD flat screen monitor with 3M resistive touch overlay
- ADA – compliant design
- Fully functioning water and vandal proof keyboard with rugged industrial trackball
- Amplified dual speaker system
- Video with up to 48 MB shared memory and Microsoft operating system
- TCP/IP Ethernet and Token Ring support
- PIK Nav-Master

Support and Maintenance (available)

- Complete software and hardware maintenance agreements, including parts and labor

Options Available

- Telephone handset and cradle with volume control
- Magnetic stripe credit/debit card reader
- Integrated coin and bill acceptor

System Integration Included

- Complete design of screens of suggested information sites
- Local integrated library system (OPAC) via web
- Statewide library information databases
- Local online city/county/state web sites
- Filter provided if requested

Certifications

- FCC Class A product approval standards
- FCC Part 15 and Part 68
- UL/ETL CSA (Canada)

Energy Profile

- Dual voltage 110v or 220v with duplex fixture (15 amps max)

Software (included)

- PIKup exclusive design
- PIKsecurity system
- Microsoft XP-PRO license

Hardware

- Amplified dual speaker system
- 8.5"-wide thermal printer with parallel interface and 750-sheet capacity paper roll



3M Library Systems

3M Center, Bldg. 225-4N-14
St. Paul, MN 55144-1000
USA
1-800-328-0067
www.3M.com/us/library

Please recycle. Printed in USA.
© 3M 2008. All rights reserved.
3M, SelfCheck and Tattle-Tape
are trademarks of 3M.

Distributed by 3M for PIK, Inc.