

Specialty Films Selection Guide

						Absorbent Pad
Properties ¹		9960	9962	9967	9971	1603
1. Sterilization ² (G=Gamma; E=Ethylene Oxide)		G	G	G, E	G	G
2. Hypoallergenic		No	No	Yes	No	No
3. Printability		Yes	Yes	Yes	Yes	N/A
4. Fluid Resistance		Yes	Yes	Yes	Yes	Absorbent
5. Heat Sealable		No	No	Yes	No	Yes
6. Light Transmission, 400nm/700nm	percentage	83/90.2	82.5/92.5	N/A	92	Opaque
7. Haze Level, maximum	percentage	2.5	1.4	N/A	1.4	N/A
8. Color		Clear	Clear	Transparent	Clear	White
9. Typical Tensile, MD	lbs/inch	166	85	15	98	7
	Newtons/25mm	738	378	66.7	439	31
10. Elongation, minimum	percentage	70	90	100	90	N/A
11. Film/Liner Caliper	mil	6.8	3.9	2.0	3.9	29
	millimeters	0.17	0.10	0.05	0.1	0.74
12. Maximum Width	inches	49	49	52	49	36
	centimeters	124.5	124.5	132	124.5	91.4
13. Maximum Length	yards	1600	2500	1500	1700	100
	meters	1463	2286	1372	1545	92
14. Approx. Roll Diameter	inches	22	21	12.5	17.7	12
	centimeters	56	53	32	50	30.5
15. Shelf Life	years	1	1	2	1	5

¹ Properties listed are based on limited testing and for comparative purposes only. It is the customer's responsibility to determine the final suitability of our products for use in their application.

² Recommended suitability is based on the processability of product through typical sterilization conditions. It is the customer's responsibility to determine the final suitability of our products for use in their application.