



Novec™

Electronic Coating

EGC-1702

Introduction

3M™ Novec™ Electronic Coating EGC-1702 is a clear, low viscosity solution of a fluorochemical acrylate polymer coating carried in a hydrofluoroether solvent. The solvent is nonflammable, has low toxicity and provides acceptable environmental properties for today's demanding electronic applications. It contains no volatile organic compounds (VOCs). When applied to clean, moisture-free surfaces such as copper, aluminum, ceramic, steel, tin or glass, Novec coating EGC-1702 dries to form an ultra-thin transparent film with excellent anti-wetting, anti-stiction, anti-migration, and anti-corrosion properties for many diverse applications. This makes it ideal for many uses in the electronics industry including coating MR recording heads, spindle motors, head gimbal assemblies (HGAs), MEMS, CRTs and LCDs. The low surface energy film repels liquids such as lubricating oils, hydrocarbon oils and silicones.

Novec coating EGC-1702 will form a clear, nearly invisible, uniform film that is insoluble in solvents such as heptane, toluene, and water. It is strippable with fluorinated solvents. These films can endure up to 175°C for prolonged periods and maintain good repellency.

Typical Properties

Not for
specification
purposes

Properties	Novec Coating EGC-1702
Appearance	Clear, colorless to light-colored liquid solution
Solids	0.2%
Specific Gravity @ 25°C	1.5
Solvent	3M™ Novec™ Engineered Fluid HFE-7100DL
Boiling Point of Solvent	61°C
Flash Point	None
Thermal Stability of Dry Film	Repellent to chlorinated silicone oil after 24 hrs at 175°C
Surface Energy of Dry Film	11-12 dynes/cm
Coating Thickness (dip coated)	~0.1 micron
Refractive Index of Dry Film	1.38

Environmental, Health and Safety

Before using this product, please read the current product Material Data Safety Sheet (available through your 3M sales or technical service representative) and the precautionary statement on the product package. Follow all applicable precautions and directions.

3M™ Novec™ Electronic Coating EGC-1702 Advantages

The low surface energy films cast from 3M™ Novec™ Electronic Coating EGC-1702 have excellent repellency to hydrocarbon oils, silicone oils, synthetic fluids and aqueous solutions. With a surface energy of 11-12 dynes/cm, Novec coating EGC-1702 films compare favorably to coatings of polyethylene and polytetrafluoroethylene, which have surface energy values of approximately 31 and 18 dynes/cm respectively. This property enables non-solubilizing solvents such as heptane, toluene, and water as well as liquids having low surface tension values such as lubricating oils, silicones, etc. to bead and drain freely from surfaces coated with Novec coating EGC-1702 while leaving the film intact. EGC-1702 coating exhibits many of the practical characteristics desired in a coating system, as seen below, making it ideal for many applications.

Properties	Novec Coating EGC-1702
Ease of Application	Excellent
Removable	Yes
Solder-through Repairability	Yes
Solvent/Chemical Resistance	Excellent
Ease of Cure/Dry	Dries at room temperature and can be handled in under two minutes
Shelf Life	4 years
Transparent	Yes
Environmental	Low in toxicity, non-ozone depleting, nonflammable, not a VOC
One Part System	Yes

Resources

For additional technical information on Novec coating EGC-1702, call 3M Specialty Materials at one of the numbers below. For other 3M global offices, and information on additional 3M products, visit our web site at www.3m.com/electronicmaterials

United States

3M Specialty Materials
3M Center, Building 223-6S-04
St. Paul, MN 55144-1000
800 810 8513
800 810 8514 (Fax)

Europe

3M Specialty Materials
3M Belgium N. V.
Haven 1005, Canadastraat 11
B-2070 Zwijndrecht
32 3 250 7521

3M Canada Company

Specialty Materials
P.O. Box 5757
London, Ontario
N6A 4T1
800 364 3477

Sumitomo 3M Limited

33-1, Tamagawadai 2-chome
Setagaya-ku, Tokyo
158-8583 Japan
813 3709 8250

Asia Pacific and Latin America

Call (U.S.) **651 736 7123**

Important Notice to Purchaser: The information in this publication is based on tests that we believe are reliable. Your results may vary due to differences in test types and conditions. You must evaluate and determine whether the product is suitable for your intended application. Since conditions of product use are outside of our control and vary widely, the following is made in lieu of all express or implied warranties (including the warranties of merchantability or fitness for a particular purpose): Except where prohibited by law, 3M's only obligation and your only remedy, is replacement or, at 3M's option, refund of the original purchase price of product that is shown to have been defective when you received it. In no case will 3M be liable for any direct, indirect, special, incidental, or consequential damages (including, without limitation, lost profits, goodwill, and business opportunity) based on breach of warranty, condition or contract, negligence, strict tort, or any other legal or equitable theory.



3M Specialty Materials

3M Center, Building 223-6S-04
St. Paul, MN 55144-1000

www.3m.com/electronicmaterials

Issued: 09/01

© 2001 3M IPC

98-0212-2547-3 (HB)