

“3M™ Wall Display, your single solution to effective presentations.”

3M Wall Display

- **Display Size** 60" diagonal viewable area; 4:3 aspect ratio; 48"W x 36"H
 - **Viewing Angle** 170° horizontal, 170° vertical
 - **Optical Structure** Single 0.7", DLP™ Texas Instruments technology, XGA (1024 x 768)
 - **Colors** 24 bit full color
 - **ANSI Contrast Ratio** 150:1 typical; 100:1 minimum
 - **Lamp Type** SHP
 - **Lamp Life** 2000 Hours typical
 - **Dimensions** 47.6"H x 53.2"W x 7.0"D (1208 mm x 1350 mm x 179 mm)
 - **Weight** 3.7" (92 mm) including mounting bracket
 - **Video Compatibility** Approx. 85 lbs. (39 kg.)
 - **RGB Compatibility** NTSC, NTSC 4.43, PAL, PAL-N, PAL-M, SECAM
 - **Mouse Emulation** VGA to SXGA: 640 x 480, 720 x 400, 800 x 600, 832 x 624, 1024 x 768, 1152 x 864, 1280 x 960, 1280 x 1024
 - **Computer Input** Serial, ADB, USB
 - **Video Input** Analog RGB 15 pin D-Sub
 - **Audio** Digital RGB DVI-D
 - **Video Input** Audio 3.5 mm stereo mini
 - **Audio out** RCA jack
 - **Serial Control** Mini-Din 4 pin
 - **Audio amp** RCA jacks
 - **Power Requirements** RCA jacks loop-through
 - **Environmental** 9 pin D-Sub, RS-232
 - **Regulatory** 18 Watt per channel
 - **Included Accessories** Two 3.1" stereo
 - **User Interface** Input 100-240 VAC, 50/60 Hz, 3 Wire Grounded, 350 W. max
 - **Presentation Tools** Operating 10 - 35°C, 10 - 85%RH, without condensation
 - **Warranty** Storage -10 - 60°C, 10 - 85%RH, without condensation
- Altitude 0 - 6000 feet above sea level
- UL, CE, FCC Class A
- Power Cord Set (US, UK, Euro), VGA Cable (2 m), AV RCA cable (3 m), S-video cable (2 m), 3.5 mm stereo mini cable (2 m)
- Mac ADB
- IR Remote with navigator and mouse emulation, AAA batteries
- Single-position, fixed, hanging mount
- On-screen menu system; operable with or without remote
- Reveal, Blank, Freeze, Magnify, Pan, and Pointer
- One-year limited warranty on parts and labor. 90 day warranty on lamp

Covered by U.S. Patents 6,179,426 and 442,205
Other patents are pending.

“Wherever there's a great meeting, you'll find 3M.”™


www.3M.com/meetings



3M Wall Display

CONNECTION

3M™ Wall Display Connector Panel



"Wherever there's a great meeting, you'll find 3M."™

www.3M.com/meetings

3M

Visual Systems Division
Building A145-5N-01
6801 River Place Blvd.
Austin, TX 78726-9000

3M Canada

P.O. Box 5757
London, Ontario, Canada
N6A 4T1

3M Mexico, S.A. de C.V.

Apartado Postal 14-139
Mexico, D.F. 07070
Mexico

Specifications subject to change
without notice.

Digital Light Processing, DLP Digital
Micromirror Device and DMD are
trademarks of Texas Instruments.

© 3M 2001 Vikuiti and the Vikuiti
"Eye" symbol are trademarks of 3M.

LITHO in USA © 3M IPC 2001
Rev. A
78-6970-8501-3 (08.01.100C)