

3M™ Benchtop Air Ionizer 963E

The use of ionized air in electronics work environments eliminates the build up of potentially damaging static charges. Air ionizers are primarily used to control static charge on nonconductive materials. Grounding is normally used to control charge on conductive objects and personnel, however, nonconductors cannot be grounded to drain electrostatic charge. Ionization is the only method of neutralizing a static charge on a nonconductor. Ionized air can neutralize static charges on circuit board substrates, insulating tapes and plastic objects found in the work area. The 3M Benchtop Air Ionizer 963E blankets the benchtop with ionized air to help prevent static from damaging sensitive electronics.

The 963E ionizer uses AC 100V to 230V power. The ionizer features a two-speed fan, a power indicator lamp, a static-dissipative plastic housing, and a combination metal-plastic stand that can also double as a mounting bracket.

Rapid neutralization of electrostatic charge

The ion-generation technology present in the 963E ionizer is capable of producing extremely large amounts of ions, resulting in nearly instantaneous static charge neutralization. The 963E ionizer is capable of reducing a static charge of 1000V to 100V in less than one second, at a one foot distance, when tested* at the high fan speed. In addition, the powerful fan allows the generated ions to be carried at high speed for long distances. At a distance of three feet, the discharge time only increases to approximately five seconds.

**When tested according to ANSI/ESD S3.1-1991*

Intrinsically balanced, maintenance-free

3M ionizers have a proprietary, intrinsically balanced ion generation system which ensures that equal levels of positive and negative ions are produced despite variations in line voltage, fan speed, and emitter point condition. No adjustment or calibration is required to maintain ion balance. This allows the unit to generate a balanced mix of positive and negative ions - even if the emitter points become dirty.

The 963E ionizer is virtually maintenance free. The ionizer's unique design requires only periodic cleaning of emitter points to maintain optimum performance. The points do not require replacement and the unit does not require adjustment before or after cleaning.



3M™ Benchtop Air Ionizer 963E

Basic Features

- Two versions available, depending on power cord plug
- Neutralizes static charges on nonconductive objects
- Maintains equal balance of positive-negative ions
- Two-speed fan
- Static-dissipative housing
- UL, C-UL, CE, NOM certification

Quiet and comfortable air flow

The two-speed fan in the 3M™ Benchtop Air Ionizer 963E is extremely quiet at low speed. Where industrial noise may irritate personnel and lower productivity, the 963E Ionizer may be used without contributing significantly to the ambient noise. The fan's gentle airflow does not disturb paper or delicate parts. The high-speed fan setting can be used for more rapid neutralization of static charges in environments where faster decay rates are required.

Static-dissipative housing safe to use in ESD sensitive areas

The injection-molded plastic case is constructed of static dissipative plastic. The conductivity of the case prevents a static charge from building up on the surface of the housing, a common problem with ionizers. This "ESD-safe" design allows the ionizer to be part of your overall static-safeguarded electronic workstation.

Meets Global Regulatory Requirements

Global usage of electronic products are often dependent on the product meeting regulatory requirements for the country of usage. To achieve this end, the 963E Ionizer has been tested to, and have passed, regulatory testing for U.S., Canada, Mexico and the European Union. The 963E Ionizer carries the UL, C-UL, NOM marks and CE mark.

Specifications	
Operating Voltage and Frequency	AC 220V/230V 50/60 Hz 0.12A 20W
Power Outlet	IEC 320 Socket
Supplied Power Cord	6' (1.8 m) cord with IEC 320 and Continental Europe (EURO) plugs or US plug
Dimensions	6.0" W x 7.4" H x 3.0" D (15.2 cm W x 18.8 cm H x 7.8 cm D)
Weight	2.5 lb. (1.1 kg)
Air Velocity	low speed - 100 fpm (0.5 m/s) high speed - 300 fpm (1.5 m/s)
Static Discharge Time*	1' (30 cm) < 1 second at high fan speed 3' (91 cm) < 5 second at high fan speed
Certifications and Approvals	CE, UL, C-UL, NOM
Warranty	1-year

(All values are typical, not specifications)

*When tested according to ANSI/ESD S3.1-1991

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether indirect, special, incidental or consequential regardless of the legal theory asserted.**



Electronic Solutions Division Static Control Products

6801 River Place Blvd.
Austin, TX 78726-9000
1-866-722-3736
www.3Mstatic.com

Please recycle. Printed in U.S.A.
© 3M 2009. All rights reserved.
98-0799-0457-3