



PTFE Skived Film Tape

5480 • 5481

Technical Data

June, 2009

Product Description 3M™ PTFE Skived Film Tape 5480 and 5481 has a film backing with a silicone adhesive.

Product Construction	Backing	Adhesive	Color	Standard Roll Length
	Skived PTFE (polytetrafluoroethylene)	Silicone	Gray	36 yds. (32.9 m)

Typical Physical Properties **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

			ASTM Test Method
3M tape 5480			
Adhesion to Steel:	20 oz./in. width (22 N/100 mm)		D-3330
Tensile Strength:	27 lbs./in. width (473 N/100 mm)		D-3759
Elongation at Break:	140%		D-3759
Backing Thickness:	2.0 mils (0.05 mm)		D-3652
Total Tape Thickness:	3.7 mils (0.09 mm)		D-3652
Temperature Use Range:	-65° to 400°F (-54° to 204°C)		
3M tape 5481			
Adhesion to Steel:	32 oz./in. width (35 N/100 mm)		D-3330
Tensile Strength:	49 lbs./in. width (858 N/100 mm)		D-3759
Elongation at Break:	335%		D-3759
Backing Thickness:	5.0 mils (0.13 mm)		D-3652
Total Tape Thickness:	6.8 mils (0.17 mm)		D-3652
Temperature Use Range:	-65° to 400°F (-54° to 204°C)		

Features

- Skived film tapes demonstrate good conformability when wrapping rollers.
- Provides excellent chemical resistance except to organic solvents. **Note:** The silicone adhesive will be attacked by commercial organic solvents and so are not recommended for applications requiring organic resistance.
- To help prevent wrinkling or bubbling of the backing on PTFE film tapes when they are subjected to temperatures above 250°F (121°C), pre-heat the surface to at least 150°F (66°C) (preferred 180°F, 82°C) to obtain best results.

CAUTION: When PTFE film tape is exposed to temperatures above 400°F (204°C), small quantities of hazardous vapors may be released. **INHALATION OF THESE VAPORS MAY BE HARMFUL OR MAY CAUSE RESPIRATORY TRACT IRRITATION.** Do not heat or expose PTFE film tape to temperatures above 400°F (204°C).

3M™ PTFE Skived Film Tape

5480 • 5481

Application Ideas

- Wrapping rubber laminating rollers on hot polyethylene extruders to create a release surface to help minimize clean-up.
- Easy-release surface provided by wrapping rollers, plates, belts, etc. where build-up of sticky materials and inks can occur.
- Chemical resistant surface for sealing and masking.

Storage

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2009 70-0709-5114-3 (6/09)