

3M™ SelfCheck™ System (S-Series)

[CHECK-IN]

The affordable, reliable automated check-in system

As a complete check-in and sorting system that is both affordable and reliable, the 3M™ SelfCheck™ System S-Series helps libraries increase circulation and maintain a more accurate catalog, while improving productivity and customer service. With its real-time check-in feature, easy-to-use interface and return receipt, customers are sure each item is returned correctly. In addition, staff can quickly separate exceptions and send materials to the stacks—and customers can immediately check out items with limits. Along with a scalable 3- or 5-bin design, the S-Series lets libraries customize the sort matrix so bins are equally distributed. The system notifies staff when bins are full and sends an instant e-mail if the circulation system goes offline or the printer is out of paper. Libraries can also monitor the number of processed items and schedule staff during peak periods, when the return rate is highest. Most important, the S-Series allows staff to spend more time helping customers.

Real-Time Check-In

- Items are instantly checked in upon return
- Customers receive return receipts
- Speeds the return of items to the stacks
- Reduces the number of claims returned

Automatic Staff Hold Receipts

- Quickly separates exceptions

E-mail Notifications

- Instant notification if the circulation system goes offline or the printer is out of paper

Easy-To-Use Interface

- Customers and staff can easily learn how to use the system

Statistics

- Monitor the return rate
- Schedule staff during peak periods

Customized Sorting

- Set the sort matrix for your library
- Equally distribute items among bins
- Scalable 3- or 5-bin design
- System automatically stops sorting to full bins

Dimensions

- Wall Unit:
57.3" h x 39.3" w x 62.8" l
(1456 mm x 1000 mm x 1596 mm)
- Sorter (3-bin):
64" x 41.8" x 57.6"
(1626 mm x 1060 mm x 1464 mm)
- Sorter (5-bin):
64" x 41.8" x 95"
(1626 mm x 1060 mm x 2413 mm)

Energy Profile

- Wall Unit:
220–240 VAC, single phase
50–60 Hz 3A
- Sorter:
220–240 VAC, single phase
50–60 Hz 2.5A

Weight (Approximate)

- Wall Unit:
880 lbs (400 Kg)
- Sorter (3-bin):
440 lbs (200 Kg)
- Sorter (5-bin):
620 lbs (282 Kg)

WALL UNIT



SORTER (3 OR 5 BIN)

UL-Certified



3M Library Systems

3M Center, Building 225-4N-14

St. Paul, MN 55144-1000

1-800-328-0067

In Canada, 1-800-364-3577

www.3M.com/us/library

© 3M 2007

Printed in U.S.A.

3M, SelfCheck and Tattle-Tape are trademarks of 3M.