

# Universal Self-Service Station (RF)



- Seamless interface with most circulation systems**
- Instantaneous communication for fast, efficient checkout**
- Attractive and durable design**
- Enhanced customer privacy, convenience and satisfaction**
- Daily, weekly and monthly statistics reports available**
- Ability to print on receipt paper or tabs**



**The automated self-checkout station provides a powerful, flexible package that allows library customers to manage their own transactions easily and efficiently.**

Give your customers a user-friendly alternative to long checkout lines. Checkpoint's automated self-checkout station provides a powerful, flexible package that allows library customers to manage their own transactions easily and efficiently. It simplifies the checkout process, helps eliminate waiting, ensures customer privacy and increases customer satisfaction.

#### **A complete solution to complement your RF anti-theft system**

The system includes:

- Touch-screen monitor running an advanced graphical user interface (GUI) walks customers through the checkout process.
- High-performance omni-directional barcode scanner makes it easy to capture information from materials and library cards.
- High-speed, long-life thermal printer with integrated cutter.
- Optional tab printer.

#### **User interface is custom tailored to your library**

On the system's touch-screen monitor, easy-to-use software clearly guides customers through the checkout process. Video clips showing the location of barcodes, date due cards, etc. are customized to reflect your library's specific operations, so the customer can checkout without assistance.

#### **Review customer self-checkout status with custom reports**

With the user-friendly reporting capability, now you can easily run daily, weekly or monthly usage reports. Generate reports manually or schedule them to run automatically. You can display reports on screen, print them or save them to a file and even circulate them via e-mail.

#### **Upgradable to RFID**

This solution offers you the flexibility to upgrade to RFID by adding appropriate internal components and software.

# Universal Self-Service Station (RF)

## Specifications:

### Physical Specifications

**Dimensions:** 24" H x 15" W x 18.5" D  
(610mm x 380mm x 470mm)

**Weight:** 77 lbs. (35 kg)

**Electrical Requirements:** 110/220VAC, 50/60Hz,  
3/1.5 amp, 185 watt

**Packaging:** tabletop (standard)  
built-in or free standing kiosk

### Environmental

#### Operating temperature:

32°F to 104°F (0°C to 40°C)

#### Storage temperature:

-4°F to 140°F (-20°C to 60°C)

#### Storage/operating humidity:

10% to 90%, non-condensing

### Communications

**Network:** TCP/IP

**Library:** SIP, SIP2

### Peripherals

**Monitor:** 15" touch screen LCD flat panel  
(1024x768 resolution)

**Barcode Scanner:** high-performance line scan  
(left or right mount)

**Printer:** high-speed thermal direct receipt printer with  
drop-in paper loading

**Paper Supply:** 3 1/8" wide x 3 1/4" diameter  
(80mm wide x 83mm diameter) roll

### Security Support

**Radio Frequency (RF):** detuning receipts or date due labels

**Upgradable to Radio Frequency Identification (RFID):**  
any ISO-15693 or MCRF compatible systems

### Software

**Operating System:** Windows/XP Pro

**Languages:** 2 languages standard, additional options upon request

#### Standard Features:

Patron authentication

Cardless sign-on

Checkout

Display account status

Renewals

Graphical User Interface (GUI) for customization including:

Receipt format, Patron messages, Screen graphics

### Optional Features

#### Check-in

### Certifications

#### US/Canada:

EMI, EMC – FCC part 15 subparts b and c

Safety – CUI (dual listing comprising of UL60950-1, and 22.2 60950-1)

#### Australia/New Zealand:

EMI – Australia-New Zealand 4268

EMC – Cispar 11

Safety – Australia-NZ 60950

#### Australia/New Zealand:

EMI – EN 300 330-2

EMC – EN 301 489

Safety – EN60950

Human Exposure – EN 50634

### Superior performance drives customer satisfaction and enhances security

Universal self-service station communicates instantaneously with the host circulation system, providing immediate customer status and material classification for fast, efficient checkout. If a customer attempts to perform a restricted transaction—such as using an expired library card, borrowing more materials than permitted or leaving fines unpaid—a polite reminder is shown to direct the customer to visit your library's circulation department.

*Distributed  
exclusively by*



### 3M Library Systems

3M Center  
Building 225-4N-14  
St. Paul, MN 55144  
1-800-328-0067  
In Canada, 1-800-364-3577

[www.3M.com/us/library](http://www.3M.com/us/library)